

SGM72022A General Purpose DPDT Transfer Switch

GENERAL DESCRIPTION

The SGM72022A is a double-pole/double-throw (DPDT) transfer switch, which supports from 0.4GHz to 5.8GHz. The device features low insertion loss and high isolation, which make it suitable for high linearity and 2G/3G/4G/5G applications.

The SGM72022A has the ability to integrate DPDT transfer switch and GPIO controller on an SOI chip. Internal driver and decoder for switch control signals are offered by the GPIO controller, which makes it flexible in RF path routing and band selection.

No external DC blocking capacitors are required on the RF paths as long as no external DC voltage is applied, which can save PCB area and cost.

The SGM72022A is available in a Green ULGA-1.1× 1.5-10L package.

FEATURES

- Low Insertion Loss
- Operating Frequency Range: 0.4GHz to 5.8GHz
- High Isolation
- GPIO Interface for 1.3V to V_{DD} Control Logic
- Broadband Performance Suitable for All Cellular Modulation Schemes up to 5.8GHz
- Ultra-Low Current Consumption
- Linearity and Harmonic Performance Ideally Suited for LTE Applications
- No External DC Blocking Capacitors Required
- Available in a Green ULGA-1.1×1.5-10L Package

APPLICATIONS

2G/3G/4G/5G Applications

BLOCK DIAGRAM




Figure 1. SGM72022A Block Diagram

LOGIC TRUTH TABLE


VCTL	ACTIVE PATH
L	RF1 to RF3, RF2 to RF4
Н	RF1 to RF4, RF2 to RF3



PACKAGE/ORDERING INFORMATION

MODEL	PACKAGE SPECIFIED TEMPERATURE RANGE		ORDERING NUMBER	PACKAGE MARKING	PACKING OPTION
SGM72022A	ULGA-1.1×1.5-10L	-40°C to +85°C	SGM72022AYULU10G/TR	6G XX	Tape and Reel, 5000

MARKING INFORMATION



Green (RoHS & HSF): SG Micro Corp defines "Green" to mean Pb-Free (RoHS compatible) and free of halogen substances. If you have additional comments or questions, please contact your SGMICRO representative directly.

ABSOLUTE MAXIMUM RATINGS

Supply Voltage, V _{DD} 3.6V
Control Voltage, V _{CTL}
Maximum Input Power
39dBm (1:1 VSWR, +25°C, 25%DC)
Junction Temperature+150°C
Storage Temperature Range55°C to +150°C
Lead Temperature (Soldering, 10s)+260°C
ESD Susceptibility
HBM2000V
CDM 2000V

RECOMMENDED OPERATING CONDITIONS

Operating Temperature Range	40°C to +85°C
Operating Frequency Range	0.4GHz to 5.8GHz
Supply Voltage Range, V _{DD}	1.7V to 3.3V
Control Low Voltage, V _{CTL_L}	0V to 0.45V
Control High Voltage, V _{CTL H}	1.3V to 3.3V

OVERSTRESS CAUTION

Stresses beyond those listed in Absolute Maximum Ratings may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect reliability. Functional operation of the device at any conditions beyond those indicated in the Recommended Operating Conditions section is not implied.


ESD SENSITIVITY CAUTION

This integrated circuit can be damaged if ESD protections are not considered carefully. SGMICRO recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage. ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because even small parametric changes could cause the device not to meet the published specifications.

DISCLAIMER

SG Micro Corp reserves the right to make any change in circuit design, or specifications without prior notice.

PIN CONFIGURATION



PIN DESCRIPTION

PIN	NAME	FUNCTION
1, 3, 5, 7	GND	Ground.
2	RF3	RF Port 3.
4	RF1	RF Port 1.
6	RF2	RF Port 2.
8	RF4	RF Port 4.
9	VCTL	Logic Control.
10	VDD	Supply Voltage.

ELECTRICAL CHARACTERISTICS

 $(T_A = +25^{\circ}C, V_{DD} = 1.7V \text{ to } 3.3V, \text{ typical values are at } V_{DD} = 2.8V, P_{IN} = 0 \text{dBm}, \text{ input and output resistance} = 50\Omega, \text{ unless otherwise noted.})$

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS	
DC Characteristics							
Supply Voltage	V_{DD}		1.7	2.8	3.3	V	
Supply Current	I_{VDD}			60	80	μA	
Control Voltage	V _{CTL_H}	High	1.3	1.8	3.3	V	
Control Voltage	V _{CTL_L}	Low	0		0.45	V	
Control Current	I _{CTL}			2	8	μA	
Switching Time	t _{SW}	10% VCTL to 90% RF		2	3	μs	
Turn-On Time	t _{ON}	50% V _{DD} to 90% RF			20	μs	
RF Characteristics							
		f ₀ = 0.4GHz to 1.0GHz		0.30	0.50		
	IL	f ₀ = 1.0GHz to 2.0GHz		0.32	0.60	dB	
Insertion Loss (RF1/RF2 to RF3/RF4)		f ₀ = 2.0GHz to 2.7GHz		0.34	0.70		
		f ₀ = 3.0GHz to 3.8GHz		0.47	0.80		
		f ₀ = 4.8GHz to 5.8GHz		0.66	1.15		
	ISO	f ₀ = 0.4GHz to 1.0GHz	30	33			
Isolation		f ₀ = 1.0GHz to 2.0GHz	27	30		dB	
(RF1/RF2 to RF3/RF4;		f ₀ = 2.0GHz to 2.7GHz	20	22			
RF1 to RF2, RF3 to RF4)		f ₀ = 3.0GHz to 3.8GHz	16	19			
		f ₀ = 4.8GHz to 5.8GHz	14	18			
2 nd Harmonic	2f ₀	f ₀ = 824MHz to 915MHz, P _{IN} = 35dBm		-88		dBc	
3 rd Harmonic	3f ₀	f ₀ = 824MHz to 915MHz, P _{IN} = 35dBm		-80		dBc	
Input Return Loss (RF1/RF2 to RF3/RF4)	RL	f ₀ = 0.4GHz to 5.8GHz		-15		dB	
0.1dB Compression Point (RF1/RF2 to RF3/RF4)	P _{0.1dB}	f ₀ = 0.4GHz to 5.8GHz		38		dBm	
VSWR (RF1, RF2, RF3, RF4)	VSWR	f ₀ = 0.4GHz to 5.8GHz		1.5			
2 nd Order Intermodulation	IMD2	$f_1 > 800MHz$ at 20dBm, $f_2 > 2.5GHz$ at -15dBm		-105		dBm	
3 rd Order Intermodulation	IMD3	f ₁ > 800MHz at 20dBm, f ₂ > 2.5GHz at -15dBm		-105		dBm	

TYPICAL APPLICATION CIRCUIT




Figure 2. SGM72022A Typical Application Circuit

EVALUATION BOARD LAYOUT




Figure 3. SGM72022A Evaluation Board Layout

SGM72022A

General Purpose DPDT Transfer Switch


REVISION HISTORY

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Original (SEPTEMBER 2022) to REV.A

Page

PACKAGE OUTLINE DIMENSIONS ULGA-1.1×1.5-10L




Cymphol	Dimensions In Millimeters					
Symbol	MIN	MOD	MAX			
А	0.500	0.550	0.600			
A1	0.150	0.180	0.210			
A2	0.370 REF					
b	0.150 0.200		0.250			
D	1.050	1.100	1.150			
E	1.450 1.500		1.550			
е	0.400 BSC					
L	0.150	0.200	0.250			
L1	0.000	0.050	0.100			
eee	0.100					

NOTE: This drawing is subject to change without notice.

TAPE AND REEL INFORMATION

REEL DIMENSIONS




NOTE: The picture is only for reference. Please make the object as the standard.

KEY PARAMETER LIST OF TAPE AND REEL

Package Type	Reel Diameter	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P0 (mm)	P1 (mm)	P2 (mm)	W (mm)	Pin1 Quadrant
ULGA-1.1×1.5-10L	7"	9.5	1.3	1.7	0.75	4.0	4.0	2.0	8.0	Q1

CARTON BOX DIMENSIONS



NOTE: The picture is only for reference. Please make the object as the standard.

KEY PARAMETER LIST OF CARTON BOX

Reel Type	Length Width (mm)		Height (mm)	Pizza/Carton	1
7" (Option)	368	227	224	8	
7"	442	410	224	18	200007