




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2013.08.08	李芳忠




Specifications
 Current Rating: 3Amp
 Insulation Resistance: 1000MΩMin.
 Dielectric Withstanding Voltage: 600VAC
 Contact Resistance: 20mΩMax.
 Operating Temperature: -40°C to +105°C
 Materials
 Contact Material: Brass
 Insulator Material: High Temperature Thermoplastic, UL 94V-0 Nylon 6T (Halogen Free) or the equivalent material
 All materials must meet Greenconn requirement for environment protection.

Ordering Information

G PHA109 - XX XX A 017 R 1 B X

- No. of Pins per Row: 01~40
- Standard Plating: 02=Gold Flash, 01=Tin, 05=Gold Flash/Tin
- Color: 1=Black
- Standard Packing: A=Box, C=Tube
- Selective Plating



Recommended P.C.Board Hole Layout
 (Tolerance: ±0.05)

REV. 01	UNIT. mm	SCALE. 4:1	PAGE. 1/1		GENERAL TOLERANCE		DESIGN: 李芳忠	DWG. NO. GPHA109-CA17RB	TITLE. 2.54 PIN HEADER SINGLE ROW DIP TYPE CONNECTOR
	X: ±5.0°	X: ±0.30	CHECKED: 劉北平		DATE: 2013.08.08	PART NO. GPHA109-XXXX A017R1BX			
					X: ±3.0°	X: ±0.25	AUDITED:		
					.XX' ±2.0°	.XX ±0.15	DATE:		
					.XXX' ±1.0°	.XXX ±0.10	DATE:		
							APPROVED:		

1 2 3 4 5 6 7 8 9

A B C D E F