

SGM8634C 550µA, 6MHz, Rail-to-Rail I/O CMOS Operational Amplifier

GENERAL DESCRIPTION

The SGM8634C is a quad, low voltage, low noise and low power operational amplifier, which can operate from 2.5V to 5.5V single supply, while consuming only 550µA quiescent current per amplifier at 5V.

The SGM8634C features a 3.5mV maximum input offset voltage. The minimum input common mode voltage is within 0.1V below the negative rail, and the output swing is rail-to-rail with heavy loads. It exhibits a high gain-bandwidth product of 6MHz and a slew rate of 3.7V/µs. These specifications make the operational amplifier appropriate for various applications.

The SGM8634C is available in Green SOIC-14 and TSSOP-14 packages. It is specified over the extended -40°C to +125°C industrial temperature range.

FEATURES

Input Offset Voltage: 3.5mV (MAX)High Gain-Bandwidth Product: 6MHz

• High Slew Rate: 3.7V/µs

Settling Time to 0.1% with 2V Step: 2.1µs

Overload Recovery Time: 0.9µs

Low Noise: 12nV/√Hz

Rail-to-Rail Input and Output

Supply Voltage Range: 2.5V to 5.5V

Input Voltage Range: -0.1V to 5.6V with V_s = 5.5V

• Low Supply Current: 550µA/Amplifier (TYP)

-40°C to +125°C Operating Temperature Range

Available in Green SOIC-14 and TSSOP-14 Packages

APPLICATIONS

Sensors

Audio

Active Filters

A/D Converters

Communications

Test Equipment

Cellular and Cordless Phones

Laptops and PDAs

Photodiode Amplification


Battery-Powered Instrumentation

PACKAGE/ORDERING INFORMATION

MODEL	PACKAGE DESCRIPTION	SPECIFIED TEMPERATURE RANGE	ORDERING NUMBER	PACKAGE MARKING	PACKING OPTION
001100010	SOIC-14	-40°C to +125°C	SGM8634CXS14G/TR	SGM8634XS14 XXXXX	Tape and Reel, 2500
SGM8634C	TSSOP-14	-40°C to +125°C	SGM8634CXTS14G/TR	SGM8634 XTS14 XXXXX	Tape and Reel, 3000

MARKING INFORMATION

NOTE: XXXXX = Date Code and Vendor Code.



Green (RoHS & HSF): SG Micro Corp defines "Green" to mean Pb-Free (RoHS compatible) and free of halogen substances. If you have additional comments or questions, please contact your SGMICRO representative directly.

ABSOLUTE MAXIMUM RATINGS

Supply Voltage, +V _S to -V _S	6V
Input Common Mode Voltage Range	
(-V _S) -	$0.3V$ to $(+V_S) + 0.3V$
Junction Temperature	+150°C
Storage Temperature Range	65°C to +150°C
Lead Temperature (Soldering, 10s)	+260°C
ESD Susceptibility	
HBM	1500V
MM	400V

RECOMMENDED OPERATING CONDITIONS

Operating Temperature Range-40°C to +125°C

OVERSTRESS CAUTION

Stresses beyond those listed in Absolute Maximum Ratings may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect reliability. Functional operation of the device at any conditions beyond those indicated in the Recommended Operating Conditions section is not implied.

ESD SENSITIVITY CAUTION


This integrated circuit can be damaged if ESD protections are not considered carefully. SGMICRO recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage. ESD damage can range from subtle performance degradation to complete device failure. Precision

integrated circuits may be more susceptible to damage because even small parametric changes could cause the device not to meet the published specifications.

DISCLAIMER

SG Micro Corp reserves the right to make any change in circuit design, or specifications without prior notice.

PIN CONFIGURATIONS





ELECTRICAL CHARACTERISTICS


(At T_A = +25°C, V_S = 5V, V_{CM} = $V_S/2$, R_L = 600 Ω , Full = -40°C to +125°C, unless otherwise noted.)


PARAMETER	SYMBOL	CONDITIONS	TEMP	MIN	TYP	MAX	UNITS	
Input Characteristics								
			+25°C		0.8	3.5		
Input Offset Voltage	Vos		Full			5	mV	
Input Bias Current	I _B		+25°C		1		pА	
Input Offset Current	Ios		+25°C		1		pА	
Input Common Mode Voltage Range	V _{CM}	V _S = 5.5V	Full	-0.1		5.6	V	
		V 55VV 04V4 0V	+25°C	72	86			
Common Mode Rejection Ratio	CMRR	$V_S = 5.5V$, $V_{CM} = -0.1V$ to 4V	Full	70			dB	
		V _S = 5.5V, V _{CM} = -0.1V to 5.6V	+25°C		78			
On an Lagar Vallage Cain		$R_L = 600\Omega$, $V_{OUT} = 0.15V$ to $4.85V$	+25°C	88	102		40	
Open-Loop Voltage Gain	A _{OL}	$R_L = 10k\Omega, V_{OUT} = 0.05V \text{ to } 4.95V$	+25°C	90	108		dB	
Input Offset Voltage Drift	ΔV _{OS} /ΔΤ		Full		2.4		μV/°C	
Output Characteristics							•	
Outrout Valtage Code of frage Dail		R _L = 600Ω	+25°C		100			
Output Voltage Swing from Rail	V _{OUT}	R _L = 10kΩ	+25°C		15		mV	
Outside Object Object Occupant	I _{SC}		+25°C	±32	±45			
Output Short-Circuit Current			Full	±12			mA	
Closed-Loop Output Impedance		f = 200kHz, G = 1	+25°C		3		Ω	
Power Supply							•	
Operating Voltage Range	Vs		Full	2.5		5.5	V	
Outro cont Commont//Amontifica		I _{OUT} = 0	+25°C		550	675		
Quiescent Current//Amplifier	lα		Full			825	μA	
Davier Complet Dalastics Datia	5000		+25°C	68	85		40	
Power Supply Rejection Ratio	PSRR	$V_S = 2.5V$ to 5.5V, $V_{CM} = (-V_S) + 0.5V$	Full	66			dB	
Dynamic Performance								
Gain-Bandwidth Product	GBP	$R_L = 10k\Omega$	+25°C		6		MHz	
Phase Margin	φο		+25°C		60		0	
Full-Power Bandwidth	BW _P	< 1% distortion, R_L = 600Ω	+25°C		250		kHz	
Slew Rate	SR	G = +1, 2V Step, R _L = 10kΩ	+25°C		3.7		V/µs	
Settling Time to 0.1%	ts	G = +1, 2V Step, R _L = 600Ω	+25°C		2.1		μs	
Overload Recovery Time	ORT	$V_{IN} \times G = V_S, R_L = 600\Omega$	+25°C		0.9		μs	
Noise	•				•	•	•	
Input Voltage Noise Density	e _n	f = 1kHz	+25°C		12		nV/√Hz	
Input Current Noise Density	in	f = 1kHz	+25°C		3		fA/√Hz	


TYPICAL PERFORMANCE CHARACTERISTICS



















TYPICAL PERFORMANCE CHARACTERISTICS (continued)



















TYPICAL PERFORMANCE CHARACTERISTICS (continued)



















TYPICAL PERFORMANCE CHARACTERISTICS (continued)














APPLICATION INFORMATION

Rail-to-Rail Input

When SGM8634 works at the power supply between 2.5V and 5.5V, the input common mode voltage range is from (-V_S) - 0.1V to (+V_S) + 0.1V. In Figure 1, the ESD diodes between the inputs and the power supply rails will clamp the input voltage not to exceed the rails.




Figure 1. Input Equivalent Circuit

Rail-to-Rail Output

The SGM8634 supports rail-to-rail output operation. In single power supply application, for example, when +V_S = 5V, -V_S = GND, $10k\Omega$ load resistor is tied from OUT pin to ground, the typical output swing range is from 0.015V to 4.985V.

Driving Capacitive Loads

The SGM8634 is designed for unity-gain stable for capacitive load up to 1000pF. If greater capacitive load must be driven in application, the circuit in Figure 2 can be used. In this circuit, the IR drop voltage generated by $R_{\rm ISO}$ is compensated by feedback loop.




Figure 2. Circuit to Drive Heavy Capacitive Load

Power Supply Decoupling and Layout

A clean and low noise power supply is very important in amplifier circuit design, besides of input signal noise, the power supply is one of important source of noise to the amplifier through $+V_S$ and $-V_S$ pins. Power supply bypassing is an effective method to clear up the noise at power supply, and the low impedance path to ground of decoupling capacitor will bypass the noise to GND. In application, $10\mu F$ ceramic capacitor paralleled with $0.1\mu F$ or $0.01\mu F$ ceramic capacitor is used in Figure 3. The ceramic capacitors should be placed as close as possible to $+V_S$ and $-V_S$ power supply pins.




Figure 3. Amplifier Power Supply Bypassing

Grounding

In low speed application, one node grounding technique is the simplest and most effective method to eliminate the noise generated by grounding. In high speed application, the general method to eliminate noise is to use a complete ground plane technique, and the whole ground plane will help distribute heat and reduce EMI noise pickup.

Reduce Input-to-Output Coupling

To reduce the input-to-output coupling, the input traces must be placed as far away from the power supply or output traces as possible. The sensitive trace must not be placed in parallel with the noisy trace in same layer. They must be placed perpendicularly in different layers to reduce the crosstalk. These PCB layout techniques will help to reduce unwanted positive feedback and noise.

APPLICATION INFORMATION (continued)

Typical Application Circuits

Difference Amplifier

The circuit in Figure 4 is a design example of classical difference amplifier. If $R_4/R_3 = R_2/R_1$, then $V_{OUT} = (V_P - V_N) \times R_2/R_1 + V_{REF}$.




Figure 4. Difference Amplifier

High Input Impedance Difference Amplifier

The circuit in Figure 5 is a design example of high input impedance difference amplifier, the added amplifiers at the input are used to increase the input impedance and eliminate drawback of low input impedance in Figure 4.




Figure 5. High Input Impedance Difference Amplifier

Active Low-Pass Filter

The circuit in Figure 6 is a design example of active low-pass filter, the DC gain is equal to $-R_2/R_1$ and the -3dB corner frequency is equal to $1/2\pi R_2C$. In this design, the filter bandwidth must be less than the bandwidth of the amplifier, the resistor values must be selected as low as possible to reduce ringing or oscillation generated by the parasitic parameters in PCB layout.




Figure 6. Active Low-Pass Filter

550µA, 6MHz, Rail-to-Rail I/O CMOS Operational Amplifier

SGM8634C


REVISION HISTORY


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Original (MARCH 2018) to REV.A


Page


PACKAGE OUTLINE DIMENSIONS SOIC-14






RECOMMENDED LAND PATTERN (Unit: mm)







Symbol		nsions meters	Dimensions In Inches			
	MIN	MAX	MIN	MAX		
Α	1.35	1.75	0.053	0.069		
A1	0.10	0.25	0.004	0.010		
A2	1.25	1.65	0.049	0.065		
A3	0.55	0.75	0.022	0.030		
b	0.36	0.49	0.014	0.019		
D	8.53	8.73	0.336	0.344		
Е	5.80	6.20	0.228	0.244		
E1	3.80	4.00	0.150	0.157		
е	1.27	0.050	BSC			
L	0.45	0.80	0.018	0.032		
L1	1.04	REF	0.040 REF			
L2	0.25	BSC	0.01 BSC			
R	0.07		0.003			
R1	0.07		0.003			
h	0.30	0.50	0.012	0.020		
θ	0°	8°	0°	8°		

PACKAGE OUTLINE DIMENSIONS TSSOP-14





RECOMMENDED LAND PATTERN (Unit: mm)






Symbol	_	nsions meters	Dimensions In Inches			
	MIN MAX		MIN	MAX		
А		1.200		0.047		
A1	0.050	0.150	0.002	0.006		
A2	0.800	1.050	0.031	0.041		
b	0.190	0.300	0.007	0.012		
С	0.090	0.200	0.004	0.008		
D	4.860	5.100	0.191	0.201		
E	4.300	4.500	0.169	0.177		
E1	6.250	6.550	0.246	0.258		
е	0.650 BSC		0.026 BSC			
L	0.500	0.700	0.02	0.028		
Н	0.25 TYP		0.01 TYP			
θ	1°	7°	1°	7°		

TAPE AND REEL INFORMATION

REEL DIMENSIONS




NOTE: The picture is only for reference. Please make the object as the standard.

KEY PARAMETER LIST OF TAPE AND REEL

Package Type	Reel Diameter	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P0 (mm)	P1 (mm)	P2 (mm)	W (mm)	Pin1 Quadrant
SOIC-14	13"	16.4	6.60	9.30	2.10	4.0	8.0	2.0	16.0	Q1
TSSOP-14	13"	12.4	6.95	5.60	1.20	4.0	8.0	2.0	12.0	Q1

CARTON BOX DIMENSIONS



NOTE: The picture is only for reference. Please make the object as the standard.

KEY PARAMETER LIST OF CARTON BOX

Reel Type	Length (mm)	Width (mm)	Height (mm)	Pizza/Carton
13"	386	280	370	5