

# SGM321XC5 1MHz, 60µA, Rail-to-Rail I/O CMOS Operational Amplifier

#### **GENERAL DESCRIPTION**

The SGM321XC5 is a single, low cost, voltage feedback amplifier. The device can operate from 2.1V to 5.5V single supply, while consuming only 60μA quiescent current. It provides rail-to-rail input with a wide input common mode voltage range and rail-to-rail output voltage swing. This feature makes SGM321XC5 appropriate for buffering ASIC.

The SGM321XC5 offers a gain-bandwidth product of 1MHz and an ultra-low input bias current of 10pA. It is well suited for piezoelectric sensors, integrators and photodiode amplifiers.

The SGM321XC5 is designed into a wide range of applications, such as battery-powered instrumentation, safety monitoring, portable systems, and transducer interface circuits in low power systems.

The SGM321XC5 is available in a Green SC70-5 package. It is specified over the extended -40°C to +125°C temperature range.

#### **FEATURES**

Low Cost

Input Offset Voltage: 5mV (MAX)
Ultra-Low Input Bias Current: 10pA

• Unity-Gain Stable

Gain-Bandwidth Product: 1MHzRail-to-Rail Input and Output

Supply Voltage Range: 2.1V to 5.5V

Input Voltage Range: -0.1V to 5.6V with V<sub>S</sub> = 5.5V

• Low Supply Current: 60μA

• -40°C to +125°C Operating Temperature Range

• Available in a Green SC70-5 Package

#### **APPLICATIONS**

ASIC Input or Output Amplifiers

Piezoelectric Transducer Amplifiers

**Battery-Powered Equipment** 

Portable Equipment

Sensor Interfaces

Medical Instrumentation

Mobile Communications

**Audio Outputs** 

**Smoke Detectors** 

Notebook PCs

PCMCIA Cards

**DSP Interfaces** 

#### PACKAGE/ORDERING INFORMATION

MODEL	PACKAGE DESCRIPTION	SPECIFIED TEMPERATURE RANGE	ORDERING NUMBER	PACKAGE MARKING	PACKING OPTION
SGM321XC5	SC70-5	-40°C to +125°C	SGM321XC5/TR	321	Tape and Reel, 3000

Green (RoHS & HSF): SG Micro Corp defines "Green" to mean Pb-Free (RoHS compatible) and free of halogen substances. If you have additional comments or questions, please contact your SGMICRO representative directly.

#### **ABSOLUTE MAXIMUM RATINGS**

Supply Voltage, +V <sub>S</sub> to -V <sub>S</sub>	6V
Input Common Mode Voltage Range	
(-V <sub>S</sub> ) - 0.3	$V \text{ to } (+V_S) + 0.3V$
Package Thermal Resistance @ T <sub>A</sub> = +25°C	
SC70-5, θ <sub>JA</sub>	333°C/W
Junction Temperature	+150°C
Storage Temperature Range	-65°C to +150°C
Lead Temperature (Soldering, 10s)	+260°C
ESD Susceptibility	
HBM	4000V
MM	400V

#### RECOMMENDED OPERATING CONDITIONS

Operating Temperature Range .....-40°C to +125°C

#### **OVERSTRESS CAUTION**

Stresses beyond those listed in Absolute Maximum Ratings may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect reliability. Functional operation of the device at any conditions beyond those indicated in the Recommended Operating Conditions section is not implied.

#### **ESD SENSITIVITY CAUTION**


This integrated circuit can be damaged if ESD protections are not considered carefully. SGMICRO recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures

can cause damage. ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because even small parametric changes could cause the device not to meet the published specifications.

#### **DISCLAIMER**

SG Micro Corp reserves the right to make any change in circuit design, or specifications without prior notice.

#### PIN CONFIGURATION




## **ELECTRICAL CHARACTERISTICS**


(At  $V_S$  = 5V,  $R_L$  = 100k $\Omega$  connected to  $V_S/2$ , and  $V_{OUT}$  =  $V_S/2$ , unless otherwise noted.)


				SGM321XC5						
DADAMETED	OVMOOL	CONDITIONS	TYP	MIN/MAX OVER TEMPERATURE						
PARAMETER	SYMBOL	CONDITIONS	+25℃	+25°C	-40°C to +125°C	UNITS	MIN/MAX			
Input Characteristics	nput Characteristics									
Input Offset Voltage	Vos	$V_{CM} = V_S/2$	0.8	5	6	mV	MAX			
Input Offset Voltage Drift	$\Delta V_{OS}/\Delta T$		2.7			μV/°C	TYP			
Input Bias Current	I <sub>B</sub>		10			pА	TYP			
Input Offset Current	I <sub>os</sub>		10			pA	TYP			
Input Common Mode Voltage Range	V <sub>CM</sub>	V <sub>S</sub> = 5.5V	-0.1 to 5.6			V	TYP			
Common Mada Bajaction Batio	CMRR	$V_S = 5.5V$ , $V_{CM} = -0.1V$ to 4V	70	62	60	- dB MIN				
Common Mode Rejection Ratio	CIVIKK	$V_S = 5.5V$ , $V_{CM} = -0.1V$ to 5.6V	68	56	53					
Onen Leen Veltage Cain	^	$R_L = 5k\Omega$ , $V_{OUT} = 0.1V$ to 4.9V	80	70	68	40	MAINI			
Open-Loop Voltage Gain	A <sub>OL</sub>	$R_L$ = 100k $\Omega$ , $V_{OUT}$ = 0.035V to 4.965V	84	80	72	dB MIN				
Output Characteristics										
	V <sub>OH</sub>	R <sub>L</sub> = 100kΩ	4.997	4.980	4.960	V	MIN			
	V <sub>OL</sub>	R <sub>L</sub> = 100kΩ	5	20	40	mV	MAX			
Output Voltage Swing from Rail	V <sub>OH</sub>	$R_L = 10k\Omega$	4.992	4.970	4.950	V	MIN			
	V <sub>OL</sub>	$R_L = 10k\Omega$	8	30	50	mV	MAX			
0.4	I <sub>SOURCE</sub>	D 400 to 1/40	84	60	40	A	MIN			
Output Current	I <sub>SINK</sub>	$R_L = 10\Omega$ to $V_S/2$	75	60	40	mA				
Power Supply	•				•	•				
0 " 1/4 " D				2.1	2.5	V	MIN			
Operating Voltage Range				5.5	5.5	V	MAX			
Power Supply Rejection Ratio	PSRR	V <sub>S</sub> = 2.5V to 5.5V, V <sub>CM</sub> = 0.5V	82	60	56	dB	MIN			
Quiescent Current	IQ		60	80	84	μA	MAX			
Dynamic Performance (C <sub>L</sub> = 100p	oF)				I.					
Gain-Bandwidth Product	GBP		1			MHz	TYP			
Slew Rate	SR	G = +1, 2V Output Step	0.52			V/µs	TYP			
Settling Time to 0.1%	ts	G = +1, 2V Output Step	5.3			μs	TYP			
Overload Recovery Time		$V_{IN} \cdot G = V_S$	2.6			μs	TYP			
Noise Performance										
January Vallage and Nation Dec. 19	_	f = 1kHz	27			nV/√Hz	TYP			
Input Voltage Noise Density	e <sub>n</sub>	f = 10kHz	20			nV/√Hz	TYP			


### TYPICAL PERFORMANCE CHARACTERISTICS


At  $T_A$  = +25°C,  $V_S$  = 5V, and  $R_L$  = 100k $\Omega$  connected to  $V_S/2$ , unless otherwise noted.


















## **TYPICAL PERFORMANCE CHARACTERISTICS (continued)**


At  $T_A$  = +25°C,  $V_S$  = 5V, and  $R_L$  = 100k $\Omega$  connected to  $V_S/2$ , unless otherwise noted.

















## **TYPICAL PERFORMANCE CHARACTERISTICS (continued)**


At  $T_A$  = +25°C,  $V_S$  = 5V, and  $R_L$  = 100k $\Omega$  connected to  $V_S/2$ , unless otherwise noted.















#### Overload Recovery Time



#### APPLICATION INFORMATION

#### Rail-to-Rail Input

When SGM321XC5 works at the power supply between 2.1V and 5.5V, the input common mode voltage range is from (-V<sub>S</sub>) - 0.1V to (+V<sub>S</sub>) + 0.1V. In Figure 1, the ESD diodes between the inputs and the power supply rails will clamp the input voltage not to exceed the rails.




Figure 1. Input Equivalent Circuit

#### Rail-to-Rail Output

The SGM321XC5 supports rail-to-rail output operation. In single power supply application, for example, when  $+V_S = 5V$ ,  $-V_S = GND$ ,  $100k\Omega$  load resistor is tied from OUT pin to  $V_S/2$ , the typical output swing range is from 0.005V to 4.997V.

#### **Driving Capacitive Loads**

The SGM321XC5 is designed for unity-gain stable for capacitive load up to 250pF. If greater capacitive load must be driven in application, the circuit in Figure 2 can be used. In this circuit, the IR drop voltage generated by  $R_{\rm ISO}$  is compensated by feedback loop.




Figure 2. Circuit to Drive Heavy Capacitive Load

#### **Power Supply Decoupling and Layout**

A clean and low noise power supply is very important in amplifier circuit design, besides of input signal noise, the power supply is one of important source of noise to the amplifiers through  $+V_S$  and  $-V_S$  pins. Power supply bypassing is an effective method to clear up the noise at power supply, and the low impedance path to ground of decoupling capacitor will bypass the noise to GND. In application,  $10\mu F$  ceramic capacitor paralleled with  $0.1\mu F$  or  $0.01\mu F$  ceramic capacitor is used in Figure 3. The ceramic capacitors should be placed as close as possible to  $+V_S$  and  $-V_S$  power supply pins.




Figure 3. Amplifier Power Supply Bypassing

# **APPLICATION INFORMATION (continued)**

#### **Typical Application Circuits**

#### **Difference Amplifier**

The circuit in Figure 4 is a design example of classical difference amplifier. If  $R_4/R_3 = R_2/R_1$ , then  $V_{OUT} = (V_P - V_N) \times R_2/R_1 + V_{REF}$ .




Figure 4. Difference Amplifier

#### **High Input Impedance Difference Amplifier**

The circuit in Figure 5 is a design example of high input impedance difference amplifier, the added amplifiers at the input are used to increase the input impedance and eliminate drawback of low input impedance in Figure 4.




Figure 5. High Input Impedance Difference Amplifier

#### **Active Low-Pass Filter**

The circuit in Figure 6 is a design example of active low-pass filter, the DC gain is equal to  $-R_2/R_1$  and the -3dB corner frequency is equal to  $1/2\pi R_2C$ . In this design, the filter bandwidth must be less than the bandwidth of the amplifier, the resistor values must be selected as low as possible to reduce ringing or oscillation generated by the parasitic parameters in PCB layout.




Figure 6. Active Low-Pass Filter

## 1MHz, 60µA, Rail-to-Rail I/O **CMOS Operational Amplifier**

## **SGM321XC5**


## **REVISION HISTORY**


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Original (JUNE 2019) to REV.A


Page


# PACKAGE OUTLINE DIMENSIONS SC70-5





RECOMMENDED LAND PATTERN (Unit: mm)






Symbol		nsions meters	Dimensions In Inches		
	MIN	MAX	MIN	MAX	
Α	0.900	1.100	0.035	0.043	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.000	0.035	0.039	
b	0.150	0.350	0.006	0.014	
С	0.080	0.150	0.003	0.006	
D	2.000	2.200	0.079	0.087	
Е	1.150	1.350	0.045	0.053	
E1	2.150	2.450	0.085	0.096	
е	0.65 TYP		0.026 TYP		
e1	1.300 BSC		0.051 BSC		
L	0.525 REF		0.021	REF	
L1	0.260	0.460	0.010	0.018	
θ	0°	8°	0° 8°		

## TAPE AND REEL INFORMATION

#### **REEL DIMENSIONS**




NOTE: The picture is only for reference. Please make the object as the standard.

#### **KEY PARAMETER LIST OF TAPE AND REEL**

Package Type	Reel Diameter	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P0 (mm)	P1 (mm)	P2 (mm)	W (mm)	Pin1 Quadrant
SC70-5	7"	9.5	2.25	2.55	1.20	4.0	4.0	2.0	8.0	Q3

#### **CARTON BOX DIMENSIONS**



NOTE: The picture is only for reference. Please make the object as the standard.

#### **KEY PARAMETER LIST OF CARTON BOX**

Reel Type	Length (mm)			Pizza/Carton	
7" (Option)	368	227	224	8	
7"	442	410	224	18	