


High Current Chip Perforation Bead

◆ PRODUCT IDENTIFICATION

SBH 0755 S 471 N T T
(1) (2) (3) (4) (5) (6) (7)

- 1: Series Type
- 2: Chip Size (mm): Length X Width
- 3: Material Code
- 4: Nominal Impedance: 470=47 Ω ; 471=470 Ω ;
- 5: Impedance Tolerance: N= $\pm 25\%$
- 6: Company Code
- 7: Packaging: Tape Carrier Package

◆ DIMENSION (: mm)




A	B	C	D	E
5.0 \pm 0.2	4.8 \pm 0.2	5.4 \pm 0.2	2.0 \pm 0.2	7.0 \pm 0.3

◆ ELECICAL SPECIFICATION

MEAS. ITEM	SPEC.				TEST FREQ.
Z	470	Ω	\pm	25%	100MHZ/0.25V
RDC	0.012	Ω	Max.		3302 LCR Meter
IDC	6000	mA	Max.		VR712 LCR Meter+VR1133H
TEMPERATURE	15°C	30°C			
HUMIDITY	25%	85%	RH		

● HP 4191A MILLIOHMMETER

◆ PACKAGING INFORMATION


Part No.	D	P	A0	B0	Packing Quantity
SBH0755S471NTT	16±0.2	12±0.1	7.0±0.3	9.0±0.3	1000PCS/R