



Switching Diodes

FEATURES

- Low forward voltage : $V_F(3) = 0.9 \text{ V}(\text{Typ.})$
- Fast reverse recovery time: $t_{rr} = 1.6 \text{ ns}(\text{Typ.})$
- Small Total Capacitance : $C_T = 0.9\text{pF}(\text{Typ.})$

MARKING: B3

SOT-23



Maximum Ratings @ $T_a=25^\circ\text{C}$

Parameter	Symbol	Value	Unit
Peak Reverse voltage	V_{RM}	85	V
DC Blocking Voltage	V_R	80	V
Average Rectified Output Current	I_o	100	mA
Peak forward surge current	I_{FM}	300	mA
Power Dissipation	P_D	150	mW
Junction Temperature	T_J	125	°C
Storage temperature range	T_{STG}	-55 ~ +150	°C

Electrical Characteristics@ $T_a=25^\circ\text{C}$

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Reverse breakdown voltage	V_R	$I_R=100\mu\text{A}$	80			V
Forward voltage	V_{F1}	$I_F=1 \text{ mA}$		0.6		V
	V_{F2}	$I_F=10 \text{ mA}$		0.72		V
	V_{F3}	$I_F=100 \text{ mA}$		0.9	1.2	V
Reverse voltage leakage current	I_{R1}	$V_R=30 \text{ V}$			0.1	uA
	I_{R2}	$V_R=80 \text{ V}$			0.5	uA
Capacitance between terminals	C_T	$V_R=0 \text{ V}, f=1 \text{ MHz}$		0.9	3.0	pF
Reverse recovery time	t_{rr}	$I_F=10 \text{ mA}$		1.6	4.0	ns

Fig.1 Power Derating Curve




Fig.2 Reverse Characteristics




Fig.3 Forward Characteristics






Fig.4 Capacitance Characteristics




SOT-23 Package Outline Dimensions



SOT-23 mechanical data

UNIT		A	C	D	E	H _E	e	M	L	L ₁	a	∠
mm	max	1.1	0.15	1.4	3.0	2.6	0.5	1.95	0.55 (ref)	0.36 (ref)	0.15	12°
	min	0.9	0.08	1.2	2.8	2.2	0.3	1.7			0.0	
mil	max	43	6	55	118	102	20	77	22 (ref)	14 (ref)	6	
	min	35	3	47	110	87	12	67			0.0	

The recommended mounting pad size



Marking

Type number	Marking code
1SS184	B3