





Switching:25mA at 24VDC
 Non-Switching:100mA at 50VDC
 Initial:50m Ω Max
 After life:100mΩ Max
 Insulation Resistance:100mΩ Min,60 sec at 500VDC
 Dielectric Strength:500VAC for 60seconds
 Swith Capacitance:5pF Max at 1MHZ
 Operation Temperature:-30°C to + 85°C
 Storage Temperature:-40°C to + 85°C
 Operation Force:500gf Max
 Mechanical Life:3000 cycles opertions
 Resistance to Soldering:260±5°C for 3-5 seconds




| Poles(N) | A Dimension(mm) |
|----------|-----------------|
| 01 | 2.54 |
| 02 | 5.08 |
| 03 | 7.62 |
| 04 | 10.16 |
| 05 | 12.70 |
| 06 | 15.24 |
| 07 | 17.78 |
| 08 | 20.32 |
| 09 | 22.86 |
| 10 | 25.40 |
| 12 | 30.48 |



SCHMATIC

| Part Name | Material | Finished |
|------------------|---------------|----------|
| Base | PPS UL94 VO | Black |
| Cover | PPS UL94 VO | Black |
| Actuator | Nylon UL94 VO | White |
| Movadle | Copper Alloy | Gold |
| Terminal Contact | Brass | Gold |
| Terminal | Brass | Gold/Tin |

| | | | | |
|-----|------|----------|-------------|-------|
| A4 | | | | |
| A3 | | | Terminal | |
| A2 | | | | |
| A1 | | | | |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |
| | | A | | B |



| COMMON | TOLERANCE |
|---------|-----------|
| X.XX | ± 0.10 |
| X.X | ± 0.15 |
| X | ± 0.25 |
| ANGULAR | — |

| | | | | |
|----------|--------|------------|------|----------------------|
| UNIT | MM | PROJECTED | | PRODUCT NAME: |
| DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TSD110EZ |
| DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpcu.tw |

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission