

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

Features

- Negligible switching losses
- High junction temperature capability
- Low leakage current
- Good trade-off between leakage current and forward voltage drop
- Avalanche capability specified

Description

These Schottky rectifiers are designed for high frequency miniature switched mode power supplies such as adaptators and on board DC/DC converters. They are available in SMB, and low-profile SMB.




Table 1. Device summary

Symbol	Value
$I_{F(AV)}$	3 A
V_{RRM}	100 V
T_j (max)	175 °C
V_F (max)	0.68 V

1 Characteristics

Table 2. Absolute ratings (limiting values)

Symbol	Parameter		Value	Unit	
V_{RRM}	Repetitive peak reverse voltage		100	V	
$I_{F(AV)}$	Average forward current	SMB	$T_L = 115\text{ °C } \delta = 0.5$	3	A
		SMB flat	$T_L = 140\text{ °C } \delta = 0.5$		
I_{FSM}	Surge non repetitive forward current		$t_p = 10\text{ ms}$ sinusoidal	75	A
P_{ARM}	Repetitive peak avalanche power		$t_p = 1\text{ }\mu\text{s } T_j = 25\text{ °C}$	2400	W
T_{stg}	Storage temperature range		-65 to + 175	°C	
T_j	Operating junction temperature ⁽¹⁾		175	°C	

1. $\frac{dP_{tot}}{dT_j} < \frac{1}{R_{th(j-a)}}$ condition to avoid thermal runaway for a diode on its own heatsink

Table 3. Thermal resistance

Symbol	Parameter		Value	Unit
$R_{th(j-l)}$	Junction to lead	SMB	25	°C/W
		SMB flat	15	

Table 4. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Typ.	Max.	Unit
$I_R^{(1)}$	Reverse leakage current	$T_j = 25\text{ °C}$	$V_R = V_{RRM}$	-	-	1	μA
		$T_j = 125\text{ °C}$		-	0.4	1	mA
$V_F^{(2)}$	Forward voltage drop	$T_j = 25\text{ °C}$	$I_F = 3\text{ A}$	-	-	0.84	V
		$T_j = 125\text{ °C}$		-	0.63	0.68	
		$T_j = 25\text{ °C}$	$I_F = 6\text{ A}$	-	-	0.92	
		$T_j = 125\text{ °C}$		-	0.71	0.76	

1. Pulse test: $t_p = 5\text{ ms}$, $\delta < 2\%$

2. Pulse test: $t_p = 380\text{ }\mu\text{s}$, $\delta < 2\%$

To evaluate the conduction losses use the following equation:

$$P = 0.6 \times I_{F(AV)} + 0.027 I_{F(RMS)}^2$$

Figure 1. Average forward power dissipation versus average forward current




Figure 2. Average forward current versus ambient temperature (delta = 0.5)




Figure 3. Normalized avalanche power derating versus pulse duration




Figure 4. Normalized avalanche power derating versus junction temperature




Figure 5. Non repetitive surge peak forward current versus overload duration (maximum values) (SMB)




Figure 6. Non repetitive surge peak forward current versus overload duration (maximum values) (SMB flat)




Figure 7. Relative variation of thermal impedance junction to ambient versus pulse duration (SMB)




Figure 8. Relative variation of thermal impedance junction to lead versus pulse duration (SMB flat)




Figure 9. Reverse leakage current versus reverse voltage applied (typical values)




Figure 10. Junction capacitance versus reverse voltage applied (typical values)




Figure 11. Forward voltage drop versus forward current




Figure 12. Thermal resistance junction to ambient versus copper surface under each lead (SMB)





Figure 13. Thermal resistance junction to ambient versus copper surface under each lead (SMBflat)



2 Package Information

Table 5. SMB dimensions

Ref.	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A1	1.90	2.45	0.075	0.096
A2	0.05	0.20	0.002	0.008
b	1.95	2.20	0.077	0.087
c	0.15	0.40	0.006	0.016
E	5.10	5.60	0.201	0.220
E1	4.05	4.60	0.159	0.181
D	3.30	3.95	0.130	0.156
L	0.75	1.50	0.030	0.059

Figure 14. SMB footprint (dimensions in mm)





Table 6. SMBflat dimensions

Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	0.90		1.10	0.035		0.043
b ⁽¹⁾	1.95		2.20	0.077		0.087
c ⁽¹⁾	0.15		0.40	0.006		0.016
D	3.30		3.95	0.130		0.156
E	5.10		5.60	0.200		0.220
E1	4.05		4.60	0.189		0.181
L	0.75		1.50	0.029		0.059
L1		0.40			0.016	
L2		0.60			0.024	

1. Applies to plated leads

Figure 15. SMBflat footprint (dimensions in mm)


3 Ordering information

Table 7. Ordering information

Order code	Marking	Package	Weight	Base qty	Delivery mode
STPS3H100	SS310	SMB	0.107 g	3000	Tape and reel
STPS3H100UF	S310	SMB flat	0.050g	3000	Tape and reel