
- Qualified for Automotive Applications
- ESD Protection Exceeds 2000 V Per MIL-STD-883, Method 3015; Exceeds 200 V Using Machine Model (C = 200 pF, R = 0)
- 2-V to 5.5-V V_{CC} Operation
- Max t_{pd} of 6.5 ns at 5 V
- Typical V_{OLP} (Output Ground Bounce)
 <0.8 V at V_{CC} = 3.3 V, T_A = 25°C
- Typical V_{OHV} (Output V_{OH} Undershoot)
 >2.3 V at V_{CC} = 3.3 V, T_A = 25°C
- Support Mixed-Mode Voltage Operation on All Ports
- I_{off} Supports Partial-Power-Down Mode Operation



description/ordering information

This hex inverter is designed for 2-V to 5.5-V V_{CC} operation.

The SN74LV04A contains six independent inverters. This device performs the Boolean function $Y = \overline{A}$.

The device is fully specified for partial-power-down applications using I_{off}. The I_{off} circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

ORDERING INFORMATION†

| T _A | PACKAGE [‡] | | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|----------------|----------------------|---------------|--------------------------|---------------------|
| -40°C to 105°C | TSSOP - PW | Tape and reel | SN74LV04ATPWRQ1 | LV04AT |

[†] For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at http://www.ti.com.

FUNCTION TABLE (each inverter)

| INPUT A | OUTPUT Y |
|------------|-------------|
| Н | L |
| L | Н |

logic diagram, each inverter (positive logic)





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



[‡] Package drawings, thermal data, and symbolization are available at http://www.ti.com/packaging.

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

| Supply voltage range, V _{CC} | –0.5 V to 7 V |
|--|-----------------------------------|
| Input voltage range, V _I (see Note 1) | –0.5 V to 7 V |
| Voltage range applied to any output in the high-impedance | |
| or power-off state, V _O (see Note 1) | –0.5 V to 7 V |
| Output voltage range, V _O (see Notes 1 and 2) | –0.5 V to V _{CC} + 0.5 V |
| Input clamp current, I _{IK} (V _I < 0) | –20 mA |
| Output clamp current, I _{OK} (V _O < 0) | –50 mA |
| Continuous output current, I _O (V _O = 0 to V _{CC}) | ±25 mA |
| Continuous current through V _{CC} or GND | ±50 mA |
| Package thermal impedance, θ _{JA} (see Note 3) | 113°C/W |
| Storage temperature range, T _{stg} | –65°C to 150°C |

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.
 - 2. This value is limited to 5.5 V maximum.
 - 3. The package thermal impedance is calculated in accordance with JESD 51-7.

recommended operating conditions (see Note 4)

| | | | MIN | MAX | UNIT | |
|-----------------|------------------------------------|--|---------------------|---------------------|----------|--|
| V_{CC} | Supply voltage | | 2 | 5.5 | V | |
| | | V _{CC} = 2 V | 1.5 | | | |
| v | High lavel inner true to | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$ | $V_{CC} \times 0.7$ | | v | |
| V_{IH} | High-level input voltage | $V_{CC} = 3 \text{ V to } 3.6 \text{ V}$ | $V_{CC} \times 0.7$ | | V | |
| | | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$ | $V_{CC} \times 0.7$ | | | |
| | | V _{CC} = 2 V | | 0.5 | | |
| ., | | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$ | | $V_{CC} \times 0.3$ | . | |
| V_{IL} | Low-level input voltage | $V_{CC} = 3 \text{ V to } 3.6 \text{ V}$ | | $V_{CC} \times 0.3$ | V | |
| | | V _{CC} = 4.5 V to 5.5 V | | $V_{CC} \times 0.3$ | | |
| VI | Input voltage | <u>.</u> | 0 | 5.5 | V | |
| Vo | Output voltage | | 0 | V _{CC} | V | |
| | | V _{CC} = 2 V | | -50 | μΑ | |
| | | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$ | | -2 | | |
| I _{OH} | High-level output current | $V_{CC} = 3 \text{ V to } 3.6 \text{ V}$ | | -6 | mA | |
| | | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$ | | -12 | | |
| | | V _{CC} = 2 V | | 50 | μΑ | |
| | | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$ | | 2 | | |
| l _{OL} | Low-level output current | V _{CC} = 3 V to 3.6 V | 6 | | mA | |
| | | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$ | 12 | | | |
| | | V _{CC} = 2.3 V to 2.7 V | | 200 | | |
| Δt/Δν | Input transition rise or fall rate | V _{CC} = 3 V to 3.6 V | | 100 | ns/V | |
| | | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$ | | 20 | | |
| T _A | Operating free-air temperature | • | -40 | 105 | °C | |

NOTE 4: All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.



electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | V _{CC} | MIN | TYP | MAX | UNIT | | |
|---------------------------------------|----------------------------------|-----------------|----------------------|-----|------|------|--|--|
| | $I_{OH} = -50 \mu\text{A}$ | 2 V to 5.5 V | V _{CC} -0.1 | | | | | |
| \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ | $I_{OH} = -2 \text{ mA}$ | 2.3 V | 2 | | | ٧ | | |
| V _{OH} | $I_{OH} = -6 \text{ mA}$ | 3 V | 2.48 | | | V | | |
| | $I_{OH} = -12 \text{ mA}$ | 4.5 V | 3.8 | | | | | |
| | $I_{OL} = 50 \mu A$ | 2 V to 5.5 V | | | 0.1 | | | |
| | I _{OL} = 2 mA | 2.3 V | | | 0.4 | ., | | |
| V _{OL} | I _{OL} = 6 mA | 3 V | | | 0.44 | V | | |
| | I _{OL} = 12 mA | 4.5 V | | | 0.55 | | | |
| I _I | V _I = 5.5 V or GND | 0 to 5.5 V | | | ±1 | μΑ | | |
| I _{CC} | $V_I = V_{CC}$ or GND, $I_O = 0$ | 5.5 V | | | 20 | μΑ | | |
| I _{off} | V_1 or $V_0 = 0$ to 5.5 V | 0 | | | 5 | μΑ | | |
| C | V – V or CND | 3.3 V | | 2.3 | | nE | | |
| C _i | $V_I = V_{CC}$ or GND | 5 V | | 2.3 | | pF | | |

switching characteristics over recommended operating free-air temperature range, V_{CC} = 2.5 V \pm 0.2 V (unless otherwise noted) (see Figure 1)

| DADAMETED | FROM | то | LOAD | T, | գ = 25°C | | MAIN | MAY | LINUT |
|-----------------|---------|----------|------------------------|-----|----------|------|------|-----|-------|
| PARAMETER | (INPUT) | (OUTPUT) | CAPACITANCE | MIN | TYP | MAX | MIN | MAX | UNIT |
| t _{pd} | Α | Υ | C _L = 50 pF | | 10 | 15.5 | 1 | 18 | ns |

switching characteristics over recommended operating free-air temperature range, V_{CC} = 3.3 V \pm 0.3 V (unless otherwise noted) (see Figure 1)

| DADAMETER | FROM TO (OUTPUT) | | LOAD | T _A = 25°C | | | MAINI | MAY | |
|-----------------|------------------|----------|------------------------|-----------------------|-----|------|-------|-----|------|
| PARAMETER | (INPUT) | (OUTPUT) | CAPACITANCE | MIN | TYP | MAX | MIN | MAX | UNIT |
| t _{pd} | А | Υ | C _L = 50 pF | | 7.3 | 10.6 | 1 | 12 | ns |

switching characteristics over recommended operating free-air temperature range, V_{CC} = 5 V \pm 0.5 V (unless otherwise noted) (see Figure 1)

| DADAMETED | FROM | то | TO LOAD T _A = 25°C | | | | 84181 | | LINUT |
|-----------------|---------|----------|-------------------------------|-----|-----|-----|-------|-----|-------|
| PARAMETER | (INPUT) | (OUTPUT) | CAPACITANCE | MIN | TYP | MAX | MIN | MAX | UNIT |
| t _{pd} | Α | Υ | C _L = 50 pF | | 5.1 | 7.5 | 1 | 8.5 | ns |

SCLS514C - JULY 2003 - REVISED FEBRUARY 2008

noise characteristics, V_{CC} = 3.3 V, C_L = 50 pF, T_A = 25°C (see Note 5)

| | PARAMETER | MIN | TYP | MAX | UNIT |
|--------------------|---|------|------|------|------|
| V _{OL(P)} | Quiet output, maximum dynamic V _{OL} | | 0.3 | 8.0 | V |
| $V_{OL(V)}$ | Quiet output, minimum dynamic V _{OL} | | -0.1 | -0.8 | V |
| V _{OH(V)} | Quiet output, minimum dynamic V _{OH} | | 3.1 | | V |
| $V_{IH(D)}$ | High-level dynamic input voltage | 2.31 | | | V |
| $V_{IL(D)}$ | Low-level dynamic input voltage | | | 0.99 | V |


NOTE 5: Characteristics are for surface-mount packages only.

operating characteristics, $T_A = 25^{\circ}C$

| | PARAMETER | | NDITIONS | V _{CC} | TYP | UNIT |
|--------------------|-------------------------------|------------------------|------------|-----------------|------|------|
| | Dower dissination conscitones | C - 50 nE | f = 10 MHz | 3.3 V | 9.6 | pF |
| C _{pd} Po | Power dissipation capacitance | $C_L = 50 \text{ pF},$ | f = 10 MHz | 5 V | 11.4 | |



PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, $Z_O = 50 \Omega$, $t_f \leq 3$ ns. $t_f \leq 3$ ns.
- D. The outputs are measured one at a time, with one input transition per measurement.
- E. t_{PLZ} and t_{PHZ} are the same as t_{dis} .
- F. t_{PZL} and t_{PZH} are the same as t_{en}.
- G. t_{PHL} and t_{PLH} are the same as t_{pd} .
- $\mbox{\rm H.}\;\;\mbox{\rm All}\;\mbox{\rm parameters}\;\mbox{\rm and}\;\mbox{\rm waveforms}\;\mbox{\dot{a}}\mbox{\rm re}\;\mbox{\rm not}\;\mbox{\rm applicable}\;\mbox{\rm to}\;\mbox{\rm all}\;\mbox{\rm devices}.$

Figure 1. Load Circuit and Voltage Waveforms









10-Dec-2020

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|-------------------|--------|--------------|--------------------|------|----------------|--------------|-------------------------------|--------------------|--------------|-------------------------|---------|
| | | | | | | | (6) | | | | |
| SN74LV04ATPWRG4Q1 | ACTIVE | TSSOP | PW | 14 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 105 | LV04AT | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN74LV04A-Q1:



PACKAGE OPTION ADDENDUM

10-Dec-2020

Enhanced Product: SN74LV04A-EP

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Enhanced Product Supports Defense, Aerospace and Medical Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Jun-2022

TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width |
|----|---|
| В0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | _ | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|-------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| SN74LV04ATPWRG4Q1 | TSSOP | PW | 14 | 2000 | 330.0 | 12.4 | 6.9 | 5.6 | 1.6 | 8.0 | 12.0 | Q1 |

PACKAGE MATERIALS INFORMATION

www.ti.com 3-Jun-2022



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74LV04ATPWRG4Q1 | TSSOP | PW | 14 | 2000 | 356.0 | 356.0 | 35.0 |

PW (R-PDSO-G14)

PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M—1994.
- B. This drawing is subject to change without notice.
 - Sody length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.
- E. Falls within JEDEC MO-153



PW (R-PDSO-G14)

PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated