





东莞市祥如电子有限公司

SPECIFICATION FOR APPROVAL 样品承认书

| | | | | | |
|--|---------------------|-------------------|--|-------------|-----------|
| CUSTOMER(客户): | | | PAGE: 1 OF 1 | | |
| ITEM: XRCD75-103K | | | Customer' s ITEM: | | |
| Item 项目 | Spec. (mm) 规格值 | Typ. 实测值 | 1. MECHANICAL DIMENSIONS(外形尺寸):  | | |
| A | 7.8±0.3 | 7.56 | | | |
| B | 7.0±0.3 | 7.10 | | | |
| C | 5.0±0.3 | 5.10 | | | |
| D | | | | | |
| E | | | | | |
| F | | | | | |
| G | | | | | |
| H | 7.5 ref | | | | |
| I | 3.0 ref | | | | |
| J | 2.0 ref | | | | |
| Marking(印字): " 103" | | | | | |
| 2. ELECTRICAL CHARACTERISTICS(电特性要求): | | | | | |
| ITEM(项目) | Specifications(规格值) | Typ.(参考 值) | Test equipments(测试仪器) | | |
| L | 10MH ±10% | 10.0MH | VR 102 LCR METER. | | |
| Test Freq. | @1kHz 0.25V | | VR 102 LCR METER. | | |
| DCR | 0.07 OHM MAX | 0.07OHM | VR 102 LCR METER. | | |
| R. Currentt | 0.15A | | | | |
| Ope. Temp. | -20°C TO 80°C | | HC-D3M TEMP. & HUMIDITY CHAMBER | | |
| Other1 | 产品需印字 "103' " | | | | |
| Other1 | 包装方式: 编带 | | | | |
| ITEM: XRCD75-103K | | | Customer' s ITEM: | | |
| DATE(测试日期): 2022-05-16 | | |  | | |
| QUANTITY(数量): 10 PCS | | | | | |
| TEST Freq. (测试频率): L:@1kHz 0.25V | | | | | |
| WIRE(铜线): 0.07mm | | URNS (圈数): 15.5Ts | | | |
| TEMP(温度): 25.5 °C | | HUMI.(湿度): 55 % | | | |
| CUSTOMER APPROVED(客户确认栏) | | | APPROVED(确认) | CHECKED(检查) | DRQWN(制图) |
| | | | 陈勇 | 李少辉 | 黄永强 |
| ISSUED DATE(出版日期): 2022-05-16 版次: 1.0 | | | | | |

检测报告



RoHS

ISSUED NO : 12060802

| | | | | | | | | | |
|--|--|------------|------------------------|-----------------------------|-----------|--|--|-----------------------------------|-------|
| NO: GKDZJWPSZ10056 | | | | | | | | | |
| Customer | | | Date | | | 2022/5/16 | | Part No | 1page |
| Item | | | Quantity | | | 10PCS | | Pages | P1 |
| Winding | | | ⊙ 0.07mm*498.0TS (REF) | | | | | Temp | 28°C |
| COLL DATE | | Q0= | | CO= | | Humidint | | 50% | |
| Electrical Characteristics | | | | Dimension (Unit:mm) | | | | | |
| ITEM | L(OA) | DCR | IDC | A | B | C | | | |
| SPEC | 10MH ±10% | 32Ω MAX | 0.15A | 7.8 ±20% | 7 ±20% | 5.00 ±20% | | | |
| 测试频率 | 1KHZ/0.25V | | | | | | | | |
| 1 | 10.20 | 28.00 | 0.14 | 7.55 | 7.12 | 5.06 | | | |
| 2 | 10.30 | 29.00 | 0.13 | 7.53 | 7.13 | 5.03 | | | |
| 3 | 10.10 | 31.00 | 0.15 | 7.52 | 7.14 | 5.04 | | | |
| 4 | 9.80 | 31.00 | 0.14 | 7.53 | 7.16 | 5.06 | | | |
| 5 | 9.70 | 28.00 | 0.12 | 7.56 | 7.12 | 5.07 | | | |
| 6 | 9.80 | 29.00 | 0.16 | 7.62 | 7.15 | 5.02 | | | |
| 7 | 10.20 | 27.00 | 0.14 | 7.64 | 7.14 | 5.04 | | | |
| 8 | 10.30 | 28.00 | 0.13 | 7.63 | 7.13 | 5.08 | | | |
| 9 | 10.50 | 26.00 | 0.12 | 7.59 | 7.16 | 5.05 | | | |
| 10 | 10.20 | 27.00 | 0.14 | 7.57 | 7.14 | 5.05 | | | |
| X | 10.11 | 28.40 | 0.14 | 7.57 | 7.139 | 5.05 | | | |
| R | 1.17 | 0.01 | 0.08 | 0.04 | 0.04 | 0.03 | | | |
| Test Instruments | | | | | | | | | |
| 测试仪表: HM2792 <input checked="" type="checkbox"/> TH1772B <input checked="" type="checkbox"/> YD2511 <input checked="" type="checkbox"/> YD2775B <input checked="" type="checkbox"/> Marking 字朝电极任意一方 <input type="checkbox"/> 字朝顶极 <input type="checkbox"/> 字首朝进线 <input checked="" type="checkbox"/> 其它 <input type="checkbox"/> | | | | | | | | | |
| Aspect: | OK <input checked="" type="checkbox"/> | | | NO <input type="checkbox"/> | | | | | |
| Dimension: | OK <input checked="" type="checkbox"/> | | | NO <input type="checkbox"/> | | | | | |
| REMARK: | | | | | | INSPECTED | | CHECKED | |
| | | | | | | Accepted <input checked="" type="checkbox"/> | | Rejected <input type="checkbox"/> | |