

MOSFET Silicon N-Channel MOS**1. Applications**

Single-ended flyback or two-transistor forward topologies.
PC power, PD Adaptor, LCD & PDP TV and LED lighting.

**2. Features**






Low drain-source on-resistance: $R_{DS(ON)} = 4.2\text{m}\Omega$ (typ.)
Easy to control Gate switching
Enhancement mode: $V_{th} = 2.5$ to 3.5 V

**Table 1 Key Performance Parameters**

| Parameter | Value | Unit |
|----------------------|-------|------------------|
| $V_{DS} @ T_{j,max}$ | 85 | V |
| $R_{DS(on),max}$ | 5.2 | $\text{m}\Omega$ |
| $Q_{g,typ}$ | 68.4 | nC |
| $I_{D,pulse}$ | 480 | A |

3. Packaging and Internal Circuit

| Part Name | Package | Marking |
|------------|---------|------------|
| AUP052N085 | TO220 | AUP052N085 |
| AUB050N085 | TO263 | AUB050N085 |
| AUN045N085 | DFN5X6 | AUN045N085 |



Released

1 Maximum ratings

at $T_j = 25^\circ\text{C}$, unless otherwise specified

Table 2 Maximum ratings

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|--|----------------------|--------|------|------|------|--|
| | | Min. | Typ. | Max. | | |
| Continuous drain current ¹⁾ | I_D | | - | 119 | A | $T_C=25^\circ\text{C}$ |
| Continuous drain current | I_D | | - | 89 | A | $T_C=100^\circ\text{C}$ |
| Pulsed drain current ²⁾ | $I_{D,\text{pulse}}$ | - | - | 480 | A | $T_C=25^\circ\text{C}$ |
| Avalanche energy, single pulse | E_{AS} | - | - | 420 | mJ | $T_c=25^\circ\text{C}$, VDD=50V, I=41A, L=0.5mH, RG=25Ω |
| Avalanche current, single pulse | I_{AR} | - | - | 41 | A | $T_c=25^\circ\text{C}$, VDD=50V, L=0.5mH, RG=25Ω |
| Gate source voltage (static) | V_{GS} | -20 | - | 20 | V | static; |
| Power dissipation | P_{tot} | - | - | 183 | W | $T_C=25^\circ\text{C}$ |
| Storage temperature | T_{stg} | -55 | - | 150 | °C | |
| Operating junction temperature | T_j | -55 | - | 150 | °C | |
| Transconductance | GFS | - | 76 | - | S | VDS=5V IDS=50A |

¹⁾ Limited by $T_{j,max}$. Maximum Duty Cycle D = 0.50

²⁾ Pulse width t_p limited by $T_{j,max}$

³⁾ Identical low side and high side switch with identical RG

Released

2 Thermal characteristics

Thermal characteristics (TO220)

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|--|------------|--------|------|------|------|----------------------------------|
| | | Min. | Typ. | Max. | | |
| Thermal resistance, junction - case | R_{thJC} | - | - | 0.9 | °C/W | - |
| Thermal resistance, junction - ambient | R_{thJA} | - | - | 62 | °C/W | device on PCB, minimal footprint |

Thermal characteristics (TO263)

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|--|------------|--------|------|------|------|----------------------------------|
| | | Min. | Typ. | Max. | | |
| Thermal resistance, junction - case | R_{thJC} | - | - | 1.0 | °C/W | - |
| Thermal resistance, junction - ambient | R_{thJA} | - | - | 60 | °C/W | device on PCB, minimal footprint |

Thermal characteristics (DFN5X6)

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|--|------------|--------|------|------|------|----------------------------------|
| | | Min. | Typ. | Max. | | |
| Thermal resistance, junction - case | R_{thJC} | - | - | 1.3 | °C/W | - |
| Thermal resistance, junction - ambient | R_{thJA} | - | - | 50 | °C/W | device on PCB, minimal footprint |

3 Electrical characteristics

at $T_j=25^\circ\text{C}$, unless otherwise specified

Table 4 Static characteristics

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|----------------------------------|-----------------------------|--------|------|-----------|------------------|--|
| | | Min. | Typ. | Max. | | |
| Drain-source breakdown voltage | $V_{(\text{BR})\text{DSS}}$ | 85 | - | - | V | $V_{\text{GS}}=0\text{V}, I_{\text{D}}=250\mu\text{A}$ |
| Gate threshold voltage | $V_{(\text{GS})\text{th}}$ | 2.5 | | 3.5 | V | $V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=250\mu\text{A}$ |
| Zero gate voltage drain current | I_{DSS} | - | - | 1 | μA | $V_{\text{DS}}=85\text{V}, V_{\text{GS}}=0\text{V}, T_j=25^\circ\text{C}$ |
| Gate-source leakage current | I_{GSS} | - | - | ± 100 | nA | $V_{\text{GS}}=\pm 20\text{V}, V_{\text{DS}}=0\text{V}$ |
| Drain-source on-state resistance | $R_{\text{DS}(\text{on})}$ | - | 4.2 | 5.2 | $\text{m}\Omega$ | $V_{\text{GS}}=10\text{V}, I_{\text{D}}=20\text{A}, T_j=25^\circ\text{C}(\text{TO220})$ |
| Drain-source on-state resistance | $R_{\text{DS}(\text{on})}$ | - | 3.9 | 5.0 | $\text{m}\Omega$ | $V_{\text{GS}}=10\text{V}, I_{\text{D}}=20\text{A}, T_j=25^\circ\text{C}(\text{TO263})$ |
| Drain-source on-state resistance | $R_{\text{DS}(\text{on})}$ | - | 3.7 | 4.5 | $\text{m}\Omega$ | $V_{\text{GS}}=10\text{V}, I_{\text{D}}=20\text{A}, T_j=25^\circ\text{C}(\text{DFN5X6})$ |
| Gate resistance (Intrinsic) | R_{G} | - | 1.8 | - | Ω | $f=1\text{MHz}$, open drain |

Table 5 Dynamic characteristics

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|------------------------------|----------------------------|--------|------|------|------|---|
| | | Min. | Typ. | Max. | | |
| Input capacitance | C_{iss} | - | 4587 | - | pF | $V_{\text{GS}}=0\text{V}, V_{\text{DS}}=40\text{V}, f=1\text{MHz}$ |
| Output capacitance | C_{oss} | - | 824 | - | pF | $V_{\text{GS}}=0\text{V}, V_{\text{DS}}=40\text{V}, f=1\text{MHz}$ |
| Reverse transfer capacitance | C_{rss} | - | 5.5 | - | pF | $V_{\text{GS}}=0\text{V}, V_{\text{DS}}=40\text{V}, f=0.7\text{MHz}$ |
| Turn-on delay time | $t_{\text{d}(\text{on})}$ | - | 22 | - | ns | $V_{\text{DD}}=40\text{V}, V_{\text{GS}}=10\text{V}, I_{\text{D}}=56\text{A}, R_{\text{G}}=1.6\Omega$ |
| Rise time | t_{r} | - | 33.6 | - | ns | $V_{\text{DD}}=40\text{V}, V_{\text{GS}}=10\text{V}, I_{\text{D}}=56\text{A}, R_{\text{G}}=1.6\Omega$ |
| Turn-off delay time | $t_{\text{d}(\text{off})}$ | - | 34.6 | - | ns | $V_{\text{DD}}=40\text{V}, V_{\text{GS}}=10\text{V}, I_{\text{D}}=56\text{A}, R_{\text{G}}=1.6\Omega$ |
| Fall time | t_{f} | - | 17.4 | - | ns | $V_{\text{DD}}=40\text{V}, V_{\text{GS}}=10\text{V}, I_{\text{D}}=56\text{A}, R_{\text{G}}=1.6\Omega$ |

Table 6 Gate charge characteristics

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|-----------------------|----------------------|--------|------|------|------|---|
| | | Min. | Typ. | Max. | | |
| Gate to source charge | Q_{gs} | - | 24.6 | - | nC | $V_{\text{DD}}=40\text{V}, I_{\text{D}}=56\text{A}, V_{\text{GS}}=0 \text{ to } 10\text{V}$ |
| Gate to drain charge | Q_{gd} | - | 15.5 | - | nC | $V_{\text{DD}}=40\text{V}, I_{\text{D}}=56\text{A}, V_{\text{GS}}=0 \text{ to } 10\text{V}$ |
| Gate charge total | Q_{g} | - | 68.4 | - | nC | $V_{\text{DD}}=40\text{V}, I_{\text{D}}=56\text{A}, V_{\text{GS}}=0 \text{ to } 10\text{V}$ |
| Gate plateau voltage | V_{plateau} | - | 5.2 | - | V | $V_{\text{DD}}=40\text{V}, I_{\text{D}}=56\text{A}, V_{\text{GS}}=0 \text{ to } 10\text{V}$ |

Released

Table 7 Reverse diode characteristics

| Parameter | Symbol | Values | | | Unit | Note / Test Condition |
|-------------------------------|-----------|--------|------|------|------|--|
| | | Min. | Typ. | Max. | | |
| Diode forward voltage | V_{SD} | - | 0.7 | - | V | $V_{GS}=0V$, $I_F=1A$, $T_j=25^\circ C$ |
| Reverse recovery time | t_{rr} | - | 44 | - | ns | $V_R=40V$, $I_F=56A$, $di_F/dt=100A/\mu s$ |
| Reverse recovery charge | Q_{rr} | - | 42 | - | nC | $V_R=40V$, $I_F=56A$, $di_F/dt=100A/\mu s$ |
| Peak reverse recovery current | I_{rrm} | - | 1.9 | - | A | $V_R=40V$, $I_F=56A$, $di_F/dt=100A/\mu s$ |

Released

4. Electrical characteristics diagram













Diagram 7: Typ. Power Dissipation

Diagram 8: Typ. Drain Current De-rating

Diagram 9: Typ. Gate charge

Diagram 10: Typ. R_ds(on) vs Gate Voltage

Diagram 11: Typ. Maximum Safe Operating Area

Diagram 12: Single Pulse Power Rating, Junction-to-Case


Fig 13 : Max. Transient Thermal Impedance



5. Test Circuits

Table 8 Diode characteristics



| Test circuit for diode characteristics | Diode recovery waveform |
|--|--|
|  $R_{G1} = R_{G2}$ |  |

Table 9 Switching times






| Switching times test circuit for inductive load | Switching times waveform |
|--|---|
|  |  |

Table 10 Unclamped inductive load





| Unclamped inductive load test circuit | Unclamped inductive waveform |
|---|--|
|  |  |

6 Package Outlines




Outline PG-T0220

Outline PG-T0263 (JJW)



Released



| SYMBOLS | DIMENSION IN MM | | | DIMENSION IN INCHES | | |
|---------|-----------------|-------|-------|---------------------|-------|-------|
| | MIN | NOM | MAX | MIN | NOM | MAX |
| * A | 0.900 | 1.000 | 1.100 | 0.035 | 0.039 | 0.043 |
| A1 | 0.000 | --- | 0.050 | 0.000 | --- | 0.002 |
| b | 0.246 | 0.254 | 0.312 | 0.010 | 0.010 | 0.012 |
| * c | 0.310 | 0.410 | 0.510 | 0.012 | 0.016 | 0.020 |
| d | 1.27 BSC | | | 0.050 BSC | | |
| * D | 4.950 | 5.050 | 5.150 | 0.195 | 0.199 | 0.203 |
| D1 | 4.000 | 4.100 | 4.200 | 0.157 | 0.161 | 0.165 |
| * D2 | --- | --- | 0.125 | --- | --- | 0.005 |
| e | 0.62 BSC | | | 0.024 BSC | | |
| * E | 5.500 | 5.600 | 5.700 | 0.217 | 0.220 | 0.224 |
| * E1 | 6.050 | 6.150 | 6.250 | 0.238 | 0.242 | 0.246 |
| E2 | 3.425 | 3.525 | 3.625 | 0.135 | 0.139 | 0.143 |
| E3 | 0.150 | 0.250 | 0.350 | 0.006 | 0.010 | 0.014 |
| * F4 | 0.175 | 0.275 | 0.375 | 0.007 | 0.011 | 0.015 |
| F | - | - | 0.100 | - | - | 0.004 |
| * L | 0.500 | 0.600 | 0.700 | 0.02 | 0.02 | 0.03 |
| L1 | 0.600 | 0.700 | 0.800 | 0.02 | 0.03 | 0.03 |

NOTE:

1. PACKAGE BODY SIZE EXCLUDE MOLD FLASH AND GATE BURR.
MOLD FLASH AT THE NON-LEAD SIDES SHOULD BE LESS THAN 5 MIL EACH SIDE.
2. CONTROLLING DIMENSION IS MILLIMETER, INCH FOR REFERENCE ONLY.

Outline PG-DFN5X6 (JJW)

Released

Revision History

| Revision | Date | Subjects (major changes since last revision) |
|----------|------------|--|
| 1.0 | 2021-11-10 | Preliminary version |
| 1.1 | 2021-11-16 | Updated Qrr |
| 1.2 | 2021-11-17 | Add gfs data |
| 1.3 | 2021-12-28 | Added Electrical characteristics diagram |
| 1.4 | 2022-1-10 | Added DFN5X6 package |

Released