

# 产品规格承认书

## Specification for approval

客户名称:

Customer: \_\_\_\_\_

产品名称:

塑胶型盒式微型保险丝

Product Name:

Plastic cartridge type micro fuse

规格型号:

Specification Type :

SST T1.6A 250V

客户料号:

Customer Part No. \_\_\_\_\_

供应商:

东莞市诚润电子科技有限公司

Supplier:

Dongguan Chevron Electronic Technology Co.,Ltd

供应商地址:

广东省东莞市厚街镇宝宏路鼎昊高新科技产业园 D 栋二楼

Supplier Address:

2nd FLOOR of D BUILDING ,No. 29 BAOHONG ROAD, DINGHAO HIGH-NEW TECHNOLOGY INDUSTRIAL PARK, HOUJIE 523961, GUANGDONG,CHINA

编制 Prepared	审核 Checked	批准 Approved
林雪莲	邓波	刘富强

承认 Signature	审核 Checked	批准 Approved

供方签章:

SUPPLIER:

日期: 2023.3.30

DATE:



需方签章:

CUSTOMER:

日期:

DATE:

### 1. 适用范围 / Scope of Application

本产品适用于各类电子设备电路的过流保护作用, 广泛应用于照明设备、电源设备以及适配器等领域。

This product is suitable for various kinds of electronic devices' circuit over current protection. Widely used in industrial of Lighting, Power supply and Adapter applications, etc.

### 2. 安规认证标准及编号 / Standards and Agency Approvals

2.1 执行标准: 遵循 UL248-1/14; IEC60127-1/3; GB/9364.1/3。


Standards: In accordance with UL248-1/14; IEC60127-1/3; GB/9364.1/3。


2.2 认证范围 Certification:

额定电压 Rated Voltage	安规标准 Agency	认证电流 Ampere Range	证书编号 Agency File Number
250v/300v/350v/400v	UL-CUL	100mA ~16A	E358589
250V	自我声明	1A/1.6A/2A/2.5A/3.15A/4A/5A/6.3A	2020980207000081
250V	CQC	1A/1.6A/2A/2.5A/3.15A/4A/5A/6.3A	CQC2019010207260848
250V	PSE	1A/1.6A/2A/2.5A/3.15A/4A/5A/6.3A	PSE20021776/20021775
250V	VDE	1A/1.6A/2A/2.5A/3.15A/4A/5A/6.3A	40052042
250V	KC	1A/1.6A/2A/2.5A/3.15A/4A/5A/6.3A	Su05044-20001/2

### 3. 结构及尺寸 / Dimensions and Structure

单位: 毫米 / Unit: mm



 <b>CHEVRON</b> 誠潤電子	产品规格书	文件版本 Version	A/4
		文件编号 No	FMQ-GC-011-108
	型号 Type: SST	安规类型 Approved	IEC/GB

材料明细 / Material Details


编号 NO.	零件名称 Part Name	材质 Material
①	外壳 Cap	尼龙料 PA66
②	内芯 Fuse Base	尼龙料 PA66
③	熔丝 Fuse element	合金 Alloy
④	引线 Lead Wire	铜镀锡 Copper tin plating

4. 产品标示 / Product Marking

保险丝两端铜帽或外壳上需有下列标示。

The fuses cap shall have the following markings.







示例 Example:



1. 诚润工厂标识/Chevlon Logo
2. 产品型号名称/Product Type Name
3. 电器特性符号/ Electrical Characteristic symbol
4. 额定电流/Rated Current(A): A 或 or mA
5. 额定电压/Rated Voltage(V)
6. 认证符号/Approval Marks

**注意 / Note:** 对于标示的大小和位置没有规定。  
 Size and position of the markings shall not be provided

**5. 产品特性/Product Characteristic**

零件编号	Rated Current	Rated Voltage	Maximum Voltage drop	Breaking Capacity	I2T A2s	Safety Approvals																		
																								
SST0100	100mA	250V 300V 350v 400v	350	UL 120A@2 50A	0.06	●	○	○	○	○	○													
SST0125	125mA		300		100A@3 00V	0.08	●	○	○	○	○	○												
SST0160	160mA		280			100A@3 00V	0.1	●	○	○	○	○	○											
SST0200	200mA		260				50V	0.2	●	○	○	○	○	○										
SST0250	250mA		240					50A@40 0V	0.3	●	○	○	○	○	○									
SST0315	315mA		220						100A@3 00V	0.40	●	○	○	○	○	○								
SST0400	400mA		200							50V	0.50	●	○	○	○	○	○							
SST0500	500mA		190								50A@40 0V	0.9	●	○	○	○	○	○						
SST0630	630mA		180									100A@3 00V	1.2	●	○	○	○	○	○					
SST0750	750mA		170										50V	2.3	●	○	○	○	○	○				
SST0800	800mA		160											50A@40 0V	3.2	●	○	○	○	○	○			
SST1100	1.0A		140												CCC 35A@25 0Vac 10In@2 50Vac VDE 35A@25 0V 35A@30 0V	5.8	●	●	●	●	●	●		
SST1125	1.25A		130	14.5	12.8	●	○	○	○	○	○													
SST1160	1.6A		120		21.9	14.5	●	●	●	●	●	●												
SST1200	2.0A		100			42.6	21.9	●	●	●	●	●	●											
SST1250	2.5A		100				72.0	42.6	●	●	●	●	●	●										
SST1315	3.15A		100					83.2	72.0	●	●	●	●	●		●								
SST1400	4.0A		100						148	83.2	●	●	●	●		●	●							
SST1500	5.0A		100							195	148	●	●	●		●	●	●						
SST1630	6.3A		100								215	195	●	●		●	●	●	●					
SST1800	8.0A		120									250	215	●		○	○	○	○	○				
SST2100	10.0A	180	272										250	●		○	○	○	○	○				
SST2120	12.0A	180											280	272		●	○	○	○	○	○			
SST2125	12.5A	180												300		280	●	○	○	○	○	○		
SST2150	15.0A	140														/	300	●	○	○	○	○	○	
SST2160	16.0A	140															/	/	●	○	○	○	○	○

○pending ●approved

## 6. 外观及形状 / Appearances and Configuration

6.1 外观不应出现显著的污点、裂纹，标识应该容易辨识。

There shall not be any remarkable stain and crack on the appearances, markings shall be easily legible.

6.2 形状：带直线引脚方形保险丝。

Configuration: Square fuse with straight pin

## 7. 产品特性 / Product Characteristics

7.1 引脚拉力强度 / Lead Pull Strength

10 牛顿 10±1 秒 / 10N for 10±1 Seconds

7.2 引脚推力强度 / Lead Thrust Strength

2 牛顿 10±1 秒 / 2N for 10±1 Seconds

7.3 可焊性 / Solder ability

波峰焊/Wave : 260°C, ≤3s;

烙铁焊/Soldering Iron: 350±10°C, ≤3s.

7.4 耐焊接热 / Soldering Heat Resistance

波峰焊/Wave : 260°C, <10s;

烙铁焊/Soldering Iron: 350°C, <2s.

## 8 电气特性 / Electrical Characteristics

8.1 实验条件: Test Condition

所有测试环境温度为 25±5°C。

All electrical test is to be conducted with the ambient air at a temperature of 25±5°C.

8.2 分断能力 / Interrupting Rating:

参考 5 / REF 5

The insulation resistance value of fuse is greater than 0.1MΩ after breaking capacity testing.

8.3 温度上升试验 / Rising Temperature Test:

温度上升试验: 通 1.5 倍额定电流 15 分钟, 然后每隔 15 分钟增加 0.1 倍额定电流。测得熔

断体断开时任何部位的温升不得超过  $135^{\circ}\text{C}$ ，周围环境温度为  $25 \pm 5^{\circ}\text{C}$ 。


Under the ambient temperature of  $25 \pm 5^{\circ}\text{C}$ , through 1.5 times the rated current for 15 minutes, then every 15 minutes, add an increase of 0.1 times the rated current. When operates, the temperature rise in any part of fuse should not exceed  $135^{\circ}\text{C}$ . Ambient Temperature is  $25 \pm 5^{\circ}\text{C}$ .

Rising temperature= The surface temperature-Ambient temperature

#### 8.4 熔断时限 / Opening Time

额定电流的% % of Ampere Rating	熔断时间 Opening Time
210%	$T < 2\text{min}$
275%	$400\text{ms} < T < 10\text{s}$
400%	$150\text{ms} < T < 3\text{s}$
1000%	$20\text{ms} < T < 150\text{ms}$

#### 8.5 平均时间电流曲线图 / Average Time Current Curves



## 9 环境特性 / Environmental Characteristic

### 9.1 使用温度范围 / Operating Temperature

-55℃~+125℃。

### 9.2 保存条件 Stock Condition


温度在 10℃~60℃，相对湿度≤75%平均可以存放 3 年。

Can be stored for 3 years under tight seal condition at temperature of 10℃~60℃, relative humidity ≤75%

### 9.3 若操作环境温度超出 25±5℃范围，在选用保险丝规格时，需考虑操作环境温度对保险丝的影响，请参照如下：温度-电流曲线图。

When choosing the fuse's specification, if the operating environmental temperature beyond the scope from 20~30℃, engineer should consider the environmental temperature's affection to fuses. Please refer: Temperature Rerating Curve:

### Temperature Rerating Curve



#### 9.4 建议焊接参数 / Recommended Soldering Parameters

##### A. 波峰焊参数 / Wave Parameters:

锡炉温度 / Solder Pot Temperature:  $260^{\circ}\text{C} \pm 10^{\circ}\text{C}$

焊接时间 / Solder Dwell Time: 2~5s

##### B. 手工焊参数 / Hand-Solder Parameters:

烙铁温度 / Solder Iron Temperature:  $350 \pm 5^{\circ}\text{C}$

焊接时间 / Heating Time: 3s Max

### 10 包装 / Packaging

#### 10.1 包装袋/盒印明下列标示: / The following items indicated on the label:

产品料号、额定(电压、电流)、分断类型及安规名称。

Catalog number, ratings (voltage, current), interrupting type and safety mark.


包装材料均符合 ROHS/REACH/HF 的环保要求, 且包装材料不会和零件发生化学反应, 造成不良。

The packing material conforms to ROHS/REACH/HF environmental protection request. And the packing materials will not have the chemical reaction with the components.

#### 10.2 包装数量 / Packing Quantity

每 1 个内盒 1000pcs / 1000pcs in per inner box;

散装根据客户要求 / Bulk according to customer requirements






二：编带产品外箱尺寸

图一

图二

图三



图三：短引脚散装包装尺寸

图四：短引脚外箱尺寸

附件 I: 安规证书和 SGS 证书 / Appendix I: Safety approval certificates and SGS approval