

UG4KB05-UG4KB100/G

Single Phase 4.0Amp Glass passivated Bridge Rectifiers


Features

- The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- · Idea for printed circuit board
- · Glass passivated Junction chip
- · Low reverse leakage
- · High forward surge current capability
- High temperature soldering guaranteed 250 °C/10 seconds at terminals
- The G suffix is uses for photoresist chip, otherwise it is a knife scraping chip

Description

- Case:Molded plastic body
- Terminals:Solder plated, solderable per MIL-STD-750,Method 2026
- · Polarity:Polarity symbol marking on body
- · Mounting Position: Any

Mechanical Data



Maximum Ratings And Electrical Characteristics (@T_A=25°C unless otherwise noted)

Symbol	Parameter	UG4K	UG4K	UG4K	UG4K	UG4K	UG4K	UG4K	Unit
		B05	B10	B20	B40	B60	B80	B100	
V_{RRM}	Maximum repetitive peak reverse voltage	50	100	200	400	600	800	1000	V
V _{RMS}	Maximum RMS voltage	35	70	140	280	420	560	700	V
V_{DC}	Maximum DC blocking voltage	50	100	200	400	600	800	1000	V
I _{AV}	Maximum average forward	4.0							А
	rectified current with heatsink								
1	Peak forward surge current, 8.3ms single	120.0						Α	
I _{FSM}	half sine-wave	120.0							^
I _t ²	Rating for fusing (t=8.3ms, T _A =25°C)	59.76					A _S ²		
V _F	Maximum forward voltage at 4.0A	1.10				V			
I _R	Maximum DC reverse current@T _A =25°C	5.0							
	at rated DC blocking voltage @T _A =125°C	500						uA	
CJ	Typical junction capacitance (Note 1)	38.0					pF		
R_{qJA}	Typical thermal resistance	55.0					°C/W		
T _J T _{STG}	Operating junction ,storage temperature range	-55 to +150				°C			

Revision: 2022-Jan-1

Note:(1)Measured at 1MHz and applied reverse voltage of 4.0V D.C.

BORN SEMICONDUCTOR , INC. ALL RIGHT RESERVED





UG4KB05-UG4KB100/G

Revision: 2022-Jan-1

Single Phase 4.0Amp Glass passivated Bridge Rectifiers

Ratings And Characteristic Curves

Figure 1:DERATING CURVE OUTPUT RECTIFIED CUR-




Figure 2:MAXIMUM NON-REPETITIVE PEAK FOR-




Figure 3:YPICAL FORWARD VOLTAGE CHARACTER-





Figure 4:TYPICAL REVERSE LEAKAGE CHARACTER-






UG4KB05-UG4KB100/G

Revision: 2022-Jan-1

Single Phase 4.0Amp Glass passivated Bridge Rectifiers


Suggested Soldering Temperature Profile



Note:

- (1)Recommended reflow methods: IR , vapor phase oven, hot air oven, wave solder.
- (2)The device can be exposed to a maximum temperature of 265°C for 10 seconds.
- (3)Devices can be cleaned using standard industry methods and solvents.
- (4)If reflow temperatures exceed the recommended profile, devices may not meet the performance require ments.

Outline Drawing -D3K



SYMBOL	MILLIMETER					
STIVIBUL	MIN.	MAX.				
Α	14.2	14.7				
В	3.30	3.60				
С	10.2	10.6				
D	13.8	14.4				
Е	1.8	2.2				
F	6.65	7.25				
G	3.71	3.91				
Н	0.3	0.55				
I	1.22	1.42				
J	0.76	0.86				
0	1.8	2.4				
Р	3.0Ф	3.4Ф				