
SCAS725 - OCTOBER 2003

- Controlled Baseline
 - One Assembly/Test Site, One Fabrication Site
- Extended Temperature Performance of -55°C to 125°C
- Enhanced Diminishing Manufacturing Sources (DMS) Support
- Enhanced Product-Change Notification
- Qualification Pedigree[†]
- 2-V to 6-V V_{CC} Operation
- Inputs Accept Voltages to 6 V
- † Component qualification in accordance with JEDEC and industry standards to ensure reliable operation over an extended temperature range. This includes, but is not limited to, Highly Accelerated Stress Test (HAST) or biased 85/85, temperature cycle, autoclave or unbiased HAST, electromigration, bond intermetallic life, and mold compound life. Such qualification testing should not be viewed as justifying use of this component beyond specified performance and environmental limits.

- Max t_{pd} of 9.5 ns at 5 V
- 3-State Noninverting Outputs Drive Bus Lines Directly
- Full Parallel Access for Loading



description/ordering information

This 8-bit latch features 3-state outputs designed specifically for driving highly capacitive or relatively low-impedance loads. The device is particularly suitable for implementing buffer registers, I/O ports, bidirectional bus drivers, and working registers.

The eight latches are D-type transparent latches. When the latch-enable (LE) input is high, the Q outputs follow the data (D) inputs. When LE is taken low, the Q outputs are latched at the logic levels set up at the D inputs.

A buffered output-enable (\overline{OE}) input can be used to place the eight outputs in either a normal logic state (high or low logic levels) or the high-impedance state. In the high-impedance state, the outputs neither load nor drive the bus lines significantly. The high-impedance state and increased drive provide the capability to drive bus lines in bus-organized systems without need for interface or pullup components.

OE does not affect the internal operations of the latches. Old data can be retained or new data can be entered while the outputs are in the high-impedance state.

To ensure the high-impedance state during power up or power down, \overline{OE} should be tied to V_{CC} through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

ORDERING INFORMATION

TA	PACKAGE	E‡	ORDERABLE PART NUMBER	TOP-SIDE MARKING
-55°C to 125°C	SOIC - DW	Tape and reel	SN74AC373MDWREP	SAC373MEP

[‡] Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.




SCAS725 - OCTOBER 2003

FUNCTION TABLE (each latch)

	INPUTS	OUTPUT	
OE	LE	D	Q
L	Н	Н	Н
L	Н	L	L
L	L	Χ	Q_0
Н	X	Χ	Z

logic diagram (positive logic)



To Seven Other Channels

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Supply voltage range, V _{CC}	
Input voltage range, V _I (see Note 1)	\dots -0.5 V to V _{CC} + 0.5 V
Output voltage range, V _O (see Note 1)	\dots -0.5 V to V _{CC} + 0.5 V
Input clamp current, I_{IK} ($V_I < 0$ or $V_I > V_{CC}$)	±20 mA
Output clamp current, I _{OK} (V _O < 0 or V _O > V _{CC)}	±20 mA
Continuous output current, $I_O(V_O = 0 \text{ to } V_{CC})$	
Continuous current through V _{CC} or GND	±200 mA
Package thermal impedance, θ_{JA} (see Note 2)	58°C/W
Storage temperature range, T _{stg} (see Note 3)	–65°C to 150°C

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.
 - 2. The package thermal impedance is calculated in accordance with JESD 51-7.
 - 3. Long-term high-temperature storage and/or extended use at maximum recommended operating conditions may result in a reduction of overall device life. See http://www.ti.com/ep_quality for additional information on enhanced plastic packaging.



recommended operating conditions (see Note 4)

			MIN	MAX	UNIT
Vcc	Supply voltage		2	6	V
		V _{CC} = 3 V	2.1		
ViH	High-level input voltage	V _{CC} = 4.5 V	3.15		V
		V _{CC} = 5.5 V	3.85		
		V _{CC} = 3 V		0.9	
VIL	Low-level input voltage	$V_{CC} = 4.5V$		1.35	V
		V _{CC} = 5.5 V		1.65	
VI	Input voltage		0	V_{CC}	٧
VO	Output voltage		0	VCC	V
		V _{CC} = 3 V		-12	
ЮН	High-level output current	$V_{CC} = 4.5 \text{ V}$		-24	mA
		$V_{CC} = 5.5 \text{ V}$		-24	
		V _{CC} = 3 V		12	
lOL	Low-level output current	$V_{CC} = 4.5 \text{ V}$		24	mA
		$V_{CC} = 5.5 \text{ V}$		24	
Δt/Δν	Input transition rise or fall rate			8	ns/V
TA	Operating free-air temperature		-55	125	°C

NOTE 4: All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	TEGT COMPLETIONS	.,	T,	_Δ = 25°C	;						
PARAMETER	TEST CONDITIONS	VCC	MIN	TYP	MAX	MIN	MAX	UNIT			
		3 V	2.9			2.9					
	I _{OH} = -50 μA	4.5 V	4.4			4.4					
V		5.5 V	5.4			5.4		V			
VOH	$I_{OH} = -12 \text{ mA}$	3 V	2.56			2.4		V			
	Jan. 24 m A	4.5 V	3.86			3.7]			
	I _{OH} = -24 mA	5.5 V	4.86			4.7					
		3 V			0.1		0.1				
	$I_{OL} = 50 \mu A$	4.5 V			0.1		0.1				
.,		5.5 V			0.1		0.1	- v			
V _{OL}	I _{OL} = 12 mA	3 V			0.36		0.5	V			
		4.5 V			0.36		0.5				
	I _{OL} = 24 mA	5.5 V			0.36		0.5				
ΙĮ	$V_I = V_{CC}$ or GND	5.5 V			±0.1		±1	μΑ			
loz	$V_O = V_{CC}$ or GND	5.5 V			±0.25		±5	μΑ			
Icc	$V_I = V_{CC}$ or GND, $I_O = 0$	5.5 V			4		80	μΑ			
Ci	$V_I = V_{CC}$ or GND	5 V		4.5				pF			

SN74AC373-EP OCTAL D-TYPE TRANSPARENT LATCH WITH 3-STATE OUTPUTS

SCAS725 - OCTOBER 2003

timing requirements over recommended operating free-air temperature range, V_{CC} = 3.3 V \pm 0.3 V (unless otherwise noted) (see Figure 1)

		$T_A = 2$	25°C	MIN		
		MIN	MIN MAX		MAX	UNIT
t _W	Pulse duration, LE high	5.5		6.5		ns
t _{su}	Setup time, data before LE↓	5.5		6.5		ns
t _h	Hold time, data after LE↓	1		1	·	ns

timing requirements over recommended operating free-air temperature range, V_{CC} = 5 V \pm 0.5 V (unless otherwise noted) (see Figure 1)

		T _A = 2	25°C	MIN	MAX	UNIT
		MIN	MIN MAX		WAX	UNII
t _W	Pulse duration, LE high	4		5		ns
t _{su}	Setup time, data before LE↓	4		5		ns
th	Hold time, data after LE↓	1		1		ns

switching characteristics over recommended operating free-air temperature range, V_{CC} = 3.3 V \pm 0.3 V (unless otherwise noted) (see Figure 1)

DADAMETED	ТО	то	T,	գ = 25°C	;	BAINI	MAY	
PARAMETER	(INPUT)	(OUTPUT)	MIN TYP MAX		MIN	MAX	UNIT	
^t PLH	ı	•	1.5	10	13.5	1	16.5	
^t PHL	D	Q	1.5	9.5	13.0	1	16	ns
^t PLH	LE	•	1.5	10	13.5	1	16.5	20
^t PHL		Q	1.5	9.5	12.5	1	15	ns
^t PZH	ŌĒ	•	1.5	9	11.5	1	14	
t _{PZL}	- OE	DE Q	1.5	8.5	11.5	1	13.5	ns
^t PHZ	ŌĒ	Q	1.5	10	12.5	1	16	ne
tPLZ	ÜE	OE Q		8	11.5	1	13	ns

switching characteristics over recommended operating free-air temperature range, V_{CC} = 5 V \pm 0.5 V (unless otherwise noted) (see Figure 1)

DADAMETED	то	то	T,	ղ = 25°C	;		MAY	
PARAMETER	(INPUT)	(OUTPUT)	MIN TYP MAX		MAX	MIN	MAX	UNIT
t _{PLH}	D	•	1.5	7	9.5	1	11.5	20
^t PHL		Q	1.5	7	9.5	1	11.5	ns
^t PLH	LE	0	1.5	7.5	9.5	1	12	20
^t PHL		LE Q	1.5	7	9.5	1	11	ns
^t PZH	<u>OE</u>	•	1.5	7	8.5	1	10.5	
^t PZL	OE	Q	1.5	6.5	8.5	1	10	ns
^t PHZ	ŌĒ	Q	1.5	8	11	1	13.5	ne
t _{PLZ}		3	1.5	6.5	8.5	1	10.5	ns


operating characteristics, V_{CC} = 5 V, T_A = 25°C

	PARAMETER	TEST CONDITIONS	TYP	UNIT
C _{pd}	Power dissipation capacitance	$C_L = 50 \text{ pF}, \qquad f = 1 \text{ MHz}$	40	pF



SCAS725 - OCTOBER 2003

PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_L includes probe and jig capacitance.

VOLTAGE WAVEFORMS

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, $Z_O = 50 \,\Omega$, $t_f \leq 2.5 \,$ ns.

(see Note B)

D. The outputs are measured one at a time with one input transition per measurement.

 v_{OL}

Figure 1. Load Circuit and Voltage Waveforms

≈0 V

VOLTAGE WAVEFORMS



PACKAGE OPTION ADDENDUM

10-Dec-2020

PACKAGING INFORMATION

www.ti.com

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
SN74AC373MDWREP	ACTIVE	SOIC	DW	20	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	SAC373MEP	Samples
V62/04621-01XE	ACTIVE	SOIC	DW	20	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	SAC373MEP	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



PACKAGE OPTION ADDENDUM

10-Dec-2020

OTHER QUALIFIED VERSIONS OF SN74AC373-EP:

• Military: SN54AC373

NOTE: Qualified Version Definitions:

• Catalog - TI's standard catalog product

• Military - QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 4-Mar-2013

TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
	Dimension designed to accommodate the component length
	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74AC373MDWREP	SOIC	DW	20	2000	330.0	24.4	10.8	13.3	2.7	12.0	24.0	Q1

www.ti.com 4-Mar-2013



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
SN74AC373MDWREP	SOIC	DW	20	2000	367.0	367.0	45.0	

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated