

SEA & LAND ELECTRONIC CORP. WWW.SEALAND-PPTC.COM

ALPHA-TOP TECHNOLOGY CORP.

APPROVAL SHEET

MODEL NO.:	SMD700L-13.2V

CUSTOMER'S APPROVAL:

CUSTOMER:

AUTHORIZED SIGNATURE/STAMP:

DATE

MANUFACTURER: HEAD OFFICE: 13F.,No.120-10,Sec.3,Zhongshan Rd.,Zhonghe Dist.,New Taipei City 23544,Taiwan Tel: 886-2-8221-2567 Fax:882-2-2225-7268 E-mail:service@chipfast.com.tw China Branch: Factory Building B)Shuangpeng,Weibu Village, Qiuchang Town, Huiyang District, Huizhou City, Guangdong Province, P.R.C.) Tel: 86-752-3562001 Fax:86-752-3558696 E-mail:service@atpptc.com

Submitted by:	Chen
Approved by:	YC Lin
DATE:	24-Dec-21

SEA & LAND ELECTRONIC CORP.



SMD700L-13.2V

Features
Surface Mount Devices
Lead free device
Size 7.5*5.5 mm 0.29*0.20 inch
Surface Mount packaging
for automated assembly

Applications Almost anywhere there is a low voltage power supply, up to 60V and a load to be protected, including: Computer mother board, Modem. Telecommunication equipments.

Alpha-Top (Sea & Land Alliance)

Performance Specification											
Model	V _{max}	max	I _{hold}	I _{trip}	Pd	Maxi Time 1	mum Го Trip	Resis	stance	Agency	Approval
Woder			@25°C	@25°C	Тур.	Current	Time	Ri min	R1 _{max}	UL	TUV
	(Vdc)	(A)	(A)	(A)	(W)	(A)	(Sec)	(Ω)	(Ω)		
SMD700L-13.2V	13.2	50	7.00	14.00	2.2	35.0	2.0	0.002	0.018		
Ihold = Hold Current.	Maximum cui	rrent device w	ill not trip in 2	5°C still air.							
Itrip = Trip Current. N	linimum curre	ent at which th	ne device will a	always trip in	25°C still air.						
Vmax = Maximum ope	rating voltage	e device can v	vithstand with	out damage a	at rated curre	nt (Imax).					
Imax = Maximum fau	Imax = Maximum fault current device can withstand without damage at rated voltage (Vmax).										
Pd = Power dissipat	Pd = Power dissipation when device is in the tripped state in 25°C still air environment at rated voltage.										
Rimin/max = Minimum/Maximum device resistance prior to tripping at 25°C.											
R1max = Maximum de	R1max = Maximum device resistance is measured one hour post reflow.										
CAUTION : Operation I	peyond the sp	pecified rating	s may result i	n damage and	d possible are	cing and flame).				

Environmental Specifications

Test	Conditions	Resistance change				
Passive aging	+85°C, 1000 hrs.	±5% typical				
Humidity aging	+85°C, 85% R.H. , 168 hours	±5% typical				
Thermal shock	+85°C to -40°C, 20 times	±33% typical				
Resistance to solvent	MIL-STD-202, Method 215	No change				
Vibration	MIL-STD-202, Method 201	No change				
Ambient operating conditions : - 40 °C to +85 °C						
Maximum surface temperature of the device in the tripped state is 125 °C						
In case of special use, please contact our engineer						

Agency Approvals :

Regulation/Standard:



2015/863/EU

EN14582

Ihold Versus Temperate	ure								
Model		Ν	/laximum amb	pient operating	g temperature	(T _{mao}) vs. ho	ld current (I _{hol}	d)	
wouer	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
SMD700L-13.2V	9.50	8.70	7.90	7.00	5.85	5.25	5.40	4.80	3.95




SMD700L-13.2V


Construction And Dimension (Unit:mm)


Model		A		В		C	D	E
laiodei	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Min.
SMD700L-13.2V	6.73	7.98	4.80	5.44	0.60	1.30	0.30	0.30

Dimensions & Marking



 α = Trademark 260 = Hold current





Termination Pad Characteristics Terminal pad materials :


Terminal pad solderability :

Tin-plated Nickel-Copper

Meets EIA specification RS186-9E and ANSI/J-STD-002 Category 3.

Rework

Use standard industry practices, the removal device must be replaced with a fresh one.



ᡗ warning:

Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.

PPTC are intended for protection against accessional over current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated. Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.


Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC. Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.

Contaminator of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices. PPTC SMD can be cleaned by standard methods. Requests that customers comply with our recommended solder pad layouts and recommended reflow profile. Improper board layouts or reflow profile could negatively impact solderability performance of

our devices.



SMD700L-13.2V




- Recommended reflow methods : IR, vapor phase oven, hot air oven. · Devices are not designed to be wave soldered to the bottom side
- of the board. Recommended maximum paste thickness is 0.25 mm (0.010 inch).
- Devices can be cleaned using standard method and solvents.
- Note : If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.


Tape And Reel Specifications (mm)

Governing Specifications	EIA 481-2
W	16.0 ± 0.3
Po	4.0 ± 0.10
P ₁	8.0 ± 0.10
P ₂	2.0 ± 0.05
A ₀	5.70 ± 0.10
B ₀	8.00 ± 0.10
B₁max.	12.1
D ₀	1.5 + 0.1, -0
F	7.5 ± 0.05
D ₀ F E ₁	1.75 ± 0.10
E ₂ min.	14.25
Tmax.	0.6
T₁max.	0.1
K ₀	0.80 ± 0.1
Leader min.	390
Trailer min.	160
Reel Dimensions	
A max.	178
N min.	60
W ₁	16.4 + 2.0, -0.0
W ₂ max.	22.4

EIA Tape Component Dimensions



EIA Reel Dimensions



- Storage And Handling Storage conditions : 40°C max, 70% R.H.
- Devices may not meet specified performance
- if storage conditions are exceeded.

Order Information		Packaging			
SMD	400L-13.2V	Tape & Reel Quantity			
Product name	Hold				
Size 7555 mm /2920 inch	Current	1500 pcs/reel			
SMD : surface mount device	7.00A				
T 0 1 1 1 E 14 (01.1					

Tape & reel packaging per EIA481-1

Labeling Information

Sea & Land Electronic Corp.	
HF Pb RoHS	
Model:	
Part no.:	
Spec.:	
Lot no.:	
Q'ty:	
會儲, 率封! 溫度, 18~33℃/濕度, 30~60% A	