




RECOMMEND P.C.B LAYOUT  
(General tolerance ±0.05)

- ### 规格 Specification
- 1.材料 MATERIAL:
- 1.1 绝缘材料 Insulator:High Temperature Thermoplastic. LCP SZ6505HF black UL94V-0.
  - 1.2 端子 Terminal:Phosphor Bronze(C5210-H.T=0.15mm)
  - 1.3 外壳 Shell:5US301-3/4H T=0.10mm
  - 1.4 弹簧 Spring: SUS301 L=9.80mm
  - 1.5 滑块 Slider: PPA black
  - 1.6 拉杆 Drawbar : SUS304-H.L=3.85mm
- 2.电镀 Plating:
- 2.1 端子 Terminal: Plated 80u/min Ni Overall  
Plated 1u"min Au Selective contact area  
Plated 1u"min Au over Ni on solder area
- 2.2 外壳 Shell:Plated 1u"min Au overll 50u"min Ni
- 3.性能 Property:
- 3.1 额定电流 Current Rating :0.5A AC/DC max
  - 3.2 额定电压 Voltage Rating :12V AC/DC
  - 3.3 环境温度 Ambient Temperature Range :-20℃+60℃
  - 3.4 环境湿度 Ambient Humidity Range :95% R.H. Max.
  - 3.5 接触电阻 Contact Resistance:100mΩ max.
  - 3.6 绝缘电阻 Insulation Resistance:1000MΩ min/500VDC
  - 3.7 耐久性 Durability:5000 cycles



PIN NO.	PIN ASSIGNMENT
P1	DAT2
P2	CD/DAT3
P3	CMD
P4	VDD
P5	CLK
P6	VSS
P7	DAT0
P8	DAT1

new		2015/5/3	A	瀚源	
ECN BO.		DESCRIPTION.	DATE.		REV.
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME TF-1151-2	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.2
			MODEL NAME TF-1151-2		X.x ±0.21
			3RD ANGLE PROJ	HanElectricity Co.,LTD	X.xx ±0.15
					ANGULAIR ±3
					FILE.NO.