

ALPHA-TOP TECHNOLOGY CORP.

APPROVAL SHEET

MODEL NO.:	nSMD075-16V	
CUSTOMER:		
CUSTOMER'S APPRO	/AL:	
AUTHORIZED SIGNAT	URE/STAMP:	
DATE		

MANUFACTURER:	
HEAD OFFICE:	
	13F.,No.120-10,Sec.3,Zhongshan Rd.,Zhonghe Dist.,New Taipei City 23544,Taiwan
	Tel: 886-2-8221-2567 Fax:882-2-2225-7268
	E-mail:service@chipfast.com.tw
China Branch:	
	Factory Building B)Shuangpeng,Weibu Village, Qiuchang Town,
	Huiyang District, Huizhou City, Guangdong Province, P.R.C.) Tel: 86-752-3562001
	Fax:86-752-3558696
	E-mail:service@atpptc.com
Submitted by:	Chen
Approved by:	
DATE:	22-Feb-22

SEA & LAND ELECTRONIC CORP.

ak al ah af az

Features Surface Mount Devices Lead free device Size 3.2*1.6 mm/0.12*0.06 inch Surface Mount packaging

for automated assembly

Applications

Digital cameras, Disk drivers, CD-ROMs,

Almost anywhere there is a low voltage power supply, up to 60V and a load to be ch protected, including: Computer mother board, Modem. USB hub PDAs & Charger, Analog & digital line card

nSMD075-16V

Alpha-Top (Sea&Land Alliance)

Performance Specification

Model	Marking	V _{max}	max	I _{hold}	I _{trip}	\mathbf{P}_{d}	Maxiı Time T		Resi	istance	Agency	Approval
Model	warking	(Vdc)	(A)	@25°C (A)	@25°C (A)	Max. (W)	Current (A)	Time (Sec)	Ri _{min} (Ω)	R1max (Ω)	UL	τυν
nSMD075-16V	αG	16	100	0.75	1.50	0.6	8.00	0.20	0.090	0.500	\checkmark	
Ihold = Hold Current.	Maximum cu	irrent device	will not trip	in 25°C still a	air.							
Itrip = Trip Current. N	1inimum curr	ent at which	the device v	will always tri	p in 25°C sti	ll air.						
Vmax = Maximum operating voltage device can withstand without damage at rated current (Imax).												
Imax = Maximum fault current device can withstand without damage at rated voltage (Vmax).												
Pd = Power dissipat	Pd = Power dissipation when device is in the tripped state in 25°C still air environment at rated voltage.											
Rimin/max = Minimum/Maximum device resistance prior to tripping at 25°C.												
R1 _{max} = Maximum device resistance is measured one hour post reflow.												
CAUTION : Operation I	CAUTION : Operation beyond the specified ratings may result in damage and possible arcing and flame.											

Environmental Specifications

Test	Conditions	Resistance change
Passive aging	+85°C, 1000 hrs.	±5% typical
Humidity aging	+85°C, 85% R.H. , 168 hours	±5% typical
Thermal shock	+85°C to -40°C, 20 times	±33% typical
Resistance to solvent	MIL-STD-202, Method 215	No change
Vibration	MIL-STD-202, Method 201	No change
Ambient operating conditions :	- 40 °C to 85 °C	
Maximum surface temperature of the dev	ice in the tripped state is 125 °C	
In case of special use, please contact our	engineer	

Agency Approvals :



E201504(Alpha-Top)/E319079(Sea&Land)

Regulation/Standard:



HF

2015/863/EU

EN14582


Ihold Versus Temperate	ure								
Model	Maximum ambient operating temperature (T_{mao}) vs. hold current (I_{hold})								
Model	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
nSMD075-16V	1.140	1.010	0.880	0.750	0.650	0.590	0.540	0.490	0.410

nSMD075-16V

Alpha-Top (Sea&Land Alliance)


Construction And Dimension (Unit:mm)									
Model	Madal A		В		(С		E	
Model	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Min.	
nSMD075-16V	3.00	3.50	1.50	1.80	0.50	1.20	0.15	0.10	

Dimensions & Marking



 α = Trademark G = Part identification

Recommended Pad Layout (mm)




Termination Pad Characteristics

Terminal pad materials : Terminal pad solderability : Rework


Tin-plated Nickel-Copper Meets EIA specification RS186-9E and ANSI/J-STD-002 Category 3.

Use standard industry practices, the removal device must be replaced with a fresh one.

Thermal Derating Curve



Typical Time-To-Trip At 25°C Average Time Current Curves



WARNING:


Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.

PPTC are intended for protection against occasional over current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated. Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.

Device performance can be impacted negatively in devices are mainted in a manner inconsistent with recommended ecutority, memary and mechanical procedures for electronic components.
 Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC.
 Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.
 Contamination of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices. PPTC SMD can be cleaned by standard methods.
 Requests that customers comply with our recommended solder pad layouts and recommended reflow profile. Improper board layouts or reflow profile could negatively impact solderability performance of our devices.

nSMD075-16V


Alpha-Top (Sea&Land Alliance)




Tape And Reel Specifications (mm)

Governing Specifications	EIA 481-1
W	8.15 ± 0.3
_P0	4.0 ± 0.10
_P1	4.0 ± 0.10
P2	2.0 ± 0.05
_A0	1.95 ± 0.10
B0	3.45 ± 0.10
B1max.	4.35
_D0	1.5 + 0.1, -0
F	3.5 ± 0.05
_E1	1.75 ± 0.10
E2min.	6.25
Tmax.	0.6
T1max.	0.1
<u>K0</u>	1.04 ± 0.1
Leader min.	390
Trailer min.	160
Reel Dimensions	
A max.	178
N min.	60
W1	9 ± 0.5
W2	12.6 ± 0.5

EIA Tape Component Dimensions



EIA Reel Dimensions



Storage And Handling • Storage conditions : 40°C max, 70% R.H.

· Devices may not meet specified performance

if storage conditions are exceeded.

Order Information	F	Packaging
nSMD	075-16V	Tape & Reel Quantity
Product name	Hold	
Size 3216 mm / 1206 inch	Current	3500 pcs/reel
SMD : surface mount device	0.75A	

Tape & reel packaging per EIA481-1

Labeling Information

