15W isolated DC-DC converter in DIP package Ultra-wide input and regulated dual output



FEATURES

- Ultra-wide 4:1 input voltage range
- High efficiency up to 90%
- No-load power consumption as low as 0.24W
- I/O isolation test voltage 1.5k VDC
- Input under-voltage protection, output short-circuit, over-current, over-voltage protection
- Operating ambient temperature range: -40°C to +105°C
- Meets CISPR32/EN55032 CLASS A without extra components
- Input reverse polarity protection available with Chassis (A2S) or 35mm DIN-Rail mounting (A4S) version
- Industry standard pin-out
- Meets EN50155 railway standard

URA_YMD-15WR3 series of isolated 15W DC-DC converter products have an ultra-wide 4:1 input voltage and feature efficiencies of up to 90%, input to output isolation is tested with 1500VDC and the converters safely operate in an ambient temperature of -40 $^\circ$ to +105 $^\circ$, input under-voltage protection, output short-circuit, over-current, over-voltage protection. They meet CLASS A of CISPR32/EN55032 EMI standards without extra components, optional packages are offered for chassis or DIN-rail mounting (A2S, A4S), adding additional input reverse polarity protection and they are widely used in applications such as industrial control, electric power, instruments, communication and railway fields.

RoHS

Selection	Guide										
		Input Voltage (VDC)		Output		Full Load	Capacitive				
Certification	Certification Part No. ¹¹	Nominal [®] (Range)	Max. [®]	Voltage(VDC)	Current (mA) Max./Min.	Efficiency [®] (%) Min./Typ.	Load [©] (µF)Max.				
	URA2405YMD-15WR3			±5	±1500/0	85/87	1500				
	URA2412YMD-15WR3	24 (9-36)				40	±12	±625/0	88/90	470	
	URA2415YMD-15WR3					(9-36)	(9-36)	(9-36)	(9-36)	40	±15
EN/BS EN	URA2424YMD-15WR3			±24	±312/0	86/88	200				
EIN/DO EIN	URA4805YMD-15WR3	48 (18-75)		±5	±1500/0	84/86	1500				
	URA4812YMD-15WR3		48	±12	±625/0	87/89	470				
	URA4815YMD-15WR3		(18-75)	(18-75)	80	±15	±500/0	87/89	330		
	URA4824YMD-15WR3			±24	±312/0	88/90	200				

Notes:

- ① Use "H" suffix for heat sink mounting, "A2S" suffix for chassis mounting and "A4S" suffix for Din-Rail mounting. We recommend to choose modules with a heat sink for enhanced heat dissipation and applications with extreme temperature requirements;
- ② Minimum input voltage and start-up voltage are increased by 1VDC for all models with A2S (wiring) and A4S (rail) suffixes because of the input reverse polarity function:
- Exceeding the maximum input voltage may cause permanent damage;
- Efficiency is measured at nominal input voltage and rated output load; efficiencies for A2S and A4S Model's is decreased by 2% due to the input reverse polarity protection circuit;
- The specified maximum capacitive load value for positive and negative output is identical.

Input Specifications					
Item	Operating Conditions	Min.	Тур.	Max.	Unit
Input Current	24VDC nominal input series, nominal input voltage		719/10	/20	
(full load / no-load)	48VDC nominal input series, nominal input voltage		364/5	/11	mA
Reflected Ripple Current			30		

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.

Course Vallence (Inc. many)	24VDC nominal input series	-0.7		50	
Surge Voltage (1sec. max.)	48VDC nominal input series	-0.7		100	
Ctart up Voltago	24VDC nominal input series	-		9	VDC
Start-up Voltage	48VDC nominal input series	-		18	VDC
Input Under-voltage Protection	24VDC nominal input series	5.5	6.5	-	
input offdet-vollage Flotection	48VDC nominal input series	12	15.5	_	
Start-up Time	Nominal input voltage & constant resistance load		10	-	ms
Input Filter		Pi filter			
Hot Plug		Unavailable			
	Module on	Ctrl pir	open or pull	ed high (3.5-1	2VDC)
Ctrl *	Module off	Ctrl pin pulled low to GND (0-1.2VDC)		VDC)	
Input current when off			2	7	mA
Note: *The Ctrl pin voltage is reference	ced to input GND.				

Output Specification	S					
Item	Operating Conditions		Min.	Тур.	Max.	Unit
Voltage Accuracy [®]	5%-100% load			±1	±3	
Linear Regulation	Input voltage variation from low to high at full load	Vo1		±0.2	±0.5	
		Vo2		±0.4	±1	%
Load Regulation [®]	5%-100% load			±0.5	±1	
Cross Regulation	Dual output, Vo1 load at 50%, Vo2 load at range of 10%-100%				±5	
Transient Recovery Time		All products		300	500	μs
Translant Deepens Deviation	25% load step change, nominal input voltage	5VDC output		±3	±8	%
Transient Response Deviation	Hornina input voltage	Others		±3	±5	
Temperature Coefficient	Full load		-		±0.03	%/℃
Ripple & Noise®	20MHz bandwidth, 5%-100% load			100	200	mV p-p
Over-voltage Protection	Input voltage range		110		160	%Vo
Over-current Protection			110	200	270	%lo
Short-circuit Protection		_		Continuous,	self-recovery	

Note: ①Output voltage accuracy for 0%-5% load is ±4% max;

②Load regulation for 0%-100% load is ±5%;

③Under 0% -5% load conditions, ripple & noise does not exceed 5%Vo. The "parallel cable" method is used for ripple and noise test, please refer to DC-DC Converter Application Notes for specific information.


Item	Operating Conditions	Min.	Тур.	Max.	Unit
11.10	Input-output Electric Strength Test for 1 minute with a leakage current of 1mA max	1500			\/D0
Isolation	Input/output-case Electric Strength Test for 1 minute with a leakage current of 1mA max.	1000			VDC
Insulation Resistance	Input-output resistance at 500VDC	1000			ΜΩ
Isolation Capacitance	Input-output capacitance at 100kHz/0.1V		2000		рF
Operating Temperature	See Fig. 1	-40		+105	•0
Storage Temperature		-55		+125	℃
Storage Humidity	Non-condensing	5		95	%RH
Pin Soldering Resistance Temperature	Soldering spot is 1.5mm away from case for 10 seconds			+300	°C
Vibration		IEC/EN61373 - Category 1, Grade B			
Switching Frequency *	PWM mode		270		kHz
MTBF	MIL-HDBK-217F@25℃	1000			k hours


Mechanical Specific	ations			
Case Material	Aluminum alloy	Aluminum alloy		
	Horizontal package	e (without heat sink)	25.40 x 25.40 x 11.70 mm	
	Horizontal package	e (with heat sink)	25.40 x 25.40 x 16.20 mm	
Discouries	A2S chassis mounting (without heat sink)		76.00 x 31.50 x 21.20 mm	
Dimensions	A2S chassis mountin	76.00 x 31.50 x 25.20 mm		
	A4S DIN-Rail mount	76.00 x 31.50 x 25.80 mm		
	A4S DIN-Rail mount	ting (with heat sink)	76.00 x 31.50 x 29.80 mm	
NA/a: ailai	without heat sink	Horizontal package/A2S chassis mounting/A4S DIN-Rail mounting	15.0g/35.0g/58.0g (Typ.)	
Weight	with heat sink	Horizontal package/A2S chassis mounting/A4S DIN-Rail mounting	19.0g/39.0g/62.0g(Typ.)	
Cooling Methods	Free air convection	n		


Electrom	agnetic C	ompatibility (EM	IC)	
Emissions	CE	CISPR32/EN55032	CLASS A (without extra components)/ CLASS B (see Fig.3-2) for	r recommended circuit)
ETTISSIONS	RE	CISPR32/EN55032	CLASS A (without extra components)/ CLASS B (see Fig.3-2) for	r recommended circuit)
	ESD	IEC/EN61000-4-2	Contact ±4kV	perf. Criteria B
	RS	IEC/EN61000-4-3	10V/m	perf. Criteria A
Immunity	EFT	IEC/EN61000-4-4	±2kV (see Fig.3-1) for recommended circuit)	perf. Criteria B
	Surge	IEC/EN61000-4-5	line to line ±2kV (see Fig.3-①for recommended circuit)	perf. Criteria B
	CS	IEC/EN61000-4-6	3 Vr.m.s	perf. Criteria A


Electromo	agnetic Co	ompatibility (EMC) (EN50155)	
	CE	EN50121-3-2 150kHz-500kHz 99dBuV (see Fig.3-2) for recommended circuit)	
Emissions	CL	EN55016-2-1 500kHz-30MHz 93dBuV (see Fig.3-2) for recommended circuit)	
ETTISSIOTIS	RE	EN50121-3-2 30MHz-230MHz 40dBuV/m at 10m (see Fig.3-2) for recommended	d circuit)
	KE	EN55016-2-1 230MHz-1GHz 47dBuV/m at 10m (see Fig.3-2) for recommended	d circuit)
	ESD	EN50121-3-2 Contact ±6kV/Air ±8kV	perf. Criteria A
	RS	EN50121-3-2 20V/m	perf. Criteria A
Immunity	EFT	EN50121-3-2 ±2kV 5/50ns 5kHz (see Fig.3-① for recommended circuit)	perf. Criteria A
	Surge	EN50121-3-2 line to line ±1kV (42 Ω , 0.5 μ F) (see Fig.3- $\!\!$ $\!\!$ for recommended circuit)	perf. Criteria A
	CS	EN50121-3-2 0.15MHz-80MHz 10V r.m.s	perf. Criteria A


Typical Characteristic Curves












Design Reference

1. Typical application


All the DC-DC converters of this series are tested before delivery using the recommended circuit shown in Fig. 2. Input and/or output ripple can be further reduced by appropriately increasing the input & output capacitor values Cin and Cout and/or by selecting capacitors with a low ESR (equivalent series resistance). Also make sure that the capacitance is not exceeding the max. capacitive load value of the product.



Input Voltage (V)

Vin	24V	48V
Cin	100µF/50V	10μF -47μF/100V
Cout	10	uF/100V

EMC compliance circuit



Notes: For EMC tests we use Part ① in Fig. 3 for immunity and part ② for emissions test. Selecting based on needs.

didifferen descript	OI I.		
Model	Vin: 24VDC	Vin: 48VDC	
FUSE	T/2.5A/250VAC	T/1.6A/250VAC	
C0, C4	330µF/50V	330µF/100V	
C1, C2	4.7µF/50V	4.7µF/100V	
С3	Refer to th	ne Cout in Fig.2	
LDM1	4.7µH		
CY1, CY2	11	nF/2kV	


- 3. The products do not support parallel connection of their output
- For additional information please refer to DC-DC converter application notes on www.mornsun-power.com

Parameter description:

MORNSUN®

THIRD ANGLE PROJECTION


URA_YMD-15WR3 Dimensions



Unit: mm[inch]

PIN1/2/3/4/5/6: φ 1.0mm


Pin diameter tolerances: $\pm 0.10[\pm 0.004]$ General tolerances: $\pm 0.50[\pm 0.020]$




Note: Grid 2.54*2.54mm

Pin-Out		
Pin	Mark	
1	Ctrl	
2	GND	
3	Vin	
4	+Vo	
5	OV	
6	-Vo	

URA_YMD-15WHR3 Dimensions






Note: Unit: mm[inch]

$$\begin{split} & PIN1/2/3/4/5/6: \ \, \varphi \ \, 1.0mm \\ & Pin \ \, diameter \ \, tolerances: \ \, \pm \ \, 0.10[\, \pm \, 0.004] \\ & General \ \, tolerances: \ \, \pm \ \, 0.50[\, \pm \, 0.020] \end{split}$$






Note: Grid 2.54*2.54mm

Pir	n-Out
Pin	Mark
1	Ctrl
2	GND
3	Vin
4	+Vo
5	OV
6	-Vo



URA_YMD-15WR3A2S Dimensions





	60.	Pin-	-Out			
Pin	1	2	3	4	5	6
Mark	Ctrl	GND	Vin	+Vo	OV	-0V

Note:


Unit: mm[inch]


Wire range: 24-12 AWG

Tightening torque: Max 0.4 N ⋅ m General tolerances: ±1.00[±0.039]

URA_YMD-15WHR3A2S Dimensions







		Pin-	-Out			
Pin	1	2	3	4	5	6
Mark	Ctrl	GND	Vin	+Vo	OV	-Vo


Note: Unit: mm[inch] Wire range: 24–12 AWG

Tightening torque: Max 0.4 N ⋅ m General tolerances: ± 1.00[± 0.039]




URA_YMD-15WR3A4S Dimensions





		Pin-	-Out			
Pin	1	2	3	4	5	6
Mark	Ctrl	GND	Vin	+Vo	OV	-0V




Note:

Unit: mm[inch] Mounting rail: TS35 Wire range: 24–12 AWG


Tightening torque: Max 0.4 N ⋅ m General tolerances: ±1.00[±0.039]

URA_YMD-15WHR3A4S Dimensions





Pin-Out							
Pin	1	2	3	4	5	6	
Mark	Ctrl	GND	Vin	+Vo	0V	-Vo	



Note:
Unit: mm[inch]
Mounting rail: TS35
Wire range: 24–12 AWG
Tightening torque: Max 0.4 N ⋅ m
General tolerances: ±1.00[±0.039]



Note:

- For additional information on Product Packaging please refer to <u>www.mornsun-power.com</u>. The Packaging bag number of Horizontal package: 58210003(without heat sink), 58200048(with heat sink), A2S/ A4S package number: 58220022;
- If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet;
- 3. The maximum capacitive load offered were tested at nominal input voltage and full load;
- 4. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%RH with nominal input voltage and rated output load;
- 5. All index testing methods in this datasheet are based on company corporate standards;
- 6. We can provide product customization service, please contact our technicians directly for specific information;
- 7. Products are related to laws and regulations: see "Features" and "EMC";
- 8. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.

Mornsun Guangzhou Science & Technology Co., Ltd.

Address: No. 5, Kehui St. 1, Kehui Development Center, Science Ave., Guangzhou Science City, Huangpu District, Guangzhou, P. R. China Tel: 86-20-38601850 Fax: 86-20-38601272 E-mail: info@mornsun.cn www.mornsun-power.com

MORNSUN®

MORNSUN Guangzhou Science & Technology Co., Ltd.