


CMOS general purpose timer

Features

- Exact equivalent in most cases for SE/NE555.
- Low Supply Current.
- High speed operation 500 kHz guaranteed.
- Wide operation supply voltage range 2 to 18 volts.
- Timing from microseconds through hours.
- Operates in both astable and monostable modes.
- Adjustable duty cycle.
- High output source/sink driver can drive TTL/CMOS

Ordering Information



DEVICE	Package Type	MARKING	Packing	Packing Qty
TLC555N	DIP8	TLC555	TUBE	2000/box
TLC555M/TR	SOP8	TLC555	REEL	2500/reel
TLC555MM/TR	MSOP8	TLC555	REEL	3000/reel




General Description

The TLC555 is CMOS RC timers providing significantly improved performance over the standard SE/NE555 and 355 timers, while at the same time being direct replacements for those devices in most applications. Improved parameters include low supply current, wide operating supply voltage range, low THRESHOLD, TRIGGER and RESET currents, no crowbarring of the supply current during output transitions, higher frequency performance and no requirement to decouple CONTROL VOLTAGE for stable operation.

Specifically, the TLC555 is stable controller capable of producing accurate time delays of frequencies.

PIN ASSIGNMENT



TRUTH TABLE

THRESHOLD	TRIGGER	RESET	OUTPUT	DISCHARGE
X	X L		L	ON
> 2/3 V _{CC}	> 1/3 V _{CC}	Н	L	ON
< 2/3 V _{CC}	> 1/3 V _{CC}	Н	STABLE	STABLE
Х	< 1/3 V _{CC}	Н	Н	OFF



Maximum Ratings And Recommended Operating Conditions

		Recomn operatingc		Maximum ratings		
Parameter, unit	Symbol	Val	ue	Val	ue	
		min	max	min	max	
Supply Voltage, V	VCC	2.0	18.0	0	18.0	
Output Current, mA	lo	-	20	-	100	
Input Voltage, V	VTH, VTRIG, VRST	-	-	-0.3	V _{CC} +0.3	
Power Dissipation, mW	PD	-	-	-	200	
Operating Temperature,°C	TOPR	0	70	0	70	
Storage Temperature,°C	TSTG	-	-	-65	150	
Lead Temperature, 1 mm from Case for 10 Seconds,°C	TSOLDER	-	-		260	



DC ELECTRICAL CHARACTERISTICS (Voltages Referenced to GND)

	0 1 1	Test Condit	ions	Val	Tempe-		
Parameter, units	Symbol	IOL, IOH	VCC, B	min	max	rature, °C	
	VTH		5.0	0.65 Vcc	0.70 Vcc	25 ± 10	
Threshold Voltage, V	۷IП		5.0	0.60 V _{CC}	0.80 V _{CC}	-20, 70	
Trigger voltage, V	VTRIG		5.0	0.31 V _{CC}	0.36 V _{CC}	25 ± 10	
	VING		5.0	0.28 V _{CC}	0.40 V _{CC}	-20, 70	
			2.0	0.4	1.0	25±10	
Reset voltage, V	VRST		18.0	0.4	1.0	20 - 10	
			2.0	0.2	1.5	-20, 70	
			18.0	0.2	1.0	-20, 70	
Control Voltage Lead, V	VCV			0.65 V _{CC}	0.69 V _{CC}	25 10	
Control voltage Lead, v	v0v			0.60 V _{cc}	0.80 V _{CC}	-20, 70	
	VOL	I _{OL} = 3.2 mA	5.0		0.4	25±10	
Output voltage Low, V		I _{OL} = 20 mA	15.0		1.0	20 - 10	
		I _{OL} = 3.2 mA	5.0		0.6	-20, 70	
		I _{OL} = 20 mA	15.0		1.5	-20, 70	
			5.0	4.0		25±10	
Output voltage High, V	Vон	I _{он} = -0.8 mA	15.0	14.3		25 - 10	
Output voltage riigh, v	VOIT	10H0.0 IIIA	5.0	3.5		-20, 70	
			15.0	14.0		-20, 70	
			2.0		200	25±10	
Supply Current, µA	ICC		18.0		300	20 <u>1</u> 10	
	100		2.0		400	-20, 70	
			18.0		600	-20, 70	



AC ELECTRICAL CHARACTERISTICS

		Test Conditions		Va	Tempe-	
Parameter, unit	Symbol	R_L, C_L	VCC, V	Min	Max	rature, °C
Rise (Fall) Time of	tTHL,	R _L = 10 MΩ, C _L = 10 pF	5.0	35	75	25±10
Output,ns	ttlh	· · ·		70	150	-20, 70
Guaranteed Max	I IMAX Astable		2.0-	500		25±10
Osc Freq,kHz			18.0	200		-20, 70
Initial accuracy, %				5		
Drift with Tomporature			5.0		0.02	
Drift with Temperature, %/°C	αf	R∟ = 1 - 100 kΩ	10.0		0.03	-20, 70
70/ C		C∟= 0.1 µF	15.0		0.06	
Drift with Supply Voltage,	٨f		5.0		3	25 ± 10
%/B	Δf		5.0		6	-20, 70




Figura 1. Block Diagram






Figura 2. Switcing Waveforms



Physical Dimensions


SOP8






Dimensions In Millimeters(SOP8)									
Symbol:	A	A1	В	С	C1	D	Q	а	b
Min:	1.35	0.05	4.90	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	5.10	6.20	4.00	0.80	8°	0.45	1.27 030

DIP8








Dimensions In Millimeters(DIP8)											
Symbol:	A	В	D	D1	Е	L	L1	а	b	с	d
Min:	6.10	9.00	8.40	7.42	3.10	0.50	3.00	1.50	0.85	0.40	2.54.000
Max:	6.68	9.50	9.00	7.82	3.55	0.70	3.60	1.55	0.90	0.50	2.54 BSC



Physical Dimensions

MSOP8



Dimensions In Millimeters(MSOP8)									
Symbol:	A	A1	В	С	C1	D	Q	а	b
Min:	0.80	0.05	2.90	4.75	2.90	0.35	0°	0.25	0.65 BSC
Max:	0.90	0.20	3.10	5.05	3.10	0.75	8°	0.35	0.05 650



IMPORTANT STATEMENT:

Huaguan Semiconductor reserves the right to change its products and services without notice. Before ordering, the customer shall obtain the latest relevant information and verify whether the information is up to date and complete. Huaguan Semiconductor does not assume any responsibility or obligation for the altered documents.

Customers are responsible for complying with safety standards and taking safety measures when using Huaguan Semiconductor products for system design and machine manufacturing. You will bear all the following responsibilities: select the appropriate Huaguan Semiconductor products for your application; Design, validate and test your application; Ensure that your application meets the appropriate standards and any other safety, security or other requirements. To avoid the occurrence of potential risks that may lead to personal injury or property loss.

Huaguan Semiconductor products have not been approved for applications in life support, military, aerospace and other fields, and Huaguan Semiconductor will not bear the consequences caused by the application of products in these fields.

The technical and reliability data (including data sheets), design resources (including reference designs), application or other design suggestions, network tools, safety information and other resources provided for the performance of semiconductor products produced by Huaguan Semiconductor are not guaranteed to be free from defects and no warranty, express or implied, is made. The use of testing and other quality control technologies is limited to the quality assurance scope of Huaguan Semiconductor. Not all parameters of each device need to be tested.

The documentation of Huaguan Semiconductor authorizes you to use these resources only for developing the application of the product described in this document. You have no right to use any other Huaguan Semiconductor intellectual property rights or any third party intellectual property rights. It is strictly forbidden to make other copies or displays of these resources. You should fully compensate Huaguan Semiconductor and its agents for any claims, damages, costs, losses and debts caused by the use of these resources. Huaguan Semiconductor accepts no liability for any loss or damage caused by infringement.