


Feature


- 30V,120A
- $R_{DS\ (ON)} < 3.8m\ \Omega @ V_{GS}=10V$
- Advanced Trench Technology
- Lead free product is acquired
- Excellent $R_{DS\ (ON)}$ and Low Gate Charge



Schematic Diagram

Application

- PWM applications
- Load Switch
- Power management



Marking and pin assignment

Package Marking and Ordering Information

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity (PCS)
120N03	AP120N03	TO-220C	13 inch	-	1000

ABSOLUTE MAXIMUM RATINGS ($T_a=25^\circ C$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	30	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current ($T_a = 25^\circ C$)	I_D	120	A
Continuous Drain Current ($T_a = 100^\circ C$)	I_D	72	A
Pulsed Drain Current ⁽¹⁾	I_{DM}	400	A
Singel Pulsed Avalanche Energy ⁽²⁾	E_{AS}	121	mJ
Power Dissipation	P_D	108	W
Thermal Resistance from Junction to Case	R_{eJC}	1.4	$^\circ C/W$
Junction Temperature	T_J	150	$^\circ C$
Storage Temperature	T_{STG}	-55~+150	$^\circ C$

MOSFET ELECTRICAL CHARACTERISTICS($T_a=25^\circ C$ unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Type	Max	Unit
Static Characteristics						
Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	30	-	-	V
Zero gate voltage drain current	I_{DSS}	$V_{DS} = 30V, V_{GS} = 0V$	-	-	1	μA
Gate-body leakage current	I_{GSS}	$V_{GS} = \pm 20V, V_{DS} = 0V$	-	-	± 100	nA
Gate threshold voltage ⁽³⁾	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = 250\mu A$	1	1.5	2.5	V
Drain-source on-resistance ⁽³⁾	$R_{DS(on)}$	$V_{GS} = 10V, I_D = 30A$	-	3.0	3.8	$m\Omega$
Drain-source on-resistance ⁽³⁾	$R_{DS(on)}$	$V_{GS} = 4.5V, I_D = 20A$	-	4.9	6.0	$m\Omega$
Dynamic characteristics						
Input Capacitance	C_{iss}	$V_{DS} = 15V, V_{GS} = 0V, f = 1MHz$	-	2680	-	pF
Output Capacitance	C_{oss}		-	393	-	
Reverse Transfer Capacitance	C_{rss}		-	330	-	
Switching characteristics						
Turn-on delay time	$t_{d(on)}$	$V_{DD}=15V, I_D=30A, R_L=1\Omega$ $V_{GS}=10V, R_G=3\Omega$	-	23	-	ns
Turn-on rise time	t_r		-	28	-	
Turn-off delay time	$t_{d(off)}$		-	74	-	
Turn-off fall time	t_f		-	36	-	
Total Gate Charge	Q_g	$V_{DS}=15V, ID=30A,$ $V_{GS}=10V$	-	30	-	nC
Gate-Source Charge	Q_{gs}		-	7.2	-	
Gate-Drain Charge	Q_{gd}		-	10.4	-	
Source-Drain Diode characteristics						
Diode Forward voltage ⁽³⁾	V_{DS}	$V_{GS} = 0V, I_S = 30A$	-	-	1.2	V
Diode Forward current ⁽⁴⁾	I_S		-	-	120	A
Body Diode Reverse Recovery Time	trr	$T_J=25^\circ C, IF=20A, di/dt=100A/us$		28		ns
Body Diode Reverse Recovery Charge	Qrr	$T_J=25^\circ C, IF=20A, di/dt=100A/us$		21		nc

Notes:

1. Repetitive Rating: pulse width limited by maximum junction temperature
2. EAS Condition: $T_J=25^\circ C, V_{DD}=20V, R_G=25\Omega, L=0.5mH, I_{AS}=22A$
3. Pulse Test: pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
4. Surface Mounted on FR4 Board, $t \leq 10$ sec

Test Circuit




Figure 1: Gate Charge Test Circuit & Waveform




Figure 2: Resistive Switching Test Circuit & Waveforms




Figure 3: Unclamped Inductive Switching Test Circuit & Waveforms

Figure1: Output Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 5: Gate Charge Characteristics




Figure 2: Typical Transfer Characteristics




Figure 4: Body Diode Characteristics




Figure 6: Capacitance Characteristics




Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Case Temperature






Figure 11: Maximum Effective Transient Thermal Impedance, Junction-to-Case



TO-220C Package Information



Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	4.40		4.60	0.173		0.181
B	0.70		0.90	0.028		0.035
C	0.45		0.60	0.018		0.024
C2	1.23		1.32	0.048		0.052
C3	2.20		2.60	0.087		0.102
D	8.90		9.90	0.350		0.390
E	9.90		10.3	0.390		0.406
F	6.30		6.90	0.248		0.272
G		2.54			0.1	
H	28.0		29.8	1.102		1.173
L1		3.39			0.133	
L2	1.14		1.70	0.045		0.067
L3	2.65		2.95	0.104		0.116
Φ		3.6			0.142	