



Most Cost-effective Decoding Platform SoC

Overview

D1s is a cost-effective AIoT chip designed by Allwinner for the intelligent decoding market. It possesses a 64bit RISC-V ISA Alibaba T-Head C906 CPU and built-in 64M DDR2, and supports Linux system. Besides, it integrates a large number of self-developed audio and video related IP, which support full format decoding such as H.265, H.264, MPEG-1/2/4, JPEG and audio interfaces such as ADC/DAC/I2S/PCM/DMIC/OWA. D1s can be widely used in smart home panels, HMI, industrial control, smart cars and other products.

Highlights

- Integrated 64-bit RISC CPU processor provides powerful computing performance.
- The 1080p full format decoding, rich display output interfaces, and Allwinner SmartColor 2.0 display enhancement technology provide excellent video experience for users.
- To reduce the BOM cost, a 64 MB DDR2 die is embedded for D1s.
- Rich peripheral interfaces, such as USB, SDIO, EMAC, TWI, UART, SPI, PWM, GPADC, IR TX&RX, and so on, greatly facilitate product expansion.
- The advanced process design with lower voltage and lower leakage, the power optimization design for typical scenes and the enhanced heat dissipation package, improve the heating experience of the product.


Features

CPU	 RISC CPU 32 KB I-cache + 32 KB D-cache 		
Memory	SIP 64MB DDR2SD3.0/eMMC 5.0, SPI Nor/NAND Flash		
Video Engine	 Video decoding H.265 up to 1080p@60fpsH.264 up to 1080p@60fpsMPEG-1/2/4, JPEG, VC1 up to 1080p@60fps Video encoding JPEG/MJPEG up to 1080p@60fps Supports input picture scaler up/down		
Display Engine	 Allwinner SmartColor2.0 post processing for an excellent display experience Supports de-interlace (DI) up to 1080p@60fps Supports G2D hardware accelerator including rotate, mixer, lbc decompression functions 		
Video OUT	 CVBS OUT interface, supporting NTSC and PAL format RGB LCD output interface up to 1920 x 1080@60fps Dual link LVDS interface up to 1920 x 1080@60fps 4-lane MIPI DSI interface up to 1920 x 1200@60fps 		
Video IN	 8-bit parallel CSI interface CVBS IN interface, supporting NTSC and PAL format 		
Audio	 2 DACs and 3 ADCs Analog audio interfaces: MICIN3P/N, LINEINL/R, FMINL/R, HPOUTL/R Digital audio interfaces: I2S/PCM, DMIC, OWA IN/OUT 		
Connectivity	 USB2.0 DRD, USB2.0 Host SDIO 3.0, SPI x 2, UART x 6, TWI x 4 PWM (8-ch), GPADC (1-ch), TPADC (4-ch), IR TX&RX 10/100/1000M EMAC with RMII and RGMII interfaces 		
Package	• eLQFP128, 14 mm x 14 mm		

Block Diagram

Video Input	RISC CPU	Internal System	Connectivity
CVBS IN	I-cache32KB	CCU	USB2.0 DRD
Parallel CSI		PLIC	USB2.0 HOST
	D-cache 32KB	T EIC	SDI03.0
Video Output	Display Engine	DMA	SPI x2 (Supports SPI Nand/Nor Flash)
MIPI DSI	DE	Thermal Sensor	TWI x4
RGB	DI	Timer	UART x6
Dual link LVDS	G2D	Timei	100M/1000M EMAC
CVBS OUT	Video Engine	High Speed Timer	GPADC (1-ch)
Audio	Video Decoding H.265/H.264	IOMMU	TPADC (4-ch)
Audio Codec	Video Encoding JPEG/MJPEG		PWM (8-ch)
I2S/PCM x2	Memory	Security System	LEDC
DMIC	SIP 64 MB DDR2	Crypto Engine	CIR TX
OWA IN/OUT	SD3.0/eMMC5.0	SID	CIR RX

Application Diagram



ABOUT ALLWINNER

Allwinner Technology, founded in 2007, is a outstanding designer dedicated to intelligent application SoC, high performance analog component and wireless connectivity IC. It is headquartered in Zhuhai China, with other R&D centers and offices in Shenzhen, HongKong, Xi'an, Beijing and Shanghai. Listed on the GEM of the Shenzhen Stock Exchange in 2015, with the stock code 300458.

Motivated by customer-oriented strategy, Allwinner aligns remarkable R&D teams with long-term core-technology investment in UHD video processing, high-performance multi-core CPU/GPU integration with AI and advanced manufacturing process in terms of high integration, ultra-low power consumption and full-stack integration platform, providing competitive turnkey solutions with considerate services. The products powered by Allwinner spread across from smart hardware, smart home, consumer electronics, HD media, smart video, connected car, industry control, wireless communication to analog products.

CONTACT US

Email: service@allwinnertech.com

This brief is for reference only and has no commitment. All content contained herein is subject to changes without notice. ©2021 Allwinner Technology Co., Ltd.