

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

Features

- Small Compact Surface Mountable Package with J-Bend Leads
- Rectangular Package for Automated Handling
- Highly Stable Oxide Passivated Junction
- Very Low Forward Voltage Drop (0.5 V Max @ 3.0 A, T_J = 25°C)
- Excellent Ability to Withstand Reverse Avalanche Energy Transients
- Guard-Ring for Stress Protection
- Device Passes ISO 7637 Pulse #1
- SBRS8 and NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable*
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Mechanical Characteristics

- Case: Epoxy, Molded, Epoxy Meets UL 94 V-0
- Weight: 217 mg (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- Polarity: Polarity Band on Plastic Body Indicates Cathode Lead
- Device Meets MSL 1 Requirements
- ESD Ratings:
 - Machine Model = C (> 400 V)
 - Human Body Model = 3B (> 8000 V)

SCHOTTKY BARRIER RECTIFIERS 3.0 AMPERES 20, 30, 40 VOLTS



SMC 2-LEAD CASE 403AC

MARKING DIAGRAM



ORDERING INFORMATION

Device	Package	Shipping [†]
MBRS320T3G	SMC (Pb-Free)	3,000 / Tape & Reel
MBRS330T3G	SMC (Pb-Free)	3,000 / Tape & Reel
MBRS340T3G	SMC (Pb-Free)	3,000 / Tape & Reel
NRVBS330T3G	SMC (Pb-Free)	3,000 / Tape & Reel
SBRS8320T3G*	SMC (Pb-Free)	3,000 / Tape & Reel
SBRS8340T3G*	SMC (Pb-Free)	3,000 / Tape & Reel



MAXIMUM RATINGS

Rating	Symbol	MBRS320T3G, SBRS8320T3G	MBRS330T3G, NRVBRS330T3G	MBRS340T3G, SBRS8340T3G	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	$egin{array}{c} V_{RRM} \ V_{RWM} \ V_{R} \end{array}$	20	30	40	\ \
Average Rectified Forward Current	I _{F(AV)}	3.0 @ T _L = 110°C 4.0 @ T _L = 105°C		Α	
Nonrepetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60 Hz)	I _{FSM}	80		А	
Operating Junction Temperature	TJ	– 65 to +150		°C	
ISO 7637 Pulse #1 (100 V, 10Ω)		5000		Pulses	
ESD Ratings: Machine Model = C Human Body Model = 3B			> 400 > 8000		V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


THERMAL CHARACTERISTICS

Thermal Resistance, Junction-to-Lead	$R_{ hetaJL}$	11	°C/W
ELECTRICAL CHARACTERISTICS			
Maximum Instantaneous Forward Voltage (Note 1) $(i_F = 3.0 \text{ A}, T_J = 25^{\circ}\text{C})$	V _F	0.50	V
Maximum Instantaneous Reverse Current (Note 1) (Rated dc Voltage, $T_J = 25^{\circ}\text{C}$) (Rated dc Voltage, $T_J = 100^{\circ}\text{C}$)	i _R	2.0 20	mA

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Pulse Test: Pulse Width = 300 μ s, Duty Cycle \leq 2.0%.

TYPICAL ELECTRICAL CHARACTERISTICS








Figure 2. Maximum Forward Voltage



TYPICAL ELECTRICAL CHARACTERISTICS (continued)





Figure 3. Typical Reverse Current

Figure 4. Maximum Reverse Current








Figure 6. Forward Power Dissipation





Figure 7. Typical Capacitance





PACKAGE DIMENSIONS


SMC 2-LEAD

CASE 403AC **ISSUE B**










NOTES:

- NOTES:

 1. DIMENSIONING AND TOLERANCING PER ANME Y14.5M, 1994.
 2. CONTROLLING DIMENSION: INCHES.
 3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.254mm PER SIDE.
 4. DIMENSIONS D AND E TO BE DETERMINED AT DATUM H.
 5. DIMENSION b SHALL BE MEASURED WITHIN THE AREA DETERMINED BY DIMENSION L.

	MILLIMETERS		INCHES		
DIM	MIN	MAX	MIN	MAX	
Α	1.95	2.61	0.077	0.103	
A1	0.05	0.20	0.002	0.008	
A2	1.90	2.41	0.075	0.095	
b	2.90	3.20	0.114	0.126	
С	0.15	0.41	0.006	0.016	
D	5.55	6.25	0.219	0.246	
E	6.60	7.15	0.260	0.281	
HE	7.75	8.15	0.305	0.321	
L	0.75	1.60	0.030	0.063	

RECOMMENDED SOLDERING FOOTPRINT*



^{*}For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.