


Table 1: Main Product Characteristics

$I_{F(AV)}$	1 A
V_{RRM}	600 V
I_R (max)	75 μ A
T_j	175°C
V_F (typ)	1.0 V
t_{rr} (max)	25 ns

FEATURES AND BENEFITS

- Ultrafast switching
- Low reverse recovery current
- Low thermal resistance
- Reduces switching & conduction losses


Table 2: Order Codes

Part Number	Marking
STTH1R06	ES1B
STTH1R06	ES1M

Part Number	Marking
STTH1R06	ES1J
STTH1R06U	ES1K

Table 3: Absolute Ratings (limiting values)

Symbol	Parameter			Value	Unit	
V_{RRM}	Repetitive peak reverse voltage			600	V	
$I_{F(RMS)}$	RMS forward voltage	DO-41		10	A	
		SMA / SMB		7		
$I_{F(AV)}$	Average forward current	DO-41	$T_c = 100^\circ\text{C}$	$\delta = 0.5$	A	
		SMA	$T_c = 125^\circ\text{C}$	$\delta = 0.5$		
		SMB	$T_c = 135^\circ\text{C}$	$\delta = 0.5$		
I_{FSM}	Surge non repetitive forward current	DO-41	$t_p = 10\text{ms}$ sinusoidal	25	A	
		SMA / SMB		20		
T_{stg}	Storage temperature range			-65 to + 175	°C	
T_j	Maximum operating junction temperature			175	°C	

Table 4: Thermal Resistance

Symbol	Parameter			Value (max.)	Unit
$R_{th(j-l)}$	Junction to lead	$L = 10\text{mm}$	DO-41	45	$^{\circ}\text{C/W}$
			SMA	30	
			SMB	25	
$R_{th(j-a)}$	Junction to ambient ⁽¹⁾	$L = 10\text{mm}$	DO-41	70	$^{\circ}\text{C/W}$

Note 1: $R_{th(j-a)}$ is measured with a copper area $S = \text{Scm}^2$ (see figure12).

Table 5: Static Electrical Characteristics

Symbol	Parameter	Test conditions		Min.	Typ	Max.	Unit
I_R	Reverse leakage current	$T_j = 25^{\circ}\text{C}$	$V_R = V_{RRM}$			1	μA
		$T_j = 150^{\circ}\text{C}$			10	75	
V_F	Forward voltage drop	$T_j = 25^{\circ}\text{C}$	$I_F = 1\text{A}$			1.7	V
		$T_j = 150^{\circ}\text{C}$			1.0	1.25	

To evaluate the conduction losses use the following equation: $P = 1.03 \times I_F(\text{AV}) + 0.27 I_F^2 (\text{RMS})$

Table 6: Dynamic Characteristics

Symbol	Parameter	Test conditions			Min.	Typ	Max.	Unit	
t_{rr}	Reverse recovery time	$T_j = 25^{\circ}\text{C}$	$I_F = 0.5\text{A}$	$I_{rr} = 0.25\text{A}$	$I_R = 1\text{A}$			25	ns
			$I_F = 1\text{A}$	$dI_F/dt = -50 \text{ A}/\mu\text{s}$	$V_R = 30\text{V}$		30	45	
t_{fr}	Forward recovery time	$T_j = 25^{\circ}\text{C}$	$I_F = 1\text{A}$ $dI_F/dt = 100 \text{ A}/\mu\text{s}$ $V_{FR} = 1.1 \times V_{Fmax}$					100	ns
V_{FP}	Forward recovery voltage	$T_j = 25^{\circ}\text{C}$	$I_F = 1\text{A}$ $dI_F/dt = 100 \text{ A}/\mu\text{s}$ $V_{FR} = 1.1 \times V_{Fmax}$					10	V

Figure 1: Conduction losses versus average forward current




Figure 3: Relative variation of thermal impedance junction to case versus pulse duration (DO-41)




Figure 5: Relative variation of thermal impedance junction to case versus pulse duration (SMB)




Figure 2: Forward voltage drop versus forward current




Figure 4: Relative variation of thermal impedance junction to case versus pulse duration (SMA)




Figure 6: Peak reverse recovery current versus dI_F/dt (typical values)




Figure 7: Reverse recovery time versus dI_F/dt (typical values)




Figure 9: Reverse recovery softness factor versus dI_F/dt (typical values)




Figure 11: Transient peak forward voltage versus dI_F/dt (typical values)




Figure 8: Reverse recovery charges versus dI_F/dt (typical values)




Figure 10: Relative variations of dynamic parameters versus junction temperature




Figure 12: Forward recovery time versus dI_F/dt (typical values)




Figure 13: Junction capacitance versus reverse voltage applied (typical values)




Figure 14: Thermal resistance junction to ambient versus copper surface under each lead (epoxy FR4, $e_{CU}=35\mu\text{m}$) (DO-41, SMB)




Figure 15: Thermal resistance junction to ambient versus copper surface under each lead (epoxy FR4, $e_{CU}=35\mu\text{m}$) (SMA)




Figure 16: SMA Package Mechanical Data

REF.	DIMENSIONS			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A1	1.90	2.03	0.075	0.080
A2	0.05	0.20	0.002	0.008
b	1.25	1.65	0.049	0.065
c	0.15	0.41	0.006	0.016
E	4.80	5.60	0.189	0.220
E1	3.95	4.60	0.156	0.181
D	2.25	2.95	0.089	0.116
L	0.75	1.60	0.030	0.063

Figure 17: SMA Foot Print Dimensions

(in millimeters)




Figure 18: SMB Package Mechanical Data

REF.	DIMENSIONS			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A1	1.90	2.45	0.075	0.096
A2	0.05	0.20	0.002	0.008
b	1.95	2.20	0.077	0.087
c	0.15	0.41	0.006	0.016
E	5.10	5.60	0.201	0.220
E1	4.05	4.60	0.159	0.181
D	3.30	3.95	0.130	0.156
L	0.75	1.60	0.030	0.063

Figure 19: SMB Foot Print Dimensions

(in millimeters)




Figure 20: DO-41 Package Mechanical Data

REF.	DIMENSIONS			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.07	5.20	0.160	0.205
B	2.04	2.71	0.080	0.107
C	28		1.102	
D	0.712	0.863	0.028	0.034

Table 7: Ordering Information

Ordering type	Marking	Package	Weight	Base qty	Delivery mode
STTH1R06	STTH1R06	DO-41	0.34 g	2000	Ammopack
STTH1R06RL	STTH1R06	DO-41	0.34 g	5000	Tape & reel
STTH1R06A	AR6	SMA	0.068 g	2000	Tape & reel
STTH1R06B	BR6	SMB	0.11 g	3000	Tape & reel

- Epoxy meets UL94, V0