

## ABS07W

3.2 x 1.5 x 0.9 mm
RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE

Due to capacity constraints, this product is temporarily unavailable. Recommended alternative part number: ABS07-120-32.768kHz-T Contact Abracon for technical assistance: tech-support@abracon.com

#### **FEATURES**

- Exceptionally low plating load of 3.0pF, ideal for wearables, wireless, and IoT applications
- Simultaneously optimized for ESR over extended operating temperature range
- Miniature 3.2x1.5x0.9 mm SMD package, ideally suited for space constrained designs
- Available with  $\pm 10$  ppm set tolerance
- Seam sealed package for long term reliability

#### **APPLICATIONS**

- Wearables
- Wireless Modules
- Internet of Things (IoT)
- Bluetooth/Bluetooth Low Energy (BLE)
- Machine-to-Machine (M2M) Connectivity
- Ultra Low Power MCU
- Near Field Communication (NFC)
- ISM Band Applications
- Ultra low power, energy saving MCU

#### STANDARD SPECIFICATIONS

PARAMETERS	MINIMUM	TYPICAL	MAXIMUM	UNITS	NOTES
Frequency		32.768		kHz	
Operation Mode	Flexur	al Mode (Tunin	g Fork)		
Operating Temperature	-40		+125	°C	See options
Storage Temperature	-55		+125	°C	
Frequency Tolerance @ +25°C	-10		+10	ppm	Refer to Note #1, ±20 ppm is also available
Shift through standard RoHS Reflow, (2) reflow cycles maximum	-2.00		+2.00	ppm	260°C peak maximum reflow temperature, relative to stand-alone set-tolerance frequency
Temperature Coefficient	-0.040	-0.036		ppm/T <sup>2</sup>	
Turn-over temperature	+20	+25	+30	°C	
Frequency Stability Over Operating Temperature, relative to in-circuit measured frequency post reflow	-200		-100	ppm	Over -40°C to +85°C
	-275		-100	ppm	Over -40°C to +105°C
	-450		-100	ppm	Over -40°C to +125°C
Load capacitance (CL)		3		pF	Refer to Note #2
Equivalent Series Resistance (ESR)		< 40	45	kΩ	@ +25±3°C
		< 45	55	kΩ	Over -40°C to +85°C
		< 50	60	kΩ	Over -40°C to +105°C
		< 60	70	kΩ	Over $-40^{\circ}$ C to $+125^{\circ}$ C
Shunt capacitance (C0)		1.15	1.30	pF	Combined Electrode & Package Capacitance
Motional Capacitance (C1)		4.68		fF	C1 also referred as Cm
Motional Inductance (L1)		5,048,571		mΗ	L1 also referred as Lm
Drive Level		0.1	0.5	$\mu W$	
Crystal sensitivity to closed-loop oscillator loading (Ts)	125		140	ppm/pF	Refer to Note #3
Q value	13000				Quality Factor
Aging @ +25°C±3°C [First Year]	-3		+3	ppm	Relative to post reflow measured frequency
Aging @ +25°C±3°C [Over 10-years]	-10		+10	ppm	Relative to post reflow measured frequency
Insulation Resistance	500			$M\Omega$	@ 100Vdc

Note #1: With an effective loop capacitance of 3.0pF, the oscillator circuit will be within set-tolerance specification; less any frequency shift due to the reflow process.

Note #2: The oscillator loop needs to present an effective loop capacitance of 3.0 pF to track the stand-alone crystal frequency. This loop capacitance is essential to ensure highest possible Closed-Loop Safety Factor for the entire population of crystals.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com **REVISED: 03.08.2021** 






3.2 x 1.5 x 0.9 mm


RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE


### **OPTIONS AND PART IDENTIFICATION**




# TYPICAL FREQUENCY TOLERANCE DISTRIBUTION (AT $25^{\circ}C \pm 3^{\circ}C$ )




## TYPICALESR DISTRIBUTION (AT 25°C±3°C)



# TYPICAL FREQUENCY Vs. TEMPERATURE CHARACTERISTICS



# TYPICALESR(EQUIVALENT SERIES RESISTANCE) Vs. OPERATING TEMPERATURE





5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com REVISED: 03.08.2021




## ABS07W



### SPICE MODEL (BASED ON TYPICAL VALUES AT $25^{\circ}$ C $\pm 3^{\circ}$ C):

#### **Quartz Crystal Equivalent Circuit**



Frequency: 32.78kHz


#### Plating Load (CL) = 3pF


C0 = 1.15 pFR1 = 38,194  $\Omega$ 

L1 = 5,048,571 mH

C1 = 4.68 fF

#### **MECHANICAL DIMENSIONS**





**DIMENSIONS: mm** 



0.75

0.75

5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com **REVISED: 03.08.2021** 




## ABS07W

3.2 x 1.5 x 0.9 mm

RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE


### RECOMMENDED REFLOW PROFILE




Zone	Description	Temperature	Time
1	Preheat	$\begin{array}{c} T_{\rm SMIN} \sim T_{\rm SMAX} \\ 150 ^{\rm o}{\rm C} \sim 200 ^{\rm o}{\rm C} \end{array}$	$60 \sim 120 \text{ sec.}$
2	Reflow	T <sub>L</sub> 217°C	$60 \sim 150 \text{ sec.}$
3	Peak Heat	${ m T_p}$ $260\pm 5^{\circ}{ m C}$	10 ±5 sec. MAX

### **PACKAGING**

## TAPE AND REEL (3,000PCS/REEL)





DIMENSIONS: mm



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com REVISED: 03.08.2021