

MOSFET Silicon N-Channel MOS

1. Applications

Synchronous rectification in SMPS,
Hard switching and High speed circuit
DC/DC in telecoms and industrial



2. Features

Low drain-source on-resistance: $R_{DS(ON)} = 5.6\text{m}\Omega$ (typ.)
High speed power switching
Enhanced body diode dv/dt capability
Enhanced avalanche ruggedness





Table 1 Key Performance Parameters

Parameter	Value	Unit
$V_{DS} @ T_{j,max}$	85	V
$R_{DS(on),max}$	6.2	$\text{m}\Omega$
$Q_{g,typ}$	55.7	nC
$I_{D,pulse}$	240	A

3. Packaging and Internal Circuit

Part Name	Package	Marking
AUA062N08BG	TO220F	AUA062N08BG
AUB062N08BG	TO263	AUB062N08BG
AUP062N08BG	TO220	AUP062N08BG
AUN062N08BG	DFN5x6	AUN062N08BG
AUD062N08BG	TO252	AUD062N08BG



1 Maximum ratings

at $T_J = 25^\circ\text{C}$, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Continuous drain current ¹⁾	I_D		-	60	A	$T_C=25^\circ\text{C}$
Pulsed drain current ²⁾	$I_{D,\text{pulse}}$	-		240	A	$T_C=25^\circ\text{C}$
Avalanche energy, single pulse	E_{AS}	-	-	290	mJ	
Gate source voltage (static)	V_{GS}	-20	-	20	V	static;
Power dissipation (TO220F)	P_{tot}	-	-	30	W	$T_C=25^\circ\text{C}$
Power dissipation (TO263&TO220&TO252)	P_{tot}	-	-	150	W	$T_C=25^\circ\text{C}$
Power dissipation (DFN5x6)	P_{tot}	-	-	74	W	$T_C=25^\circ\text{C}$
Storage temperature	T_{stg}	-55	-	175	°C	
Operating junction temperature	T_j	-55	-	175	°C	

¹⁾ Limited by $T_{j,\text{max}}$. Maximum Duty Cycle D = 0.50

²⁾ Pulse width t_p limited by $T_{j,\text{max}}$

³⁾ Identical low side and high side switch with identical R_G

2 Thermal characteristics

Table 3 Thermal characteristics(TO220F)

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	5	°C/W	-
Thermal resistance, junction - ambient	R_{thJA}	-	-	60	°C/W	device on PCB, minimal footprint

Table Thermal characteristics(TO263&TO220&TO252)

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	1	°C/W	-
Thermal resistance, junction - ambient	R_{thJA}	-	-	62	°C/W	device on PCB, minimal footprint

Table Thermal characteristics(DFN5x6)

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	1.7	°C/W	-
Thermal resistance, junction - ambient	R_{thJA}	-	-	50	°C/W	device on PCB, minimal footprint

3 Electrical characteristics

at $T_j=25^\circ\text{C}$, unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(\text{BR})\text{DSS}}$	85	-	-	V	$V_{\text{GS}}=0\text{V}, I_{\text{D}}=10\text{mA}$
Gate threshold voltage	$V_{(\text{GS})\text{th}}$	2.5		3.5	V	$V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=250\mu\text{A}$
Zero gate voltage drain current	I_{DSS}	-	-	1000	nA	$V_{\text{DS}}=80\text{V}, V_{\text{GS}}=0\text{V}, T_j=25^\circ\text{C}$
Gate-source leakage current	I_{GSS}	-	-	100	nA	$V_{\text{GS}}=20\text{V}, V_{\text{DS}}=0\text{V}$
Drain-source on-state resistance	$R_{\text{DS}(\text{on})}$	-	5.6	6.2	mΩ	$V_{\text{GS}}=10\text{V}, I_{\text{D}}=20\text{A}, T_j=25^\circ\text{C}$
Gate resistance (Intrinsic)	R_{G}	-	1.2	-	Ω	f=1MHz, open drain

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	3730	-	pF	$V_{\text{ds}}=40\text{V}, V_{\text{gs}}=0\text{V}$ f=1MHz
Output capacitance	C_{oss}	-	674	-	pF	$V_{\text{ds}}=40\text{V}, V_{\text{gs}}=0\text{V}$ f=1MHz
Reverse transfer capacitance	C_{rss}	-	24.24	-	pF	$V_{\text{ds}}=40\text{V}, V_{\text{gs}}=0\text{V}$ f=1MHz
Turn-on delay time	$t_{\text{d}(\text{on})}$	-	16.5	-	ns	$V_{\text{DD}}=40\text{V}, V_{\text{GS}}=10\text{V}, R_{\text{G}}=10\Omega$ $I_{\text{D}}=20\text{A}$
Rise time	t_r	-	13.7	-	ns	$V_{\text{DD}}=40\text{V}, V_{\text{GS}}=10\text{V}, R_{\text{G}}=10\Omega$ $I_{\text{D}}=20\text{A}$
Turn-off delay time	$t_{\text{d}(\text{off})}$	-	35.9	-	ns	$V_{\text{DD}}=40\text{V}, V_{\text{GS}}=10\text{V}, R_{\text{G}}=10\Omega$ $I_{\text{D}}=20\text{A}$
Fall time	t_f	-	13.45	-	ns	$V_{\text{DD}}=40\text{V}, V_{\text{GS}}=10\text{V}, R_{\text{G}}=10\Omega$ $I_{\text{D}}=20\text{A}$

Table 6 Gate charge characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	15.9	-	nC	$V_{\text{DS}}=40\text{V}, V_{\text{GS}}=0 \text{ to } 10\text{V}$ $I_{\text{D}}=20\text{A}$
Gate to drain charge	Q_{gd}	-	13.3	-	nC	$V_{\text{DS}}=40\text{V}, V_{\text{GS}}=0 \text{ to } 10\text{V}$ $I_{\text{D}}=20\text{A}$
Gate charge total	Q_g	-	55.7	-	nC	$V_{\text{DS}}=40\text{V}, V_{\text{GS}}=0 \text{ to } 10\text{V}$ $I_{\text{D}}=20\text{A}$


Table 7 Reverse diode characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Diode forward voltage	V_{SD}	-	0.7	-	V	$V_{GS}=0V, I_F=1A, T_j=25^\circ C$
Reverse recovery time	t_{rr}	-	40.9	-	ns	$VR=40V, IF=20A, dI/dt=200A/us$
Reverse recovery charge	Q_{rr}	-	106.8	-	uC	$VR=40V, IF=20A, dI/dt=200A/us$
Peak reverse recovery current	I_{rrm}	-	-3.7	-	A	$VR=40V, IF=20A, dI/dt=200A/us$

4 Package Outlines

TO-220F


单位: mm



Symbol	Dimensions In Millimeters		Symbol	Dimensions In Millimeters	
	Min	Max		Min	Max
C	4.3	4.8	b1	2.9	3.9
A	9.7	10.3	a	0.55	0.9
B	14.7	16.1	E	2.29	2.79
B1	3.8	4	E1	2.29	2.79
B2	2.9	3.55	C1	2.5	2.9
R	3	3.4	C2	2.15	2.7
b	12.5	13.6	c	0.4	0.7

Figure1: Outline PG-TO220F

AUA062N08BG, AUB062N08BG, AUP062N08BG, AUN062N08BG, AUD062N08BG



单位: mm

Symbol	Dimensions In Millimeters		Symbol	Dimensions In Millimeters	
	Min	Max		Min	Max
A	4.30	4.70	E	9.00	9.40
B	1.00	1.40	e1	2.34	2.74
b	0.70	0.90	e2	4.88	5.28
b1	1.15	1.35	L1	15.00	16.00
b2	0.40	0.60	L2	2.24	2.84
C	1.20	1.40	L3	1.20	1.60
D	9.80	10.20			

Figure2: Outline PG-T0263






Figure3: Outline PG-T0220



单位: mm

Symbol	Dimensions In Millimeters		Symbol	Dimensions In Millimeters	
	Min	Max		Min	Max
A	2.20	2.40	E	5.95	6.25
B	0.95	1.25	e1	2.24	2.34
b	0.50	0.70	e2	4.43	4.73
b1	0.45	0.55	L1	9.45	9.95
C	0.45	0.55	L2	1.25	1.75
D	6.45	6.75	L3	0.60	0.90
D1	5.10	5.50	K	0.00	0.10

Figure4: OutlinePG-T0252



UNIT	A	b	C	D	D1	D2	E	E1	E2	e	L	L1	H
mm	1.12	0.51	0.34	5.26	5.1	4.5	6.25	6	3.66	1.37	0.71	0.2	0.71
	0.9	0.33	0.11	4.7	4.7	3.56	5.75	5.6	3.18	1.17	0.35	0.06	0.35

Recommended Soldering Footprint




Figure5: Outline PG-DFN5x6

Revision History

Revision	Date	Subjects (major changes since last revision)
1.0	2021-01-21	Preliminary version
1.1	2021-02-04	Add package for TO263&TO220&DFN5x6&TO252