

Model CHT70 HIGH TEMPERATURE HCMOS CLOCK

Features

- Ceramic Surface Mount Package
- Extended-Industrial Temperature Ranges
- Fundamental and 3rd Overtone Crystal Designs
- Frequency Range 1.25 156.25MHz
- +1.8V, +2.5V, +3.3V Operation; +5.0V Limited Availability
- Output Enable Standard
- Tape and Reel Packaging, EIA-418

Applications

- Industrial IoT [IIoT]
- M2M Communication
- Industrial Controls
- Energy Industry

Part Dimensions: 7.0 × 5.0 × 1.8mm • 160.7885mg

onnect

Standard Frequencies


* See Page 6 for common frequencies. Check with factory for availability of frequencies not listed and for +5.0V operation.

- Commercial Military & Aerospace
- Test and Measurement

Description

CTS Model CHT70 is a low cost, small size, Clock Oscillator [XO] that operates over extended-industrial temperature ranges. CHT70 has an HCMOS/TTL compatible output, offers excellent stability and low jitter/phase noise performance.

Ordering Information



Notes:

1] Stability codes 2 and 7. Contact factory for availability.

Not all performance combinations and frequencies may be available. Contact your local CTS Representative or CTS Customer Service for availability.

This product is specified for use only in standard commercial applications. Supplier disclaims all express and implied warranties and liability in connection with any use of this product in any non-commercial applications or in any application that may expose the product to conditions that are outside of the tolerances provided in its specification.

DOC#008-0573-0 Rev. B

www.ctscorp.com

Page 1 of 6



Electrical Specifications

Operating Conditions

PARAMETER	AMETER SYMBOL CONDITIONS		MIN	TYP	MAX	UNIT	
Maximum Supply Voltage	V _{CC}	V _{CC} +1.8V to +3.3V	-0.5	-	4.0	V	
Supply Voltage			1.710	1.8	1.890	V	
		1 = 0/	2.375	2.5	2.665		
	V _{CC}	±5%	3.135	3.3	3.465		
			4.750	5.0	5.250		
Supply Current	Тур	cal @ Nominal Vcc, C _L = 15 pF, T _A = +2	25°C				
	I _{CC}	@ +1.8V	-	15 20	25 30	mA	
		@ +2.5V	-				
		@ +3.3V	-	35	40		
		@ +5.0V	-	35	55		
Output Load	CL	-	-	-	15	pF	
Operating Temperature	T _A	-	-55	+25	+105	°C	
			-55		+125		
Storage Temperature	T _{STG}	-	-55	-	+125	°C	

Frequency Stability

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	MAX	UNIT	
Frequency Range	f _o	- 1.25 - 156.25					
Frequency Stability [Note 1]	$\Delta f/f_{O}$	-	25,	25, 30, 50, 100 or 150			
Aging	-5	-	5	ppm			
1.] Inclusive of initial tolerance at time of shipment, changes in supply voltage, load, temperature and 1st year aging.							

Output Parameters

- V _{OH} V _{OL} I _{OH} I _{OL} SYM	- Logic '1' Level, CMOS Load Logic '0' Level, CMOS Load V _{OH} = 90%V _{CC} [1.8V, 2.5V, 3.3V, 5.0V] V _{OL} = 10%V _{CC} [1.8V, 2.5V, 3.3V, 5.0V] @ 50% Level	0.9V _{cc} - -	HCMOS - - - -	- 0.1V _{CC} -4, -4, -8, -16 +4, +4, +8, +16	- V mA
V _{ol} I _{oh} I _{ol}	Logic '0' Level, CMOS Load V _{OH} = 90%V _{CC} [1.8V, 2.5V, 3.3V, 5.0V] V _{OL} = 10%V _{CC} [1.8V, 2.5V, 3.3V, 5.0V]	-		-4, -4, -8, -16	
I _{oh} I _{ol}	V _{OH} = 90%V _{CC} [1.8V, 2.5V, 3.3V, 5.0V] V _{OL} = 10%V _{CC} [1.8V, 2.5V, 3.3V, 5.0V]	-	-	-4, -4, -8, -16	
I _{OL}	V _{OL} = 10%V _{CC} [1.8V, 2.5V, 3.3V, 5.0V]		-		mA
			-	+4, +4, +8, +16	ШA
SYM	@ 50% Level	4.5			
	C 33,3 E6161	45	-	55	%
	@ 10%/90% Levels, Nominal V _{CC} , C _L = 15pF				
	@ +1.8V	-	4	5	
T _r , T _f	@ +2.5V	-	4	5	ns
	@ +3.3V	-	7	10	
	@ +5.0V	-	7	10	
Ts	Application of V_{CC}	-	2	5	ms
	T _s	@ +3.3V @ +5.0V T _s Application of V _{CC}	@ +3.3V - @ +5.0V - T _s Application of V _{CC} -	@ +3.3V - 7 @ +5.0V - 7 T _s Application of V _{cc} - 2	@ +3.3V - 7 10 @ +5.0V - 7 10

DOC#008-0573-0 Rev. B

www.ctscorp.com



Model CHT70 HIGH TEMPERATURE HCMOS CLOCK

Electrical Specifications

Output Parameters


PARAMETER	SYMBOL CONDITIONS		MIN	ТҮР	MAX	UNIT
Enable Function	Standby					
Enable Input Voltage	V _{IH}	Pin 1 Logic '1', Output Enabled	$0.7V_{CC}$	-	-	V
Disable Input Voltage	V _{IL}	Pin 1 Logic '0', Output Standby	-	-	0.3V _{CC}	V
Enable Current	I _{STB}	Pin 1 Logic '0', Output Standby	-	-	10	μΑ
Enable Time	T _{PLZ}	Pin 1 Logic '1'	-	-	5	ms
Phase Jitter, RMS	tjrms	Bandwidth 12 kHz - 20 MHz	-	0.5	< 1	ps

Enable Truth Table


Pin 1	Pin 3
Logic '1'	Output
Open	Output
Logic 'O'	High Imp.
	0

Test Circuit





Output Waveform



DOC#008-0573-0 Rev. B


www.ctscorp.com

Page 3 of 6




Mechanical Specifications

Package Drawing



Recommended Pad Layout



Pin Assignments

Pin	Symbol	Function		
1	EOH	Enable		
2	GND	Circuit & Package		
3	Output	RF Output		
4	V _{CC}	Supply Voltage		

Marking Information

- 1. ** Manufacturing Site Code.
- 2. YYWW Date Code, YY = year, WW = week.
- 3. CHT70 CTS model.
- 4. ST Frequency stability/temperature code. [Refer to Ordering Information]
- 5. V Voltage code. M = 1.8V, N = 2.5V, L = 3.3V.
- 3. – Pin 1 identifier.
- xxxx Frequency Code; 3-digits for frequencies <100MHz, 4-digits for frequencies 100MHz or greater.

[See document 016-1454-0, Frequency Code Tables.]

Notes

- 1. Termination pads (e4). Barrier-plating is nickel [Ni] with gold [Au] flash plate.
- Reflow conditions per JEDEC J-STD-020; +260°C maximum, 20 seconds.
- 3. MSL = 1.

DOC#008-0573-0 Rev. B


www.ctscorp.com

Page 4 of 6




Model CHT70 HIGH TEMPERATURE HCMOS CLOCK

Packaging - Tape and Reel



Reel Drawing



Notes

- 1. Device quantity is 1k pieces maximum per 180mm reel.
- 2. Complete CTS part number, frequency value and date code information must appear on reel and carton labels.



Model CHT70 HIGH TEMPERATURE HCMOS CLOCK

Addendum

Common Frequencies Available – MHz

FREQUENCY	FREQUENCY CODE	FREQUENCY	FREQUENCY CODE	FREQUENCY	FREQUENCY CODE	FREQUENCY	FREQUENCY CODE
4.000000	040	24.000000	240	40.000000	400		
8.000000	080	24.576000	24C	48.000000	480		
10.000000	100	25.000000	250	50.000000	500		
12.000000	120	26.000000	260	100.000000	1000		
12.288000	122	27.000000	270	125.000000	1250		
14.318180	143	30.000000	300	156.250000	1562		
14.745600	147	32.000000	320				
16.000000	160	33.333000	33E				
20.000000	200	37.400000	374				
22.118400	221	38.400000	384				