



SOD-323



Features

- ✧ Fast switching.
- ✧ Designed for surface mount application.
- ✧ Plastic material-UL recognition flammability classification 94V-O

Applications

- ✧ Surface mount fast switching diode

Dimensions in inches and (millimeters)

Ordering Information




Type No.	Marking	Package Code
BAS16H	A6●	SOD-323

MAXIMUM RATING @ Ta=25°C unless otherwise specified

Characteristic	Symbol	Value	Unit
Continuous Reverse Voltage	V_R	75	V
Forward Continuous Current	I_F	200	mA
Peak forward surge current	I_{FSM}	500	mA
Power Dissipation	P_d	200	mW
Thermal Resistance Junction to Ambient	$R_{\theta JA}$	635	°C/W
Junction and Storage Temperature Range	T_j, T_{STG}	-55 to +150	°C

ELECTRICAL CHARACTERISTICS @ Ta=25°C unless otherwise specified

Characteristic	Symbol	Min	Max	Unit	Test Condition
Reverse Breakdown Voltage	$V_{(BR)R}$	75	-	V	$I_R=100\mu A$
Forward Voltage	V_F	-	715 855 1000 1250	mV	$I_F=1.0mA$ $I_F=10mA$ $I_F=50mA$ $I_F=150mA$
Reverse Current	I_R	-	1.0 50 30	μA	$V_R=75V$ $V_R=75V, T_J=150^\circ C$ $V_R=25V, T_J=150^\circ C$
Diode Capacitance	C_D	-	2	pF	$V_R=0, f=1.0MHz$
Forward recovery voltage	V_{FR}	-	1.75	V	$I_F=10mA, t_r=20ns$
Stored Charge	Q_S	-	45	pC	$I_F=10mA$ to $V_R=5.0V$ $R_L=500\Omega$
Reverse Recovery Time	t_{rr}	-	5	ns	$I_F=I_R=10mA, R_L=50\Omega$

TYPICAL CHARACTERISTICS @ $T_A=25^\circ\text{C}$ unless otherwise specified

Figure 2. Forward Voltage

Figure 3. Leakage Current

Figure 4. Capacitance

PACKAGE	SPQ/PCS	CARTON SPQ/PCS	CARTON SIZE/CM	CARTON GW/KG	CARTON NW/KG
SOD-323	3000/REEL	180000	44X44X22	9.00	8.00