

**High Current Chip Ferrite Bead**



◆ **Features**

- 1、 Internal silver printed layers and magnetic shielded structures to minimize crosstalk
- 2、 Large withstand current (allowable current:up to 6A)
- 3、 Can be used in a wide range of frequency to suppress EMI
- 4、 Three types material and wide range of impedance values for various applications
- 5、 RoHS Compliant.



◆ **Application**

- 1、 High current DC power lines.
- 2、 Noise suppression for power line or large current signal of electric equipments such as computers and peripheral devices, DVD cameras, LCD TVs, communication equipments, OA equipments, etc.


◆ **PRODUCT IDENTIFICATION**

**CMBH 1608 S 601 J S P**  
**(1) (2) (3) (4) (5) (6) (7)**

- (1) Series Type
- (2) Chip Size (mm) :Length X Width
- (3) Material Code
- (4) Nominal Impedance:600=60Ω;601=600Ω;  
102=1000Ω
- (5) Rated Current: E=300mA;F=500mA;J=800mA  
L =1000mA; M=1500mA;  
N=2000mA; P=2500mA;  
Q=3000mA; R=4000mA;  
U=5000mA W=6000mA.
- (6) Company Code
- (7) Packaging:P–Embossed paper tape, 7" reel  
E- Embossed plastic tape, 7" reel

◆ **Dimensions Unit: mm**

Size(EIA)	L	W	T	E
<b>1608(0603)</b>	1.60±0.15	0.88±0.15	0.80±0.15	0.30±0.20




◆ Specifications

Part Number	Impedance (Ω)	Test Freq. (MHz)	DCR Max. (Ω)	Rated Current (mA)
<b>CMBH1608S Series</b>				
CMBH1608S100QSP	10±25%	100	0.040	3000
CMBH1608S300QSP	30±25%	100	0.040	3000
CMBH1608S600QSP	60±25%	100	0.040	3000
CMBH1608S900QSP	90±25%	100	0.040	3000
CMBH1608S121QSP	120±25%	100	0.070	3000
CMBH1608S181NSP	180±25%	100	0.080	2000
CMBH1608S221NSP	220±25%	100	0.090	2000
CMBH1608S301LSP	300±25%	100	0.110	1000
CMBH1608S471LSP	470±25%	100	0.150	1000
CMBH1608S601LSP	600±25%	100	0.200	1000
CMBH1608S102LSP	1000±25%	100	0.300	1000
CMBH1608S152FSP	1500±25%	100	0.400	500

◆ General Technical Data

<b>Operating Temperature Range</b>	-55°C ~ +125°C
<b>Storage Condition</b>	Less than 40°C and 70% RH
<b>Soldering Method</b>	Reflow or Wave Soldering


◆ Recommended Soldering Conditions




◆ Characteristics

**CMBH1608S TYPE**


CMBH1608S100QSP




CMBH1608S300QSP




CMBH1608S600PSP




CMBH1608S900PSP C




MBH1608S121NSP




CMBH1608S181MSP




CMBH1608S221MSP




CMBH1608S301LSP




CMBH1608S471LSP




CMBH1608S601LSP



CMBH1608S102LSP



CMBH1608S152FSP



◆ Package

Size EIA (EIA)	1005 (0402)	1608 (0603)	2012 (0805)	3216 (1206)	4532 (1812)
Standard Packing Quantity (pcs / reel)	10,000	4,000	4,000	4,000	1,000