

SEA & LAND ELECTRONIC CORP.

WWW.SEALAND-PPTC.COM



ALPHA-TOP TECHNOLOGY CORP.

APPROVAL SHEET

MODEL NO.:	mSMD110-24V	
CUSTOMER:		
CUSTOMER'S APPROVA		
CUSTOMER S APPROVA	L:	
AUTHORIZED SIGNATUR	RE/STAMP:	
DATE		

MANUFACTURER:

HEAD OFFICE:

13F.,No.120-10,Sec.3,Zhongshan Rd.,Zhonghe Dist.,New Taipei City 23544,Taiwan

Tel: 886-2-8221-2567 Fax:882-2-2225-7268

E-mail:service@chipfast.com.tw

China Branch:

Factory Building B)Shuangpeng,Weibu Village, Qiuchang Town, Huiyang District, Huizhou City, Guangdong Province, P.R.C.)

Tel: 86-752-3562001 Fax:86-752-3558696 E-mail:service@atpptc.com

Submitted by: Chung Cheng Approved by: YC Lin DATE: 2-Mar-22

SEA & LAND ELECTRONIC CORP.



mSMD110-24V

Ensturne

■ Surface Mount Devices

■ Lead free device

■ Size 4.5*3.2 mm/0.18*0.12 inch
■ Surface Mount packaging

for automated assembly

Applications

Almost anywhere there is a low voltage power supply, up to 60V and a load to be

protected, including:

■ Computer mother board, Modem. USB hub■ PDAs & Charger, Analog & digital line card

■ Digital cameras, Disk drivers, CD-ROMs,

Alpha-Top (Sea & Land Alliance)

Performance Specification

						Maxi	mum	Resis	tance		
Model	V_{max}	I _{max}	I _{hold}	I _{trip}	P_d	Time 1	To Trip			Agency	Approval
Model			@25°C	@25°C	Тур.	Current	Time	Ri_{min}	R1 _{max}	UL	TUV
	(Vdc)	(A)	(A)	(A)	(W)	(A)	(Sec)	(Ω)	(Ω)	UL	100
mSMD110-24V	24	100	1.10	2.20	8.0	8.0	0.30	0.050	0.250		√

Ihold = Hold Current. Maximum current device will not trip in 25°C still air.

Itrip = Trip Current. Minimum current at which the device will always trip in 25°C still air.

Vmax = Maximum operating voltage device can withstand without damage at rated current (Imax).

Imax = Maximum fault current device can withstand without damage at rated voltage (Vmax).

Pd = Power dissipation when device is in the tripped state in 25°C still air environment at rated voltage.

Rimin/max = Minimum/Maximum device resistance prior to tripping at 25°C.

R1_{max} = Maximum device resistance is measured one hour post reflow.

CAUTION: Operation beyond the specified ratings may result in damage and possible arcing and flame.

Environmental Specifications

Test	Conditions	Resistance change
Passive aging	+85°C, 1000 hrs.	±5% typical
Humidity aging	+85°C, 85% R.H., 168 hours	±5% typical
Thermal shock	+85°C to -40°C, 20 times	±33% typical
Resistance to solvent	MIL-STD-202,Method 215	No change
Vibration	MIL-STD-202,Method 201	No change
Ambient operating conditions : - 40 °C to +85 °C		
Maximum surface temperature of the device in the	ne tripped state is 125 °C	

Agency Approvals :

R 50481056

Regulation/Standard:

Pto RoHS

2015/863/EU

HF

EN14582


I_{hold} Versus Temperature

Model	Maximum ambient operating temperature (T _{mao}) vs. hold current (I _{hold})									
	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C	
mSMD110-24V	1.60	1.45	1.28	1.10	0.92	0.83	0.71	0.66	0.52	

Construction And Dimension (Unit:mm)

Model	,	A		В			D	E
Model	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Min.
mSMD110-24V	4.37	4.73	3.07	3.41	0.60	1.60	0.30	0.25

Dimensions & Marking



Recommended Pad Layout (mm) 1.78 ±0.1 **1.78**±0.1


Termination Pad Characteristics


Terminal pad materials : Tin-plated Nickel-Copper

Terminal pad solderability: Meets EIA specification RS186-9E and ANSI/J-STD-002 Category 3.


Rework

Use standard industry practices, the removal device must be replaced with a fresh one.





Typical Time-To-Trip At 25°C




!\ WARNING:

- Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.

 PPTC are intended for protection against occasional over current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are
- · Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.

 · Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC.
- Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.
- Contamination of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices. PPTC SMD can be cleaned by standard methods.

mSMD110-24V




- Recommended reflow methods : IR, vapor phase oven, hot air oven.
- Devices are not designed to be wave soldered to the bottom side of the board.
- · Recommended maximum paste thickness is 0.25 mm (0.010 inch).
- Devices can be cleaned using standard method and solvents.

Note: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.


Tape And Reel Specifications (mm)

	=14.404.4
Governing Specifications	EIA 481-1
W	12 ± 0.3
P0	4.0 ± 0.10
P1	8.0 ± 0.10
P2	2.0 ± 0.05
A0	3.5 ± 0.23
B0	5.1 ± 0.15
B1max.	5.9
D0	1.5 + 0.1, -0
F	5.5 ± 0.05
E1	1.75 ± 0.10
E2min.	10.25
Tmax.	0.6
T1max.	0.1
K0	0.9 ± 0.15
Leader min.	390
Trailer min.	160
Reel Dimensions	
A max.	178
N min.	60
W1	12.4 + 2.0, -0.0
W2max.	18.4

EIA Tape Component Dimensions



EIA Reel Dimensions



Storage And Handling

- Storage conditions : 40°C max, 70% R.H.
- Devices may not meet specified performance if storage conditions are exceeded.

Order Information Packaging

mSMD	'110 -24V	Tape & Reel Quantity
Product name	Hold	
Size 4532mm/1812 inch	Current	1,500 pcs/reel
SMD : surface mount device	1.10A	

Tape & reel packaging per EIA481-1

Labeling Information

