LTR33xx

Low-Drift, Low-Power, Small-Footprint Series Voltage Reference

#### **General Description**


The LTR33 series devices are low temperature drift (20 ppm/°C maximum), low-power, high-precision CMOS voltage reference, featuring  $\pm 0.1\%$  initial accuracy, low operating current with power consumption less than 500 µA. This device also offers very low output noise of 15  $\mu V_{PP}/V$ , which enables its ability to maintain high signal integrity with high-resolution data converters in noise critical systems.

Packaged in the same SOT-23-3 package, LTR33xx offers enhanced specifications and pin-to-pin replacement for REF33xx and LM4132. Stability and system reliability are further improved by the low output-voltage hysteresis of the device and low long-term output voltage drift. LTR33xx is specified for the wide temperature range of -40 to +125°C

#### **Features and Benefits**


- Voltage options: 1.25 V, 2.048 V, 2.5 V, 3.0 V, 3.3 V, 4.096 V
- Initial accuracy: ±0.1% (maximum)
- Low temperature coefficient: 20 ppm/°C (maximum)
- Output 1/f noise at 0.1 to 10 Hz: 15  $\mu V_{PP}/V$
- Supply voltage: 2.7 to 5.5 V
- Power consumption: < 500 μA</li>
- Start-up time: < 400 μs</li>
- Operating temperature: -40 to 125°C
- Output Current: ± 5 mA

### Pin Configuration



# **Applications**

- Data acquisition (DAQ)
- PLC analog I/O modules
- Field transmitters
- Motor drive control module
- Battery test equipment
- LCR meters





# **Pin Description**

Pin. Name	Pin Description
VIN	Power supply voltage
GND	Ground.
REF	Reference voltage outputs , an external capacitor is required.

# Ordering Information <sup>(1)</sup>

Type Number	Output Voltage Quantity		Operating Temperature	Package Name	Marking Code	
LTR3312T20YT3	1.25 V	3000	-40 to 125°C	SOT-23-3	<b>3AXXX</b>	
LTR3320T20YT3	2.048 V	3000	–40 to 125°C	S0T-23-3	3BXXX	
LTR3325T20YT3	2.5 V	3000	–40 to 125°C	S0T-23-3	3CXXX	
LTR3330T20YT3	3.0 V	3000	–40 to 125°C	S0T-23-3	3DXXX	
LTR3333T20YT3	3.3 V	3000	–40 to 125°C	S0T-23-3	3EXXX	
LTR3340T20YT3	4.096 V	3000	–40 to 125°C	S0T-23-3	3FXXX	

(1) Please contact to your Linearin representative for the latest availability information and product details.

### Limiting Value - In accordance with the Absolute Maximum Rating System (IEC 60134).

Operating Ambient Temperature Range	-40 to 125°C
Storage Temperature Range	–50 to 125°C
Input Voltage Range	-0.3 V to 5.5 V
ESD protection	> 3000 V

Note: Stresses exceeding those listed in the Maximum Rating table may damage the device. Operation beyond the maximum Rating conditions or under harsh conditions may affect product reliability and function.

# **Recommended Operating Conditions**


Parameter	Symbol	Symbol Min.		Max.	Unit
Supply input voltage	V <sub>IN</sub>	V <sub>OUT</sub> +0.2		5.5	V
Output current range	I <sub>cc</sub>	-5		5	mA



Electrical	Charact	teristics
Licotificat	onarae	

Parameter	Symbol	Description	Min.	Тур.	Max.	Unit
Power supply voltage	V <sub>IN</sub>		2.7	5	5.5	V
Power consumption	I <sub>cc</sub>	V <sub>cc</sub> = 5.0 V, no load.		300	500	μA
		LTR3312		1.25		V
		LTR3320		2.048		V
		LTR3325		2.5		V
Output voltage	V <sub>OUT</sub>	LTR3330		3.0		V
		LTR3333		3.3		V
		LTR3340		4.096		V
Output voltage accuracy	ΔV <sub>OUT</sub>		-0.1		0.1	%
Output Noise	Vnoise	0.1 to 10 Hz		15		μVpp/V
Temperature coefficient	T <sub>c</sub>	-40 to 125°C			20	ppm/ºC
Dropout Voltage	V <sub>IN</sub> -V <sub>OUT</sub>			200		mV
Line Regulation	$\Delta V_{OUT} / \Delta V_{IN}$				100	ppm/V
Load Regulation	$\Delta V_{OUT} / \Delta I_L$				50	ppm/mA
Thermal hysteresis	dT			80		ppm
Long-term stability		0h to 1000h at 25°C		200		ppm
Short-circuit current	I <sub>sc</sub>	Souring and sinking		50		mA
Capacitive load			0.1		10	μF
Turn-on setting time					400	μs

# **Typical Application**





### P-4

### Layout


#### Layout Guidelines

For optimal performance of this design, please follow standard printed circuit board (PCB) layout guidelines, including proper decoupling close to all integrated circuits and adequate power and ground connections with large copper pours.

As shown below an example of a PCB layout for a data acquisition system using the LTR33xx.

Some key considerations are:

- Connect a low-ESR, 1 µF ceramic capacitor at the IN pin for bypass, and a 0.1 uF to 10 uF ceramic capacitor at the OUT pin for stability of the LTR33xx.
- Decouple other active devices in the system per the device specifications.
- Use a solid ground plane helps distribute heat and reduces EMI noise pickup.
- Place the external components as close to the device as possible. This configuration prevents parasitic errors (such as the Seebeck effect) from occurring.
- Minimize trace length between the reference and bias connections to the ADC to reduce noise pickup
- Do not run sensitive analog traces in parallel with digital traces. Avoid crossing digital and analog traces if
  possible, and only make perpendicular crossings when absolutely necessary.




#### Layout Example






### Tape and Reel Information



#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIETATION IN TAPE



#### \* All dimensions are nominal


Device	Package Type	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin 1 Quadrant
LTR3312T20YT3	SOT23	3	3 000	178	9.0	3.3	3.2	1.5	4.0	8.0	Q3





# Package Outlines

#### DIMENSIONS, SOT-23-3



(Unit: mm)



CAUTION: These devices are sensitive to electrostatic discharge; follow proper IC Handling Procedures. Linearin and designs are registered trademarks of Linearin Technology Corporation. © Copyright Linearin Technology Corporation. All Rights Reserved.

θ

θ1

٥°

5°

4°

10°

8°

15°

All other trademarks mentioned are the property of their respective owners.