


RoHS 2.0

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A0		新版发行	20/04/08	Yang
A1		重新核对图面	20/12/29	LiHui



NOTES:

1. MATERIAL:
  - 1.1. HOUSING: LCP ,COLOR IS BLUE,HIGH TEMPERATURE PLASTIC;
  - 1.2. CONTACT: BRASS(H65 T=0.20&0.25mm);
  - 1.3. SHELL: COLD ROLLED IRON (SPCC T=0.30mm);
2. ELECTRICAL:
  - 4.1. VOLTAGE RATING: 30V DC ;
  - 4.2. CURRENT RATING: 1.5A ;
  - 4.3. CONTACT RESISTANCE: 30MILLIOHMS MAX.;
  - 4.4. WITHSTAND VOLTAGE: 100V AC RMS 50(60)Hz,1MIN.;
  - 4.5. INSULATION RESISTANCE: 100MEGOHMS MIN @500V DC;
5. MECHANICAL:
  - 5.1. MATING FORCE: 35N MAX.;
  - 5.2. UNMATING FORCE: 5~35N ;
  - 5.3. OPERATING LIFE: 1500 CYCLES MIN.;
6. PLATING:
  - 6.1. TERMINAL:
    - NI PLATING OVER ALL,
    - Tin PLATING ON SOLDER AREA,
    - Au G/Fu" ON CONTACT AREA;
  - 6.2.SHELL: NI PLATING OVER ALL;
7. ENVIRONMENTAL:
  - 7.1. STORAGE TEMPERATURE RANGE: -40°C~+85°C;
  - 7.2. OPERATION TEMPERATURE RANGE: -25°C~+70°C;

富 港 电 子					
UNLESS OTHERWISE GENERAL TOLERANCE:		NAME:		P/N:	
X.xxx ±0.10	X.xx ±0.20	3.0 A母180° L13.7平口弯脚		ST-003-03-J	
X.x ±0.30	X ±0.35	THIRD ANGLE PROJECTION		DWG NO:	REV.
ANGULAR:		DRAWN:		CHECKED:	APPROVED:
X.xx° ±1°	X.x° ±3°	UNIT: MM		SCALE: 1:1	SIZE: A4
X° ±5°		SHEET: 1/1		REV. A1	