

1 |

2 |

3 |

4 |




P/N LEGEND

A2004 WRA-2XNP XXX





① ② ③ ④



① Series No.
 ② Connector type: WRA=Right angle A type
 ③ No. of circuits
 ④ Option code:
 Blank=Standard

SPECIFICATIONS
 Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max.
 Insulation Resistance: 1000MΩ Min.
 Withstanding Voltage: 800V AC/minute
 Pin Material: Brass/Gold-flash
 Material: Nylon 6T,UL94V-0
 Color: Natural(Beige)



Circuit No.	Dimensions			
	A	B	C	D
2X02P	2.00	8.00	4.70	---
2X03P	4.00	10.00	6.70	2.00
2X04P	6.00	12.00	8.70	4.00
2X05P	8.00	14.00	10.70	6.00
2X06P	10.00	16.00	12.70	8.00
2X07P	12.00	18.00	14.70	10.00
2X08P	14.00	20.00	16.70	12.00
2X09P	16.00	22.00	18.70	14.00
2X10P	18.00	24.00	20.70	16.00
2X11P	20.00	26.00	22.70	18.00
2X12P	22.00	28.00	24.70	20.00
2X13P	24.00	30.00	26.70	22.00
2X14P	26.00	32.00	28.70	24.00
2X15P	28.00	34.00	30.70	26.00
2X16P	30.00	36.00	32.70	28.00
2X17P	32.00	38.00	34.70	30.00
2X18P	34.00	40.00	36.70	32.00
2X19P	36.00	42.00	38.70	34.00
2X20P	38.00	44.00	40.70	36.00



 燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.			
UNIT	SCALE	SHEET	TITLE:
mm	1 : 1	1 of 1	2.00mm PITCH 90° WAFER-LOCK TYPE
DRAWN BY	APPROVED BY		
歐陽小強 2006.10.27	董正一 2006.10.27		
GENERAL TOLERANCE			
X. X±0.25		ANGLE±	
X. XX±0.15			
X. XXX±0.05			
A2	EN1112050511	2011.12.05	陳錦展
REV.	DESCRIPTION	DATE	NAME
DRAW NO. : A2004WRA-2XNP			REV. A2

1 |

2 |

3 |

4 |