



P/N LEGEND

A2501				WV-XP		X	
①	②	③	④	①	②	③	④
① Series No.							
② Connector type: WV=Vertical							
③ No. of circuits							
④ Option code:							
1=Type 1, Nylon 66,UL94V-0, Natural(White)							
2=Type 2, Nylon 66,UL94V-0, Natural(White)							
3=Type 3, Nylon 66,UL94V-0, Natural(White)							
RNNT1NK0G=Type 1, Natural							
Nylon 66,UL94V-2, No flame							

SPECIFICATIONS

Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1000V AC/minute
 Pin Material: Brass/Tin-plated

Circuit No.	Dimensions		Circuit No.	Dimensions	
	A	B		A	B
02P	2.50	7.50	12P	27.50	32.50
03P	5.00	10.00	13P	30.00	35.00
04P	7.50	12.50	14P	32.50	37.50
05P	10.00	15.00	15P	35.00	40.00
06P	12.50	17.50	16P	37.50	42.50
07P	15.00	20.00	17P	40.00	45.00
08P	17.50	22.50	18P	42.50	47.50
09P	20.00	25.00	19P	45.00	50.00
10P	22.50	27.50	20P	47.50	52.50
11P	25.00	30.00			

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.			
UNIT		SCALE		SHEET		TITLE:	
mm		1 : 1		1 of 1		2.50mm PITCH 180° WAFER	
DRAWN BY		APPROVED BY					
李勤		董正一					
2006.05.17		2006.05.17				DRAW NO. : A2501WV-XPX	
GENERAL TOLERANCE							
A3		EN1511090004		2015.11.09		郭木恩	
A2		EN1401240004		2014.01.22		郭木恩	
REV.		DESCRIPTION		DATE		NAME	
		X.X±0.25		ANGLE±		REV. A3	
		X.XX±0.15					
		X.XXX±0.05					