

# Aluminum Electrolytic Capacitor

## KN series

# KFSON

- ◆ Load life 2000 Hrs at 105°C
- ◆ RoHS Compliant




### Specifications 規格表

Ltem 項目	Performance Characteristics 特性參數								
Operating Temperature Range 工作溫度範圍	-40 to +105°C	-25 to +105°C							
Rated Voltage Range 額定電壓範圍	16 to 100 VDC	160 to 500 VDC							
Capacitance Range 容量範圍	68 to 56000 µF								
Capacitance Tolerance 靜電容量偏差	±20% (120Hz, +20°C)								
Leakage Current 漏電流	After 5 minutes at 20° C application of rated voltage, leakage current is not more than 0.01CV or 1.5mA, whichever is smaller C: Nominal Capacitance(µF) V: Rated Voltage(V)								
Dissipation Factor 損耗角正切值 tan δ (%)	rated voltage (V)	16 25 35 50 63 100 160-400 450-500							
	tan δ (Max)	50 40 40 30 20 20 15 20							
Low Temperature Characteristics 低溫特性	impedance ratio max 電容器最大阻抗比值								
	rated voltage (V)	16	25	35	50	63	100	160-400	450-500
	Z(-25°C)/Z(+20°C)	4	4	4	4	4	4	4	8
	Z(-40°C)/Z(+20°C)	15	15	15	15	15	15	-	-
Load Life 使用壽命	105°C施加額定工作電壓2000小時，經恢復後，產品性能應滿足以下要求 The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated ripple current is applied for 2000H at 105°C								
	Capacitance change	≅ ±20% of the initial value							
	D. F. (tan δ)	≅ 200% of the specified value							
	Leakage current	≅ The specified value							
Shelf Life 存儲特性	105°C放置1000小時，經恢復後20°C后，產品性能應滿足以下要求 The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1000 hours at 105°C without voltage applied.								
	Capacitance change	≅ ±20% of the initial value							
	D. F. (tan δ)	≅ 150% of the specified value							
	Leakage current	≅ The specified value							

### Diagram of Dimensions 外形尺寸圖 (mm)

●Standard Terminal Type : S (Φ22 ~ Φ35)



# Aluminum Electrolytic Capacitor

## KN series



### Frequency Coefficient

Frequency Voltage (v)	50/60 Hz	120 Hz	300 Hz	1K Hz	10K Hz	≥50K Hz
≤100V	0.95	1.00	1.07	1.13	1.19	1.20
160-250V	0.87	1.00	1.17	1.32	1.45	1.50
≥350	0.80	1.00	1.16	1.30	1.41	1.43

### Standard Ratings

Rated Voltage	Rated Capacity	Size φD*L	Rated ripple current
V	μF	mm	A
16V	3300	22*26	1.17
		22*26	1.53
	4700	25*26	1.55
		22*31	2.02
	6800	25*26	2.02
		30*26	2.02
	8200	22*31	2.20
	10000	22*31	2.79
			25*26
		30*26	2.81
	12000	22*36	3.06
		30*26	3.06
	15000	22*41	3.24
			25*36
		30*26	3.24
			35*32
	18000	22*51	3.54
			25*46
		30*36	3.51
			35*32
	22000	25*51	4.25
		30*36	4.08
			35*32
	27000	25*51	4.30
		30*41	4.30
			35*32
	33000	30*46	4.83
		35*37	4.83
39000	30*51	5.78	
	35*42	5.78	
47000	35*45	6.32	
56000	35*47	6.48	

Rated Voltage	Rated Capacity	Size φD*L	Rated ripple current
V	μF	mm	A
25V	3300	22*26	1.48
		25*26	1.48
	4700	22*26	1.88
		25*26	1.90
	6800	22*31	2.60
		25*26	2.60
	8200	30*26	2.60
		22*36	3.14
	8200	25*31	3.14
			30*26
		30*26	3.14
	10000	22*41	3.50
			25*36
		30*31	3.50
			35*27
	12000	22*46	4.02
			25*41
		30*31	4.02
			35*27
	15000	25*46	4.58
		30*36	4.58
			35*32
	18000	25*51	4.82
		30*41	4.82
			35*32
	22000	30*46	5.12
		35*37	5.12
			27000
33000	35*52	6.09	
39000	35*52	6.20	
47000	35*52	6.30	

Rated ripple current (A,rms) at 105°C, 120Hz

# Aluminum Electrolytic Capacitor

## KN series

# KFSON

### Standard Ratings

Rated Voltage	Rated Capacity	Size φ D*L	Rated ripple current
V	μ F	mm	A
35V	1500	22*26	1.26
	2200	22*26	1.35
		25*26	1.45
	2700	22*26	1.55
		25*26	1.65
	3300	22*26	1.80
		25*26	1.90
	4700	22*36	2.42
		25*26	2.30
		30*26	2.54
	6800	22*41	3.24
		25*36	3.24
		30*26	3.21
		35*27	3.24
	10000	25*46	3.96
		30*36	3.96
		35*27	3.75
	12000	25*51	4.21
		30*41	4.21
		35*32	4.21
15000	30*46	4.69	
	35*37	4.69	
22000	35*52	5.50	
27000	35*52	5.80	
	35*45	5.60	
33000	35*52	5.90	

Rated Voltage	Rated Capacity	Size φ D*L	Rated ripple current
V	μ F	mm	A
50V	1500	22*26	1.10
		25*26	1.02
	2200	22*31	1.65
		25*26	1.65
	2700	22*31	1.85
		25*26	1.85
		30*26	1.95
	3300	22*36	2.24
		25*31	2.24
		30*26	2.24
		22*46	2.95
	4700	25*36	2.80
		30*31	2.95
		35*27	2.95
		25*46	3.23
	6800	30*41	3.20
		35*32	3.26
		30*46	3.58
	8200	35*37	3.58
		30*51	4.11
10000	30*45	4.01	
	35*42	4.11	
	30*40	4.00	
	25*50	3.90	
	35*30	3.86	
15000	35*52	5.05	
18000	35*52	5.30	
22000	35*60	5.50	

Rated ripple current (A,rms) at 105°C, 120Hz

# Aluminum Electrolytic Capacitor

## KN series

### Standard Ratings

Rated Voltage	Rated Capacity	Size φ D*L	Rated ripple current
V	μ F	mm	A
63V	820	22*26	0.75
	1000	22*26	0.85
		25*26	0.85
	1500	22*26	1.10
		25*26	1.12
		30*26	1.14
	1800	22*31	1.40
		25*26	1.40
	2200	22*36	1.65
		25*31	1.65
		30*26	1.65
	2700	22*41	2.07
		25*36	2.07
		30*26	2.07
	3300	22*46	2.46
		25*36	2.40
		30*31	2.48
		35*27	2.48
	3900	25*41	2.92
		30*36	3.05
		35*27	3.05
	4700	25*51	3.43
		30*41	3.43
		35*32	3.43
	5600	30*46	3.86
		35*37	3.86
	6800	30*51	4.64
35*42		4.64	
8200	35*47	5.05	
10000	35*52	5.75	
	30*60	5.65	
	30*50	5.35	
15000	35*52	5.40	
	35*60	5.56	

Rated ripple current (A,rms) at 105°C, 120Hz

Rated Voltage	Rated Capacity	Size φ D*L	Rated ripple current
V	μ F	mm	A
100V	330	22*26	0.54
	470	22*26	0.79
		25*26	0.81
	560	22*26	0.90
		25*26	0.95
	680	22*31	1.02
		25*26	1.02
		30*26	1.14
	820	22*31	1.26
		25*26	1.26
		30*26	1.32
	1000	22*36	1.38
		25*31	1.38
		30*26	1.38
	1200	22*41	1.65
		25*36	1.65
		30*31	1.65
	1500	22*46	1.83
		25*41	1.83
		30*31	1.83
	1800	30*31	1.83
		25*41	2.52
		30*36	2.52
	2200	35*32	2.52
		25*51	3.03
		30*41	3.03
	2700	35*32	3.03
		30*46	4.10
	3300	35*37	4.10
		30*56	4.59
	3900	35*47	4.59
		35*47	4.98
	4700	35*52	5.03
35*40		4.80	
30*50		4.65	
5600	35*60	5.10	
5600	35*52	5.09	
6800	35*60	5.20	

# Aluminum Electrolytic Capacitor

## KN series



### Standard Ratings

Rated Voltage	Rated Capacity	Size φD*L	Rated ripple current
V	μF	mm	A
160V	220	22*26	0.42
	330	22*31	0.98
		25*26	0.98
		30*26	1.00
	470	22*36	1.21
		25*31	1.21
		30*26	1.21
	560	22*31	1.15
		22*41	1.40
		25*36	1.40
		30*31	1.40
	680	35*27	1.40
		22*46	1.64
		25*36	1.58
		30*31	1.65
	820	35*27	1.71
		22*36	1.49
		25*41	1.76
	1000	30*36	1.85
		35*32	1.85
		25*51	2.15
	1200	30*41	2.15
		35*32	2.15
		25*56	2.46
	1500	30*46	2.46
		35*37	2.46
	1800	30*51	2.80
35*42		2.80	
2200	30*51	3.13	
	35*42	3.13	
3300	35*52	3.26	
	35*42	3.18	
3300	35*52	3.50	
	35*45	3.35	
200V	330	22*36	1.21
		25*31	1.21
		30*26	1.21
	390	22*36	1.33
		25*31	1.34
30*31	1.45		

Rated Voltage	Rated Capacity	Size φD*L	Rated ripple current
V	μF	mm	A
200V	470	22*41	1.57
		25*36	1.59
		30*31	1.65
		35*27	1.65
		22*30	1.55
		22*36	1.65
		25*30	1.65
	560	22*46	1.81
		25*41	1.85
		30*31	1.85
		35*27	1.85
	680	22*51	2.04
		25*46	2.07
		30*30	2.04
		35*32	2.17
		25*35	2.00
		25*30	1.98
	820	22*40	2.00
		25*51	2.30
		30*35	2.30
		35*37	2.31
		25*40	2.20
	1000	25*45	2.25
		22*50	2.20
		30*40	2.62
		35*37	2.62
		25*45	2.55
		25*40	2.51
	1000	35*30	2.50
		25*50	2.55
30*30		2.45	
30*35		2.51	
30*50		3.00	
1200	35*42	3.00	
	35*47	3.28	
1500	35*50	4.01	
	35*50	4.10	
2200	30*50	3.85	
	35*50	4.10	
2700	35*50	4.10	
	35*45	3.80	

Rated ripple current (A,rms) at 105°C, 120Hz

# Aluminum Electrolytic Capacitor

## KN series

# KFSON

### Standard Ratings

Rated Voltage	Rated Capacity	Size φ D*L	Rated ripple current
V	μ F	mm	A
250V	220	22*36	1.00
		25*31	1.00
		22*30	0.95
	330	22*46	1.28
		25*36	1.28
		30*31	1.28
	390	35*27	1.28
		22*46	1.48
		30*31	1.48
	470	35*27	1.48
		25*41	1.76
		30*36	1.76
	470	35*32	1.76
		25*30	1.56
		25*35	1.60
		22*36	1.56
		30*30	1.68
		22*40	1.68
	560	25*51	1.93
		30*41	1.93
		35*32	1.93
	680	25*40	2.15
		30*46	2.22
		35*37	2.22
		30*51	2.48
		22*45	2.15
	820	30*35	2.20
		25*45	2.46
		30*35	2.43
		30*51	2.48
		35*42	2.48
		25*40	2.20
	1000	35*30	2.25
		30*50	2.74
		30*40	2.65
		35*47	2.80
	1200	30*45	2.70
		35*50	3.00
		35*55	3.00
	1500	35*50	3.50
		35*55	3.50
	2200	35*55	5.00
35*60		5.10	
35*70		5.10	

Rated Voltage	Rated Capacity	Size φ D*L	Rated ripple current
V	μ F	mm	A
400V	100	22*36	0.82
		25*31	0.82
		22*25	0.70
		25*25	0.80
	120	22*36	0.90
		25*31	0.90
		22*25	0.80
		25*25	0.85
	150	22*41	0.98
		25*36	0.98
		30*31	0.95
		35*27	0.95
		22*30	0.90
	180	25*25	0.90
		25*36	1.05
	220	30*30	1.21
		30*41	1.21
		25*40	1.21
		25*35	1.21
		35*32	1.21
		22*40	1.10
		25*30	1.10
	270	30*25	1.10
		30*40	1.40
		25*40	1.30
		30*35	1.30
	330	30*40	1.57
		35*30	1.57
		22*45	1.50
		25*40	1.50
		30*35	1.50
		35*35	1.60
	390	30*40	1.68
		35*42	1.71
	470	35*45	1.94
		25*50	1.80
		30*40	1.80
		35*35	1.80
		30*50	1.85
		30*45	1.85
		35*40	1.85
	35*50	1.98	

Rated ripple current (A,rms) at 105°C, 120Hz

# Aluminum Electrolytic Capacitor

## KN series

### Standard Ratings

Rated Voltage	Rated Capacity	Size φD*L	Rated ripple current	
V	μF	mm	A	
400V	560	35*50	2.23	
		30*45	2.23	
		35*45	2.40	
		35*40	2.40	
	680	35*62	35*62	2.85
			35*50	2.83
		35*45	35*45	2.80
			30*50	2.70
	820	35*40	35*40	2.65
			35*62	2.90
			35*45	2.83
	1000	35*50	35*50	2.85
			35*70	3.20
			35*65	3.15
	1200	35*60	35*60	3.15
			35*50	3.10
35*70			3.30	
450V	82	35*70	3.30	
		35*65	3.30	
		35*60	3.30	
	100	22*36	22*36	0.64
			25*31	0.64
			30*26	0.64
		22*41	22*41	0.74
			25*31	0.74
			30*31	0.74
			22*25	0.70
	22*35	22*35	0.72	
		25*25	0.72	
		22*46	0.82	
		25*36	0.82	
		30*31	0.82	
	120	22*30	22*30	0.80
25*25			0.80	
25*30			0.80	
30*25		30*25	0.80	
		22*51	0.96	
150	25*41	25*41	0.96	
		30*36	0.96	
	35*27	35*27	0.96	
		22*30	0.90	

Rated Voltage	Rated Capacity	Size φD*L	Rated ripple current	
V	μF	mm	A	
450V	150	22*35	0.90	
		25*30	0.90	
		25*35	0.95	
		30*25	0.95	
		30*30	0.95	
		25*46	1.14	
	180	30*36	30*36	1.10
			35*32	1.14
			30*41	1.24
	220	35*37	35*37	1.24
			22*40	1.20
			25*40	1.20
			25*50	1.20
			30*30	1.20
	270	30*51	30*51	1.48
			35*42	1.48
	330	30*40	30*40	1.60
			30*50	1.64
			25*50	1.60
		30*35	30*35	1.60
			35*30	1.60
			35*40	1.80
	390	35*52	35*52	1.86
			35*35	1.65
			35*50	1.90
	470	35*45	35*45	1.90
			30*50	1.90
			30*60	1.90
			35*50	2.40
	560	35*45	35*45	2.40
35*40			2.40	
30*50			2.40	
35*60		35*60	2.90	
		35*55	2.85	
680	35*50	35*50	2.85	
		35*45	2.80	
	30*55	30*55	2.80	
		35*70	3.20	
820	35*65	35*65	3.20	
		35*60	3.20	
		35*70	3.30	
1000	35*65	35*65	3.30	
		35*80	3.60	

Rated ripple current (A,rms) at 105°C, 120Hz

# Aluminum Electrolytic Capacitor

## KN series

**KFSON**

### Standard Ratings

Rated Voltage	Rated Capacity	Size ΦD*L	Rated ripple current
V	μF	mm	A
500V	100	22*40	0.90
		22*45	0.94
		25*40	0.94
		30*30	0.94
	120	25*40	0.94
		30*30	0.94
		35*25	0.94
	150	25*40	1.10
		30*35	1.13
		35*30	1.13
	180	25*50	1.39
		30*40	1.40
	220	30*40	1.50
		30*45	1.60
		35*35	1.60
		35*40	1.60
	270	30*50	1.70
		35*40	1.70
	330	30*55	2.10
		30*60	2.10
		35*50	2.10
	390	35*55	2.50
		35*50	2.47
	470	35*55	2.60
		35*60	2.65
	680	35*70	3.10
		35*60	2.90
820	35*80	3.80	
	40*70	3.80	
1000	40*80	4.70	

Rated ripple current (A,rms) at 105°C, 120Hz