# 規格承認書

### PECIFICATION FOR APPROVAL

客 戶								
CUSTOMER	:	立创						
項目								
ITEM	:	电磁无源一体蜂鸣	內器 (外部	驱动)				
型號								
TYPE	:	GMC25125YB-2	25R800					
描述								
DESCRIPTION	: _	ф 25.0 x 12.5mm	800Hz	$25 \Omega$	≥85DB	PBT 材质	P=10.2mm	
客戶料號								
CUSTOMER NO	). <b>:</b> _							
規格書號								
SPECIFICATION	NO N	. <b>:</b>						
版本								
EDITION NO.	:	V1.1						
日期	_							
DATE		2019-12-27						

# 客戶承認

# **CUSTOMER CONFIRM AND SIGN**

檢查	審核	承認
TESTED BY	CHECKED BY	APPROVED BY

# 東莞市赢海電子有限公司

# DONGUAN INGHAI ELECTRONICS CO.,LTD

製作	審查	確認
ISSUED BY	CHECKED BY	APPROVED BY
周明	李林	


地址: 廣東省東莞市長安鎮廈邊元灶頭工業區 16-6 號

網址: HTTP://WWW.INGHAI.COM

# DONGGUAN INGHAI ELECTRONICS CO.,LTD

**Model NO:** GMC25125YB-25R800

### A: DIMEMSIONS:



Tolerance: ±0.5mm Unit:mm

# **B: SPECIFICATIONS**


Model NO	GMC25125YB	
Rated Voltage	3.6.0V	
Operating Voltage	2.5.0~5.0V	
Max.Rated Current	Max.80mA	
Sound Pressure level(dB)at10cm/1000HZ	Min.85dB	
Resonant Frequency	800Hz	
Coil Resistance	$25\pm15\%$	
Operating Temperature	-20 °C∼+70 °C	
Storage Temperature	-30 °C~+80 °C	
Case material and color	PBT / Black	

### **Measuring condition**


Part shall be measured under a condition (Temperature:  $5 \sim 35$  °C, Humidity:  $45\% \sim 85\%$ R.H., Atmospheric pressure:  $860 \sim 1060$ hPa) unless the standard condition (Temperature:  $25\pm3$  °C, Humidity:  $60\pm10\%$ R.H. Atmospheric pressure:  $860 \sim 1060$ hPa) is regulated to measure.

### C: Acoustic Characteristics:


The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below



In the measuring test, buzzer is placed as follows:



# **D: Typical Frequency Response Curve**



# **E:** Reliability Test

After any following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall not deviate more than -10 dB from the initial value

### 1. Ordinary Temperature Life Test

### 2. High Temperature Test

The part shall be capable of with standing a storage temperature of +80 ℃ for 96 hours.

#### 3. Low Temperature Test

The part shall be capable of with standing a storage temperature of -30℃ for 96 hours.

### 4. Humidity Test

Temperature:+40  $^{\circ}$ C  $\pm$ 3  $^{\circ}$ C Relative Humidity:90% $\sim$ 95% Duration: 48 hours and expose to room temperature for 6 hours

#### 5. Temperature Shock Test

Temperature:70  $^{\circ}$ C /1hour  $\rightarrow$  25  $^{\circ}$ C/3hours  $\rightarrow$ -30  $^{\circ}$ C/1hour  $\rightarrow$  25  $^{\circ}$ C/3hours (1cycle)

Total cycle: 10 cycles

### 6. Drop Test

Standard Packaging From 120mm(Drop on hard wood or board of 5cm thick, three sides, six plain.)

#### 7. Vibration Test


Vibration: 1000cycles /min. Amplitude: 1.5mm, Duration: 1 hour in each 3 axes

#### Note:

As this product is not protected from foreign material entering, please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. The functional degradation (e.g. SPL down) may occur if foreign material enter it.

产品命名(编号)说明:

# 蜂鸣器



注:有源蜂鸣器用"yoc"驱动; 无源压电蜂鸣器用"yp-p"驱动; 无源电磁蜂鸣器用"yo-p"驱动;