

Request Samples (>)




Check Inventory (S)









- High current density
- Designed for switching frequencies between 100KHz-2MHz
- Automotive option available upon request





ELECTRICAL SPECIFICATIONS @ 25°C

PART NUMBER*	INDUCTANCE	TOLERANCE	IRMS	ISAT	DC RESISTANCE (mΩ)		TYPE	
	(uH)	(%)	(A)	(A)	TYP	MAX		
AMPLA4020S-R10NT	0.10	30	12.0	35	3.2	4	Lead Frame	
AMPLA4020S-R18NT	0.18	30	13.5	28	4.6	5.4	Lead Frame	
AMPLA4020S-R22NT	0.22	30	13.0	24	6.6	7.3	Lead Frame	
AMPLA4020S-R33MT	0.33	20	10.0	18	7.8	8.6	Lead Frame	
AMPLA4020S-R36MT	0.36	20	9.0	15	8.7	12	Lead Frame	
AMPLA4020S-R47MT	0.47	20	8.0	12	11.2	14	Lead Frame	
AMPLA4020S-R56MT	0.56	20	7.3	10	13.5	16	Lead Frame	
AMPLA4020S-R68MT	0.68	20	7.0	10	16	19	Lead Frame	
AMPLA4020S-1R0MT	1.0	20	5.0	8.5	22	27	Lead Frame	
AMPLA4020S-1R2MT	1.2	20	4.8	7.8	25	30	Lead Frame	
AMPLA4020S-1R5MT	1.5	20	4.5	7.0	34.8	42	Lead Frame	
AMPLA4020S-2R2MT	2.2	20	4.0	6.0	51	61	Lead Frame	
AMPLA4020S-3R3MT	3.3	20	3.5	4.0	69	76	Lead Frame	
AMPLA4020S-4R7MT	4.7	20	2.6	3.5	95	105	Lead Frame	
AMPLA4020S-5R6MT	5.6	20	2.2	3.0	112	125	Lead Frame	
AMPLA4020S-6R8MT	6.8	20	2.1	2.8	150	172	Lead Frame	
AMPLA4020S-8R2MT	8.2	20	2.0	2.5	158	180	Lead Frame	
AMPLA4020S-100MT	10.0	20	1.8	2.3	215	243	Lead Frame	
AMPLA4020S-150MT	15.0	20	1.5	1.9	325	374	Lead Frame	
AMPLA4020S-220MT	22.0	20	1.2	1.4	470	500	Lead Frame	

^{*} Please refer to Part Identification section

Test Conditions

Inductance: 100 kHz, 1 V, 0 Adc Humidity Range: 85 ± 2% RH

Temperature Rise Current: Current measured at Δ T of 40°C

Saturation Current: Current measured at Δ L of 30%

GENERAL SPECIFICATIONS

Operating Temperature:

-55°C to +125°C with (40°C rise) Irms current.

Maximum Part Temperature: +125°C **Components Storage Temperature:**

-55°C to +125°C

Tape and Reel Packaging Temperature: -55°C to +80°C

MSL: Level 1


MATERIALS

Carbonyl Powder Core:


Wire: Copper Terminal: Tin Plating Black Ink:

Paint: Gray

PRODUCT DIMENSIONS



RECOMMENDED LANDING PATTERN



Dimensions: mm

PART BUILDER



1. Tolerance: M = 20% 2. Packaging: B = Bulk

N = 30%


T = Tape and Reel (3,000pcs/reel)

^{*}Refer to Electrical Specification table





RECOMMENDED REFLOW PROFILE



ZONE	DESCRIPTION	TEMPERATURE	TIMES
1	Preheat	T _{smin} ~ T _{smax} 150°C ~ 200°C	60 [~] 180 sec.
2	Reflow	T _L 217°C	60 [~] 150 sec.
3	Peak Heat	T _₽ 260°C	10 sec. MAX






PACKAGING


Tape and Reel: 3,000 Units per Carton: 24,000

T&R per Carton: 8


Weight per Carton: 9.72 kg Weight per Unit: 0.175 g

Carton Dimensions: 410 x 325 x 415 mm





TYPE	А	В	С	D
13" x 12 mm	12.4 +2/-0	100.0 ± 2.0	13.0 +0.5/-0.2	330.0



B _o	A _o	K _o	Р	W	F	T	D
5.0 ± 0.1	4.4 ± 0.1	2.3 ± 0.1	8.0 ± 0.1	12.0 ± 0.3	5.5 ± 0.1	0.35 ± 0.05	1.5

Dimensions: mm

This product is commercial off-the-shelf (COTS) and not specifically designed for automotive, military, aviation, aerospace, implantable, life-dependent medical or safety applications. This product is not recommended for use in any application requiring high reliability in which component failure could result in loss of life and/or property damage without prior written approval from Abracon. Specifications are subject to change without notice. Contact Abracon for more information.



Headquarters:

5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858