



#### wide terminal type flat chip resistors

sense



#### type flat chip resistor


features

 High reliability and performance with T.C.R. ±100 x 10<sup>-6</sup>/K, resistance tolerance ±0.5%

Wide-side termination (reverse-geometry)


- Products with lead-free terminations meet EU RoHS requirements. EU RoHS regulation is not intended for Pb-glass contained in electrode, resistor element and glass.
- AEC-Q200 Tested

### dimensions and construction




Туре	<b>Dimensions</b> inches ( <i>mm</i> )						
(Inch Size Code)	L	W	с	d	t		
2A (0508)	.049±.006 (1.25±0.15)	.079±.006 (2.0±0.15)	.012±.008 (0.3±0.2)	.014±.008 (0.35±0.2)	.022±.004 (0.55±0.1)		
2B (0612)	.063±.006 (1.6±0.15)	.126±.008 (3.2±0.2)	.012±.008 (0.3±0.2)	.018±.006 (0.45±0.15)	.024±.004		
2H (1020)	.098±.006 (2.5±0.15)	.197±.006 (5.0±0.15)	.016±.008 (0.4±0.2)				
2J (1218)	.122±.006 (3.1±0.15)	.181±.006 (4.6±0.15)	.016±.008 (0.4±0.2)	.030±.006 (0.75±0.15)	(0.6±0.1)		
3A (1225)	.122±.006 (3.1±0.15)	.252±.006 (6.3±0.15)	.018±.008 (0.45±0.2)				

#### **Derating Curve**




For resistors operated at an ambient temperature of 70°C or above, a power rating shall be derated in accordance with the above derating curve.

ordering information



# 

WK73S2B (1W), WK73S3A (2W)




For resistors operated terminal temperature of described for each size or above, a power rating shall be derated in accordance with the derating curve above.

100

80

Please refer to "Introduction of the derating curve based on the terminal part temperature" in the beginning of our catalog before use.

If you want to use at rated power (\*1), use derating curves based on the terminal part temperature on the right side graph.



Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use. 10-26-20





## wide terminal type flat chip resistors


#### applications and ratings

Part Designation	Power Rating	Rated Ambient Temp.	Rated Terminal Part Temp.	T.C.R. (X 10⁰/K)	R D±0.5% E-24/E-96	F±1% E-24/E-96	2) J±5% E-24	Maximum Working Voltage	Maximum Overload Voltage	Operating Temp. Range
<b>WK73S2A</b> 1.0W <sup>1</sup>	70°C	125°C	±100	_	1 - 9.76	1 - 9.1	200V	400V		
			0~+200	_	30m - 976m	30m - 910m				
				0~+300	—	20m - 29.4m	20m - 27m			-
			125°C	±800	_	—	10m - 27m	200V	400V	
		70°C		±200	_	30m - 422m	30m - 390m			
WK73S2B				±100	430m - 9.76	430m - 9.76	430m - 9.1			
1.0W <sup>1</sup>	70°C	115°C	±800	—	—	10m - 27m	2000	400 V	-55°C	
			±200	—	30m - 422m	30m - 390m				
			±100	430m - 9.76	430m - 9.76	430m - 9.1				
WK73S2H 1.0W	70°C	125°C	±800	_	—	10m - 24m	200V	400V		
			±200	—	27m - 215m	27m - 200m				
				±100	—	220m - 9.76	220m - 9.1			+155°C
				±800	—	—	10m - 30m			
WK73S2J 1.0W	70°C	100°C	±200	_	33m - 237m	33m - 220m	200V	400V		
				±100	—	240m - 9.76	240m - 9.1			
1.5W	70°C	125°C	±800	—	—	10m - 20m	- 200V	400V		
			±300	—	22m - 32.4m	22m - 30m				
			±200	—	33m - 357m	33m - 330m				
			±100	—	360m - 9.76	360m - 9.1				
2.0W <sup>1</sup>		2.0W <sup>1</sup> 70°C	C 115°C	±800	—	—	10m - 20m	2000	4007	
	2 0\\/1			±300	—	22m - 32.4m	22m - 30m			
	2.000			±200	—	33m - 357m	33m - 330m			
				±100	—	360m - 9.76	360m - 9.1			


Rated voltage =  $\sqrt{Power rating x resistance value}$ 

<sup>1</sup> If you want to use at rated power use derating curves based on the terminal part temperature on the right side graph located on previous page. If any questions arise whether to use the "Rated Ambient Temperature" or the "Rated Terminal Part Temperature", please give priority to the "Rated Terminal Part Temperature." For more details refer to the "Introduction of the derating curves based on the terminal part temperature" in the beginning of the catalog

#### **Temperature Rise**



#### One-Pulse Limiting Electric Power WK73S 2A-3A



The maximum applicable voltage is equal to the max. overload voltage. Please contact factory for resistance characteristics of continuous applied pulse.

Regarding the temperature rise, the value of the temperature varies per conditions and board for use since the temperature is measured under our measuring conditions.

# environmental applications

#### **Performance Characteristics**

	Requirement $\Delta$	R ±(%+0.005Ω)	
Parameter	Limit	Typical	Test Method
Resistance	Within specified tolerance	_	25°C
T.C.R.	Within specified T.C.R.	—	+25°C/-55°C and +25°C/+125°C
Overload (Short time)	±2%	±0.2%	WK73S2A (1W), WK73S2B (1W), WK73S3A (2W): Rated voltage x2.0 for 5 seconds. WK7S2B, S2H, S2J, S3A: Rated voltage x2.5 for 3 seconds
Resistance to Solder Heat	±1%	±0.2%	260°C ± 5°C, 10 seconds ± 1 second
Bending Test	±1%	±0.1%	Holding point 90mm, Bending 1 time, Bending 5mm
Rapid Change of Temperature	±2%	±1%	-55°C (30 minutes), +125°C (30 minutes), 1000 cycles
Moisture Resistance	±2%	±0.2%	40°C ± 2°C, 90%-95% RH, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
Endurance at 70°C	±2%	±0.2%	70°C ± 2°C, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
High Temperature Exposure	±2%: WK73S (±5%) ±1%: all others	±0.5%: WK73S (±5%) ±0.2%: all others	+155°C, 1000 hours

Room temperature: 25°C

: Hot spot

2: Termina

PCB: FR-4t = 1.6mm

Additional environmental applications can also be found at www.koaspeer.com

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

12/10/20