



Circuit Diagram

PART NO	H	Q	H
A	4.3	R	12.5
B	4.5	S	13
C	5	T	13.5
D	5.5	U	14
E	6	V	15
F	6.5	W	16
G	7	X	17
H	7.5	Y	18
I	8	Z	19
J	8.5		15.5
K	9		16.5
L	9.5		17.5
M	10		22
N	10.5		23
O	11		25
P	11.5		20

PART NO	NO.2
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

PART NO	MATERIAL/QTY
S	SUS/1PC
C	C5210/1PC
D	SUS/2PCS
F	C5210/2PCS

PART NO	L
A	8
B	8.5
C	9
D	9.5
E	10

PART NO	NO.5-NO.6
01~99	NOTE
	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	4	Bross(0.30t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	Black	—
③	Base	—	1	Nylon	Black	—
②	Cover	—	1	SPCC	Plating Nickel	—
①	Keystoke	—	1	Nylon	Black	—

APPROVALS	DATE
DRAWN	SUNNY
CHECKED	2020.7.7

APPROVALS	TITLE:	PART NO.	SCALE:
CHECKED	TACT SWITCHS	K2-1102SP-□□□□-□□	1:1
APPROVALS	ELECTRONICS CO.,LTD		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			