## RF/Microwave C0G (NP0) Capacitors


## Ultra Low ESR "U" Series, COG (NP0) Capacitors (RoHS)



#### **GENERAL INFORMATION**


"U" Series capacitors are COG (NPO) chip capacitors specially designed for "Ultra" low ESR for applications in the communications market. Max ESR and effective capacitance are met on each value producing lot to lot uniformity. Sizes available are EIA chip sizes 0603, 0805, and 1210.

#### **DIMENSIONS:** inches (millimeters)



Size	A	В	С	D	E
0402	0.039±0.004 (1.00±0.1)	0.020±0.004 (0.50±0.1)	0.024 (0.6) max	0.010 ± 0.006 (0.25 ± 0.15)	0.014 (0.36) min
0603	0.060±0.010 (1.52±0.25)	0.030±0.010 (0.76±0.25)	0.036 (0.91) max	0.010 ± 0.005 (0.25 ± 0.13)	0.030 (0.76) min
0805	0.079±0.008 (2.01±0.2)	0.049±0.008 (1.25±0.2)	0.045 (1.15mm) max	0.020 ± 0.010 (0.51 ± 0.254)	0.020 (0.51) min
1210	0.126±0.008 (3.2±0.2)	0.098±0.008 (2.49±0.2)	0.055 (1.40mm) max	0.025 ± 0.015 (0.635 ± 0.381)	0.040 (1.02) min

#### **HOW TO ORDER**



Third digit = number of zeros or after "R" significant figures.

#### **ELECTRICAL CHARACTERISTICS**

#### **Capacitance Values and Tolerances:**

Size 0402 - 0.2 pF to 22 pF @ 1 MHz Size 0603 - 1.0 pF to 100 pF @ 1 MHz Size 0805 - 1.6 pF to 160 pF @ 1 MHz Size 1210 - 2.4 pF to 1000 pF @ 1 MHz

### **Temperature Coefficient of Capacitance (TC):**

0±30 ppm/°C (-55° to +125°C)

#### Insulation Resistance (IR):

 $10^{12}\,\Omega$  min. @ 25°C and rated WVDC  $10^{11}\,\Omega$  min. @ 125°C and rated WVDC

### Working Voltage (WVDC):

Size Working Voltage
0402 - 50, 25 WVDC
0603 - 200, 100, 50 WVDC
0805 - 200, 100 WVDC
1210 - 200, 100 WVDC

## **Dielectric Working Voltage (DWV):**

250% of rated WVDC

#### **Equivalent Series Resistance Typical (ESR):**

0402 - See Performance Curve, page 300
0603 - See Performance Curve, page 300
0805 - See Performance Curve, page 300
1210 - See Performance Curve, page 300

### Marking

Laser marking EIA J marking standard (except 0603) (capacitance code and tolerance upon request).

LEAD-FREE

LEAD-FREE COMPATIBLE COMPONENT RoHS

COMPLIANT

#### MILITARY SPECIFICATIONS

Meets or exceeds the requirements of MIL-C-55681

## RF/Microwave COG (NP0) Capacitors

## Ultra Low ESR "U" Series, COG (NP0) Capacitors (RoHS)




#### **CAPACITANCE RANGE**

On Annilohio


Сар	Available	Size			
(pF)	Tolerance	0402	0603	0805	1210
0.2	B,C	50V	N/A	N/A	N/A
0.3					
0.4	♦				
0.5	B,C				
0.6	B,Ç,D				
0.7					
0.8	▼				
0.9	B,C,D	♦	♦	♦	♦


Cap	Available	Size			
(pF)	Tolerance	0402	0603	0805	1210
1.0	B,C,D	50V	200V	200V	200V
1.1					
1.2					
1.3					
1.4					
1.5					
1.6					
1.7					
1.8					
1.9					
2.0					
2.1					
2.2					
2.4					
2.7					
3.0					
3.3					
3.6					
3.9					
4.3					
4.7					
5.1	l L				
5.6	7				
6.2	B,C,D	↓	↓	↓	↓
6.8	B,C,J,K,M				

Cap	Available			Size					
(pF)	Tolerance	04	02	06	03	08	05	12	10
7.5	B,C,J,K,M	50	ŅV	20	0V	20	0V	20	0V
8.2	♦								
9.1	B,C,J,K,M								
10	F,G,J,K,M								
11									
12									
13									
15				١ ١	7				
18				20					
20				10	0۷				
22									
24									
27		'	•						
30			VC						
33		N.	/A						
36									
39									
43									
47									
51									
56									
68									
75									
82		Ι,	L	١.	Ĺ	١.	Ĺ	١.	Ĺ
91	▼		▼	,	,	,	7	, '	7




## **ULTRA LOW ESR, "U" SERIES**







# TYPICAL ESR vs. FREQUENCY 0603 "U" SERIES



# TYPICAL ESR vs. FREQUENCY 0805 "U" SERIES




#### TYPICAL ESR vs. FREQUENCY 1210 "U" SERIES



**ESR Measured on the Boonton 34A** 



## TYPICAL SERIES RESONANT FREQUENCY "U" SERIES CHIP



## RF/Microwave C0G (NP0) Capacitors


## Ultra Low ESR "U" Series, COG (NP0) Capacitors (Sn/Pb)



#### **GENERAL INFORMATION**


"U" Series capacitors are COG (NPO) chip capacitors specially designed for "Ultra" low ESR for applications in the communications market. Max ESR and effective capacitance are met on each value producing lot to lot uniformity. Sizes available are EIA chip sizes 0603, 0805, and 1210.

### **DIMENSIONS:** inches (millimeters)



Size	Α	В	С	D	E
0402	0.039±0.004 (1.00±0.1)	0.020±0.004 (0.50±0.1)	0.024 (0.6) max	0.010 ± 0.006 (0.25 ± 0.15)	0.014 (0.36) min
0603	0.060±0.010 (1.52±0.25)	0.030±0.010 (0.76±0.25)	0.036 (0.91) max	0.010±0.005 (0.25±0.13)	0.030 (0.76) min
0805	0.079±0.008 (2.01±0.2)	0.049±0.008 (1.25±0.2)	0.045 (1.15mm) max	0.020±0.010 (0.51±0.254)	0.020 (0.51) min
1210	0.126±0.008 (3.2±0.2)	0.098±0.008 (2.49±0.2)	0.055 (1.40mm) max	0.025±0.015 (0.635±0.381)	0.040 (1.02) min

#### **HOW TO ORDER**



after "R" significant figures.

## Not RoHS Compliant

#### **ELECTRICAL CHARACTERISTICS**

#### Capacitance Values and Tolerances:

Size 0402 - 0.2 pF to 22 pF @ 1 MHz Size 0603 - 1.0 pF to 100 pF @ 1 MHz

Size 0603 - 1.0 pr to 100 pr @ 1 MHZ

Size 0805 - 1.6 pF to 160 pF @ 1 MHz Size 1210 - 2.4 pF to 1000 pF @ 1 MHz

T----- (TO)

### **Temperature Coefficient of Capacitance (TC):**

 $0\pm30$  ppm/°C (-55° to +125°C)

### Insulation Resistance (IR):

 $10^{12}\,\Omega$  min. @ 25°C and rated WVDC  $10^{11}\,\Omega$  min. @ 125°C and rated WVDC

### Working Voltage (WVDC):

Size Working Voltage 0402 - 50, 25 WVDC 0603 - 200, 100, 50 WVDC 0805 - 200, 100 WVDC 1210 - 200, 100 WVDC

#### **Dielectric Working Voltage (DWV):**

250% of rated WVDC

#### **Equivalent Series Resistance Typical (ESR):**

040 - See Performance Curve, page 306

0603 - See Performance Curve, page 306

0805 - See Performance Curve, page 306

1210 - See Performance Curve, page 306

#### Marking:

Laser marking EIA J marking standard (except 0603) (capacitance code and tolerance upon request).

### Military Specifications

Meets or exceeds the requirements of MIL-C-55681




## RF/Microwave C0G (NP0) Capacitors

Ultra Low ESR "U" Series, COG (NP0) Capacitors (Sn/Pb)




#### **CAPACITANCE RANGE**

C	ар	Available	Size			
(1	pF)	Tolerance	LD02	LD03	LD05	LD10
	).2	B,C	50V	N/A	N/A	N/A
0	0.3					
0	0.4	♦				
0	0.5	B,C				
0	0.6	B,Ç,D				
0	).7					
0	0.8	▼				
(	).9	B,C,D	♦	♦	♦	♦




Cap	Available	Size			
(pF)	Tolerance	LD02	LD03	LD05	LD10
7.5	B,C,J,K,M	50V	200V	200V	200V
8.2	♦				
9.1	B,C,J,K,M				
10	F,G,J,K,M				
11					
12					
13					
15			\ \		
18			200V		
20			100V		
22					
24					
27		*			
30		50V			
33		N/A			
36					
39					
43					
47					
51					
56					
68					
75					
82			l 1	<u> </u>	
91	▼	₹	₹	▼	▼




## **ULTRA LOW ESR, "U" SERIES**


TYPICAL ESR vs. FREQUENCY 0402 "U" SERIES




TYPICAL ESR vs. FREQUENCY 0603 "U" SERIES



TYPICAL ESR vs. FREQUENCY 0805 "U" SERIES




TYPICAL ESR vs. FREQUENCY 1210 "U" SERIES



ESR Measured on the Boonton 34A



## TYPICAL SERIES RESONANT FREQUENCY "U" SERIES CHIP



## RF/Microwave C0G (NP0) Capacitors Ultra Low ESR "U" Series, C0G (NP0) Capacitors (RoHS) Automotive, AEC Q200 Qualified



#### **GENERAL INFORMATION**

Automotive "U" Series capacitors are COG (NP0) chip capacitors specially designed for "Ultra" low ESR for applications in the automotive market. Max ESR and effective capacitance are met on each value producing lot to lot uniformity. Sizes available are EIA chip sizes 0402 and 0603.

# DIMENSIONS: inches (millimeters) 0402 060


#### inches (mm)

LEAD-FREE

LEAD-FREE COMPATIBLE COMPONENT

Size	Α	В	С	D	Е
0402	0.039±0.004 (1.00±0.1)	0.020±0.004 (0.50±0.1)	0.024 max (0.6)	N/A	N/A
0603	0.060±0.010 (1.52±0.25)	0.030±0.010 (0.76±0.25)	0.036 max (0.91)	0.010±0.005 (0.25±0.13)	0.030 min (0.76)

### **HOW TO ORDER**



#### **ELECTRICAL CHARACTERISTICS**

### **Capacitance Values and Tolerances:**

Size 0402 - 0.2 pF to 22 pF 0 1 MHz Size 0603 - 1.0 pF to 100 pF 0 1 MHz

## **Temperature Coefficient of Capacitance (TC):**

0±30 ppm/°C (-55° to +125°C)

#### Insulation Resistance (IR):

 $10^{12}\,\Omega$  min. @ 25°C and rated WVDC  $10^{11}\,\Omega$  min. @ 125°C and rated WVDC

#### Working Voltage (WVDC):

Size Working Voltage 0402 - 100, 50, 25 WVDC 0603 - 200, 100, 50 WVDC

## Dielectric Working Voltage (DWV):

250% of rated WVDC

after "R" significant figures.

### **Equivalent Series Resistance Typical (ESR):**

0402 - See Performance Curve, page 3030603 - See Performance Curve, page 303

### **Automotive Specifications**


Meets or exceeds the requirements of AEC Q200

RF/Microwave C0G (NP0) Capacitors Ultra Low ESR "U" Series, C0G (NP0) Capacitors (RoHS) Automotive, AEC Q200 Qualified




### **CAPACITANCE RANGE**


Cap	Available	Size	
(pF)	Tolerance	0402	0603
0.2	B,C	50V	N/A
0.3			
0.4	♦		
0.5	B,C		
0.6	B,Ç,D		
0.7			
0.8	▼		
0.9	B,C,D	♦	♦




Cap	Available Size		ze
(pF)	Tolerance	0402	0603
7.5	B,C,J,K,M	50V	200V
8.2	♦		
9.1	B,C,J,K,M		
10	F,G,J,K,M		
11			
12			
13			
15			🛊
18			200V
20			100V
22			
24			
27		♦	
30		50V	
33		N/A	
36			
39			
43			
47			
51			
56			
68			
75			
82			
91	▼	▼	<b>★</b>




## **ULTRA LOW ESR, "U" SERIES**






# TYPICAL ESR vs. FREQUENCY 0603 "U" SERIES



### TYPICAL SERIES RESONANT FREQUENCY "U" SERIES CHIP





## RF/Microwave "U" Series Designer Kits



## 0402

	Kit 5000 UZ							
Cap. Value PF	Tolerance	Cap. Value pF	Tolerance					
0.5		4.7						
1.0		5.6	B (± 0.1pF)					
1.5		6.8	Β (± 0.1pi )					
1.8	B (±0.1pF)	8.2						
2.2	В (10.1рг)	10.0						
2.4		12.0	J (±5%)					
3.0		15.0	3 (±3%)					
3.6								

<sup>\*\*\*25</sup> each of 15 values

## 0603

	Kit 4000 UZ						
Cap. Value PF	Tolerance	Cap. Value pF	Tolerance				
1.0		6.8					
1.2		7.5	B (±0.1pF)				
1.5		8.2					
1.8		10.0					
2.0		12.0					
2.4	B (±0.1pF)	15.0					
2.7	в (±0.1pr)	18.0					
3.0		22.0	J (±5%)				
3.3		27.0					
3.9		33.0					
4.7		39.0					
5.6		47.0					

<sup>\*\*\*25</sup> each of 24 values

## 0805

Kit 3000 UZ				
Cap. Value PF	Tolerance	Cap. Value pF	Tolerance	
1.0	B (±0.1pF)	15.0	J (±5%)	
1.5		18.0		
2.2		22.0		
2.4		24.0		
2.7		27.0		
3.0		33.0		
3.3		36.0		
3.9		39.0		
4.7		47.0		
5.6		56.0		
7.5		68.0		
8.2		82.0		
10.0	J (±5 %)	100.0		
12.0		130.0		

<sup>\*\*\*25</sup> each of 30 values

## 1210

Kit 3500 UZ				
Cap. Value PF	Tolerance	Cap. Value pF	Tolerance	
2.2	B (±0.1pF)	36.0	J (±5%)	
2.7		39.0		
4.7		47.0		
5.1		51.0		
6.8		56.0		
8.2		68.0		
9.1		82.0		
10.0	J(±5%)	100.0		
13.0		120.0		
15.0		130.0		
18.0		240.0		
20.0		300.0		
24.0		390.0		
27.0		470.0		
30.0		680.0		

<sup>\*\*\*25</sup> each of 30 values