



PLA172P 800V Normally-Open Single-Pole 6-Pin OptoMOS® Relay

Parameter	Rating	Units
Load Voltage	800	V _P
Load Current	100	mA _{rms}
	85	mA _{DC}
On-Resistance (max)	50	Ω
Input Control Current	2	mA

Features

- Guaranteed Specifications at 105°C
- -40°C to +105°C Operational Temperature Range
- 5mA Input Control Current Over Operating Temperature Range
- 800V_P Blocking Voltage
- 6.8mm Pad-to-Pad Separation of Output Pins
- ullet 5000V $_{
 m rms}$ Input/Output Isolation
- Small Surface Mount Package
- Arc-Free With No Snubbing Circuits
- No EMI/RFI Generation
- Flammability Rating UL 94 V-0

Applications

- Industrial Controls
- Instrumentation
- Multiplexers
- Data Acquisition
- Electronic Switching
- I/O Subsystems
- Meters (Watt-Hour, Water, Gas)
- Medical Equipment—Patient/Equipment Isolation

Description

IXYS Integrated Circuits' PLA172P is a single-pole, normally-open (1-Form-A) Solid State Relay, rated for operation up to 105° C, that uses optically coupled MOSFET technology to provide an enhanced input to output isolation of $5000V_{rms}$.

The unique device pinout provides more than 6.8mm of pad-to-pad separation between the high voltage output pins.

Control of the optically coupled output is by the input infrared LED. The PLA172P is designed to replace electromechanical relays, and provides bounce-free switching in a compact, surface-mount package.

Approvals


- UL Approval Pending
- EN/IEC 60950-1 Approval Pending

Ordering Information


Part #	Description
PLA172P	6-Pin (8-Pin Body) Flatpack (50/Tube)
PLA172PTR	6-Pin (8-Pin Body) Flatpack, Tape & Reel (1000/Reel)

Pin Configuration

AC/DC Configuration



Switching Characteristics of Normally-Open Devices











Absolute Maximum Ratings

(@ 25°C Unless otherwise noted)

Parameter	Ratings	Units	
Blocking Voltage (-40°C to +105°C)	800	V_P	
Reverse Input Voltage	5	V	
Input Control Current	50	mA	
Peak (10ms)	1	Α	
Input Power Dissipation ¹	Power Dissipation ¹ 150		
Output Power Dissipation			
AC Load Current ²	890	mW	
DC Load Current ³	667	TTIVV	
Isolation Voltage, Input to Output (60 Seconds)	5000	V_{rms}	
Operational Temperature	-40 to +105	°C	
Storage Temperature	-40 to +125	°C	

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

Typical values are characteristic of the device at the specified temperatures and are the result of engineering evaluations. They are provided for information purposes only and are not part of the manufacturing testing requirements.

Electrical Characteristics

Parameter	Conditions	Symbol	Min	Тур	Max	Units
Output Characteristics @ 25	°C					
Load Current	I ₌ =2mA					
AC ¹	0 "		-	-	100	mA_{rms}
DC ²	Continuous	tinuous I _L	-	-	85	mA _{DC}
Peak	t=10ms	I _{LPK}	-	-	±350	mA _P
On-Resistance ³	$I_{E}=2mA, I_{L}=100mA$		-	37	50	'
	I _E =2mA, I _I =1mA	R _{ON}	-	57	85	Ω
Off-State Leakage Current	V _I =800V _P	I _{LEAK}	-	-	1	μΑ
Switching Speeds		EL/ IIX				
Turn-On	F A 400 A	t _{on}	-	1.2	5	
Turn-Off	I _F =5mA, I _L =100mA	t _{off}	-	0.5	5	ms
Output Capacitance	I _F =0mA, V _I =20V, f=1MHz	C _{OUT}	-	10	-	pF
Output Characteristics @ 10		001		ļ.	"	
On-Resistance ³	I _F =5mA, I _I =30mA	р	-	70	110	Ω
	I _F =5mA, I _I =1mA	R _{ON}	-	110	140	
Off-State Leakage Current	V _I =800V _P	I _{LEAK}	-	-	5	μΑ
Switching Speeds						
Turn-On	I Em A I 20m A	t _{on}	-	-	10	m 0
Turn-Off	I _F =5mA, I _L =30mA	t _{off}	-	-	10	ms
Input Characteristics @ 25°C		0				
Input Control Current to Activate 4	I _L =100mA	l _F	-	0.35	2	mA
Input Control Current to Deactivate	-	l _F	0.05	-	-	mA
Input Voltage Drop	I _F =5mA	V _F	0.9	1.2	1.5	V
Reverse Input Current	V _R =5V	I _R	-	-	10	μΑ
Input Characteristics @ 105°	C					
Input Control Current to Activate	I _L =30mA	l _F	-	-	5	mA
Common Characteristics @	25°C			•	•	
Input to Output Capacitance	V _{IO} =0V, f=1MHz	C _{IO}	-	1	-	pF

¹ Derate linearly 1.33 mW / °C

² Derate linearly 8.9 mW / °C


³ Derate linearly 6.67 mW / °C


 $^{^1}$ Load derates linearly from 100mA @ 25°C to 44mA @ 105°C (0.7mA/°C). 2 Load derates linearly from 85mA @ 25°C to 38mA @ 105°C (0.59mA/°C). 3 Measurement taken within 1 second of on-time.


⁴ For applications requiring high temperature operation (greater than 60°C) a minimum LED drive current of 5mA is recommended.





PERFORMANCE DATA*
































*Unless otherwise noted, data presented in these graphs is typical of device operation at 25°C. For guaranteed parameters not indicated in the written specifications, please contact our application department.





PERFORMANCE DATA*

























Manufacturing Information

Moisture Sensitivity

All plastic encapsulated semiconductor packages are susceptible to moisture ingression. IXYS Integrated Circuits classifies its plastic encapsulated devices for moisture sensitivity according to the latest version of the joint industry standard, IPC/JEDEC J-STD-020, in force at the time of product evaluation. We test all of our products to the maximum conditions set forth in the standard, and guarantee proper operation of our devices when handled according to the limitations and information in that standard as well as to any limitations set forth in the information or standards referenced below.

Failure to adhere to the warnings or limitations as established by the listed specifications could result in reduced product performance, reduction of operable life, and/or reduction of overall reliability.

This product carries a Moisture Sensitivity Level (MSL) classification as shown below, and should be handled according to the requirements of the latest version of the joint industry standard **IPC/JEDEC J-STD-033**.

Device	Moisture Sensitivity Level (MSL) Classification
PLA172P	MSL 1

ESD Sensitivity



This product is ESD Sensitive, and should be handled according to the industry standard JESD-625.

Soldering Profile

Provided in the table below is the Classification Temperature ($T_{\rm C}$) of this product and the maximum dwell time the body temperature of this device may be ($T_{\rm C}$ - 5)°C or greater. The classification temperature sets the Maximum Body Temperature allowed for this device during lead-free reflow processes. For through-hole devices, and any other processes, the guidelines of **J-STD-020** must be observed.

Device	Classification Temperature (T _c)	Dwell Time (t _p)	Max Reflow Cycles
PLA172P	250°C	30 seconds	3

Board Wash

IXYS Integrated Circuits recommends the use of no-clean flux formulations. Board washing to reduce or remove flux residue following the solder reflow process is acceptable provided proper precautions are taken to prevent damage to the device. These precautions include, but are not limited to: using a low pressure wash and providing a follow up bake cycle sufficient to remove any moisture trapped within the device due to the washing process. Due to the variability of the wash parameters used to clean the board, determination of the bake temperature and duration necessary to remove the moisture trapped within the package is the responsibility of the user (assembler). Cleaning or drying methods that employ ultrasonic energy may damage the device and should not be used. Additionally, the device must not be exposed to flux or solvents that are Chlorine- or Fluorine-based.











Mechanical Dimensions

PLA172P Package



PLA172PTR Tape & Reel



For additional information please visit our website at: www.ixysic.com

IXYS Integrated Circuits makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in IXYS Integrated Circuits' Standard Terms and Conditions of Sale, IXYS Integrated Circuits assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of IXYS Integrated Circuits' product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. IXYS Integrated Circuits reserves the right to discontinue or make changes to its products at any time without notice.