


SPECIFICATION:
Current Rating: 1.5AMP
Contact Resistance: 20m Ω (max)
Insulation Resistance: 1000M Ω Min at 500V DC
Dielectric Strength: 500V AC Per 1 Minute
Operating Temperature: -40°C TO +105°C

MATERIALS:
Insulator: Glass filled PA9T (UL 94V-0), Black
Contact: Brass
Plating: 0.8u" Au

CONTACTS	PART NO.	A	B
6	310-2R-6P 长耳	21.92	4.00
8	310-2R-8P 长耳	23.92	6.00
10	310-2R-10P 长耳	25.92	8.00
12	310-2R-12P 长耳	27.92	10.00
14	310-2R-14P 长耳	29.92	12.00
16	310-2R-16P 长耳	31.92	14.00
20	310-2R-20P 长耳	35.92	18.00
24	310-2R-24P 长耳	39.92	22.00
26	310-2R-26P 长耳	41.92	24.00
30	310-2R-30P 长耳	45.92	28.00
34	310-2R-34P 长耳	49.92	32.00
40	310-2R-40P 长耳	55.92	38.00
44	310-2R-44P 长耳	59.92	42.00
50	310-2R-50P 长耳	65.92	48.00
60	310-2R-60P 长耳	75.92	58.00
64	310-2R-64P 长耳	69.92	62.00



PCB LAYOUT

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	TITLE: 310-2R-XP 长耳			
CHECKED:	DATE:	CLIENT P/N B-3102RXXP-A000			
DRAWN:	DATE:	UNIT	mm	SCALE	Free
SXA	2019-05-17	FILE NO.	ChamtW-310-00024	REV.	WY02

深圳市矽科盟实业有限公司
CHANKEMENG INDUSTRY CO., LTD