

Features

- Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix Designates Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1
- Super Fast Recovery Times For High Efficiency
- Halogen Free Available Upon Request By Adding Suffix "-HF"

Maximum Ratings

- Operating Junction Temperature Range: -50°C to +175°C
- Storage Temperature Range: -50°C to +175°C
- Typical Thermal Resistance: 13°C/W Junction to Lead

MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
ER3A	ER3A	50V	35V	50V
ER3B	ER3B	100V	70V	100V
ER3C	ER3C	150V	105V	150V
ER3D	ER3D	200V	140V	200V
ER3G	ER3G	400V	280V	400V
ER3J	ER3J	600V	420V	600V
ER3K	ER3K	800V	560V	800V
ER3M	ER3M	1000V	700V	1000V


Electrical Characteristics @ 25°C Unless Otherwise Specified

Average Forward Current	I _{F(AV)}	3.0A	T _L =125°C
Peak Forward Surge Current	I _{FSM}	100A	8.3ms,Half Sine
Maximum Instantaneous Forward Voltage ER3A-ER3D ER3G ER3J-ER3M	V _F	0.95V 1.25V 1.70V	I _{FM} =3.0A; T _J =25°C*
Maximum DC Reverse Current At Rated DC Blocking Voltage	I _R	5.0μA 200μA	T _J =25°C; T _J =100°C
Maximum Reverse Recovery Time ER3A~ER3J	_	35ns	I _F =0.5A; I _R =1.0A;
ER3K~ER3M	T _{RR}	75ns	Irr=0.25A
Typical Junction Capacitance	CJ	45pF	Measured at 1.0MHz V _R =4.0V

^{*}Pulse Test: Pulse Width 300 μ sec, Duty Cycle 2%


3 Amp Super Fast Recovery Silicon Rectifier 50 to 1000 Volts

SMC (DO-214AB)



DIMENSIONS						
DIM	INCHES		MM		NOTE	
	MIN	MAX	MIN	MAX	NOTE	
Α	0.079	0.103	2.00	2.62		
В	0.108	0.128	2.75	3.25		
С	0.002	0.008	0.051	0.203		
D	0.006	0.012	0.152	0.305		
Е	0.030	0.060	0.76	1.52		
F	0.305	0.320	7.75	8.13		
G	0.260	0.280	6.60	7.11		
Н	0.220	0.245	5.59	6.22		

Suggested Solder Pad Layout



^{1.} High Temperature Solder Exemptions Applied, See EU Directive Annex 7a.



Curve Characteristics

Fig. 1 - Forward Current Derating Curve

4

4

4

4

A

A

B

C

Resistive or Inductive Load

0

0

25

50

75

Lead Temperature (°C)

Fig. 2 - Maximum Non-Repetitive Peak Forward Surge
Current

120

80

90

90

40

40

20

8.3 ms Single Half Sine-Wave

0

Number of Cycles at 60 Hz

Fig. 3 - Typical Instantaneous Forward Characteristics

The standard Characteristics

Fig. 3 - Typical Instantaneous Forward Characteristics

ER3A-ER3D

ER3J-ER3M


O.5

O.5

O.01

O.5

Instantaneous Forward Voltage (V)





Ordering Information

Device	Packing	
Part Number-TP	Tape&Reel: 3Kpcs/Reel	

Note: Adding "-HF" Suffix For Halogen Free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp**. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp**, and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Rev.3-1-01012019 3/3 MCCSEMI.COM