

Features

- Halogen Free Available Upon Request By Adding Suffix "-HF"
- Lead Free Finish/RoHS Compliant (Note1) ("P"Suffix Designates Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1

Maximum Ratings

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Typical Thermal Resistance: 20°C/W Junction to Lead

MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
LMB12S	LB12S	20V	14V	20V
LMB14S	LB14S	40V	28V	40V
LMB16S	LB16S	60V	42V	60V
LMB18S	LB18S	80V	56V	80V
LMB110S	LB110S	100V	70V	100V


Electrical Characteristics @ 25°C Unless Otherwise Specified

Average Rectified Output Current	I _{F(AV)}	1.0A	T _A =80°C(Note2) T _A =40°C(Note3)
Peak Forward Surge Current	I _{FSM}	30A	8.3ms, Half Sine
Maximum Instantaneous Forward Voltage LMB12S~LMB14S LMB16S LMB18S~LMB110S	V _F	0.55V 0.65V 0.85V	I _{FM} = 0.5A ; T _A = 25°C
Maximum DC Reverse Current at Rated DC Blocking Voltage	I _R	0.1mA	T _A = 25°C

Note: 1. High Temperature Solder Exemption Applied, See EU Directive Annex Notes 7a.


- 2. On Alumina Substrate, See Fig 1.
- 3. On Glass-epoxi Substrate, See Fg 1.

1 Amp Surface Mount Schottky Bridge Rectifier 20 to 100 Volts



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	NOTE
Α	0.197	0.205	4.90	5.20	
В	0.024		0.60		
С		0.059		1.50	
D	0.024	0.032	0.60	0.80	
Е		0.189		4.80	
F	0.150	0.165	3.80	4.20	
G		0.209		5.30	
Н	0.236	0.252	6.00	6.60	
J	0.177	0.185	4.30	4.70	
K	0.0009	0.004	0.02	0.21	
L	0.006	0.012	0.15	0.30	
М	0.017	0.031	0.25	0.80	

Suggested Solder Pad Layout





Curve Characteristics




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 5 - Typical Instantaneous Forward Characteristics




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge
Current

35
30
20
20
15
10
5
8.3 ms Single Half Sine-Wave

0

Fig. 4 - Typical Instantaneous Forward Characteristics

Number of Cycles at 60 Hz

100





Fig. 6 - Typical Reverse Leakage Characteristics





Curve Characteristics

Fig. 7 - Typical Reverse Leakage Characteristics





Fig. 8 - Typical Reverse Leakage Characteristics





Ordering Information

Device	Packing	
(Part Number)-TP	Tape&Reel5Kpcs/Reel	

Note: Adding "-HF" Suffix For Halogen Free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp**. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp**, and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Rev.3-1-01012019 4/4 MCCSEMI.COM