

High Temperature Operation (125°C)

This data sheet addendum is to be used in conjunction with the existing AT45DB041E datasheet specifications. The Adesto AT45DB041E 4Mbit DataFlash devices will operate @ 125°C with the following datasheet caveats. All other parameters will meet the existing datasheet specifications.

The ordering code suffix (CAN# Code) 'HT' must be used to ensure correct operation at this extended temperature range. Adesto will not modify and republish the current datasheet to reflect the CAN# 'HT' ordering code or the above caveats. The standard [AT45DB041E datasheet](http://www.adestotech.com) is available at <http://www.adestotech.com>.

1. Electrical Specifications

1.1 DC and AC Operating Range

		AT45DB041E-xxxHT
Operating Temperature		-40°C to +125°C
Endurance (Maximum)		10,000 Cycles

1.2 DC Characteristics

Symbol	Parameter	Condition	1.65V to 3.6V			2.3V to 3.6V			Units
			Min	Typ	Max	Min	Typ	Max	
I_{DPD}	Deep Power-Down Current	$\overline{CS}, \overline{RESET}, \overline{WP} = V_{IH}$ All inputs at CMOS levels		4.5	20		5	20	μA
I_{SB}	Standby Current	$\overline{CS}, \overline{RESET}, \overline{WP} = V_{IH}$ All inputs at CMOS levels		25	45		25	45	μA
I_{CC3}	Active Current, Program Operation	$\overline{CS} = V_{CC}$		14	20		14	20	mA

1.3 AC Characteristics

Symbol	Parameter	1.65V to 3.6V		2.3V to 3.6V		Units
		Min	Max	Min	Max	
f_{CAR1}	SCK Frequency for Continuous Read (0x0B)		70		70	MHz
f_{CAR2}	SCK Frequency for Continuous Read (0x03) (Low Frequency)		33		33	MHz
t_{CS}	Minimum \overline{CS} High Time	24		24		ns
t_V	Output Valid		8		6	ns

1.4 Program and Erase Characteristics

Symbol	Parameter	1.65V to 3.6V		2.3V to 3.6V		Units
		Typ	Max	Typ	Max	
t_{BE}	Block Erase Time	30	50	30	50	ms
t_{SE}	Sector Erase Time	.7	1.3	.7	1.3	s

- Notes: 1. Values are based on device characterization, not 100% tested in production.
2. Not 100% tested (value guaranteed by design and characterization).

2. Ordering Code

2.1 Ordering Code Detail

Ordering Code ⁽¹⁾	Package	Operating Voltage	Max. Freq. (MHz)	Operation Range
AT45DB041E-SHNHT-T	8S2	1.65V to 3.6V	85MHz	Extended (-40°C to +125°C)
AT45DB041E-SHNHT-B				
AT45DB041E-SSHNT-T	8S1			
AT45DB041E-SSHNT-B				

1. The shipping carrier option code is not marked on the devices.

Package Type	
8S1	8-lead, 0.150" Wide, Plastic Gull Wing Small Outline Package (JEDEC SOIC)
8S2	8-lead, 0.208" Wide, Plastic Gull Wing Small Outline Package (EIAJ SOIC)

1. Revision History

Revision Level – Release Date	History
A – January 2015	Initial release.
B – October 2015	Corrected package type in Ordering Code Detail table.
C – August 2017	Updated corporate address information.



Corporate Office

California | USA
Adesto Headquarters
3600 Peterson Way
Santa Clara, CA 95054
Phone: (+1) 408.400.0578
Email: contact@adestotech.com

© 2017 Adesto Technologies. All rights reserved. / Rev.: DS-45DB041E-024C-8/2017

Disclaimer: Adesto Technologies Corporation makes no warranty for the use of its products, other than those expressly contained in the Company's standard warranty which is detailed in Adesto's Terms and Conditions located on the Company's web site. The Company assumes no responsibility for any errors which may appear in this document, reserves the right to change devices or specifications detailed herein at any time without notice, and does not make any commitment to update the information contained herein. No licenses to patents or other intellectual property of Adesto are granted by the Company in connection with the sale of Adesto products, expressly or by implication. Adesto's products are not authorized for use as critical components in life support devices or systems.