


Description

The ZXRE330 is a low knee current 3.3V voltage reference. Offering tight tolerances and sharp knee characteristics – consuming only $1\mu A$ when the 3.3V reference voltage can no longer be maintained.


Excellent performance is maintained over the 1μ A to 5mA operating current range. The device has been designed to be highly tolerant of capacitive loads so maintaining excellent stability.

It's available in small outline SOT23 and TO92 packages. This device offers a pin for pin compatible alternative to industry standard shunt voltage reference.

Pin Assignments



* Pin 3 must be left floating or connected to pin 2



(Top View)

* Pin 2 must be left floating or connected to pin 1

Features

- Small Packages: SOT23 & TO92
- No Output Capacitor Required
- Output Voltage Tolerance
- ZXRE330E: ±2% at +25°C
- ZXRE330A: ±0.5% at +25°C
- Low Output Noise
 - 55µV_{RMS} (10Hz to 10 kHz)
- Wide Operating Current Range 1µA to 5mA
- Extended Temperature Range -40°C to +85°C
- Low Temperature Coefficient 20ppm/°C (Typ)
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

Notes:

No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

Applications

Battery-Powered Equipment

Portable Communications Devices

Notebook and Palmtop Computers

Precision Power Supplies

Portable Instrumentation


Data Acquisition Systems

Low Current Voltage Clamps

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Typical Applications Circuit



Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.) (Voltages to GND, unless otherwise stated.)

Parameter	Rating	Unit
Continuous Reverse Current	10	mA
Continuous Forward Current	10	mA
Operating Junction Temperature	-40 to +150	°C
Storage Temperature	-65 to +150	°C

Note: 4. Operation above the absolute maximum rating may cause device failure. Operation at the absolute maximum rating, for extended periods, may reduce device reliability. Unless otherwise stated voltages specified are relative to the ANODE pin.

Package Thermal Data

Package	θ _{JA}	P _{DIS} T _{AMB} = +25°C, T _J = +150°C
SOT23	415°C/W	300mW
TO92	180°C/W	700mW

Recommended Operating Conditions (@T_A = +25°C, unless otherwise specified.)

Parameter	Min.	Max.	Unit
Reverse Current	0.002	5	mA
Operating Ambient Temperature Range	-40	+85	°C




Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Cumula al	Devenuerten	Conditions			Turn	F Limite	Unit
Symbol	Parameter T _{AMB}		AMB	Тур	E Limits		
	Reverse Breakdown Voltage	I _R = 100μΑ	+2	5°C	3.3	_	V
\/			+25°C	ZXRE330A		±16.5	
VREF	Reverse Breakdown Voltage Tolerance	I _R = 100μA		ZXRE330E	—	±66	mV
			-40 to	+85°C		±99	
	Off state Reverse Current	V V *0.0	+2	5°C	0.5	_	
IROFF	Off state Reverse Current	$V = V_{REF} * 0.9$	-40 to	+85°C		1	μA
		I _R = 5mA	-40 to +85°C		±20		_
ΔV _R /ΔT	ΔT Average Reverse Breakdown Voltage	I _R = 100μA			±15	±150	ppm/°C
	Temperature Coefficient	I _R = 10μΑ			±15		_
		2uA <i<sub>R < 100uA</i<sub>	25	25°C			mV
A) (Development development		-40 to +85°C 25°C		_	0.6	
ΔV _R	Reverse Breakdown Change With Current				10		
		100uA < I _R < 5mA	-40 to	-40 to +85°C		20	
I _{RMIN}	Minimal Operating Current	_		1	2	μΑ	
Z _R	Dynamic Output Impedance	I _R = 2mA, f = 120Hz, I _{AC} = 0.1I _R		2	_	Ω	
en	Noise Voltage	I _R = 100μA 10Hz < f < 10kHz		55	_	μV _{RMS}	
VR	Long Term Stability (non-cumulative)	t = 1000Hrs, I _R = 100µA		_	—	ppm	
V _{HYST}	Thermal Hysteresis	ΔT = -40°C to +85°C		0.08	_	%	




Typical Characteristics




Reverse Breakdown Voltage Temperature Coefficient









Off-state Reverse Current vs. Temperature



Reverse Breakdown Voltage Temperature Coefficient




Reverse Current vs. Reverse Voltage



Noise Voltage vs. Frequency



Start-up Characteristics ZXRE330




 I_R =100µA, No Load Capacitor

I_R=5mA, No Load Capacitor

Application Information

In a conventional shunt regulator application (*Figure 1*), an external series resistor (R_S) is connected between the supply voltage, V_S , and the ZXRE330.



 R_S determines the current that flows through the load (I_L) and the ZXRE330 (I_R). Since load current and supply voltage may vary, R_S should be small enough to supply at least the minimum acceptable I_R to the ZXRE330 even when the supply voltage is at its minimum and the load current is at its maximum value. When the supply voltage is at its maximum and I_L is at its minimum, R_S should be large enough so that the current flowing through the ZXRE330 is less than 10mA.

 R_S is determined by the supply voltage, (V_S), the load and operating current, (I_L and I_R), and the ZXRE330's reverse breakdown voltage, V_R.

$$R_S = \frac{V_S - V_R}{I_L + I_R}$$


Printed Circuit Board Layout Considerations

ZXRE330 in the SOT23 package have the die attached to pin 3, which results in an electrical contact between pin 2 and pin 3. Therefore, pin 3 of the SOT23 package must be left floating or connected to pin 2.

ZXRE330 in the TO92 package have the die attached to pin 2, which results in an electrical contact between pin 2 and pin 1. Therefore, pin 2 must be left floating or connected to pin1.



Ordering Information




Devi Nevrek en	Package	Destada	7" Tape and Reel		Ammo Box	
Part Number	Code	Packaging	Quantity	Part Number Suffix	Quantity	Part Number Suffix
ZXRE330ASA-7	SA	SOT23	3,000/Tape & Reel	-7	NA	NA
ZXRE330ESA-7	SA	SOT23	3,000/Tape & Reel	-7	NA	NA
ZXRE330AV-A	V	TO92	NA	NA	2,000/Box	A
ZXRE330EV-A	V	TO92	NA	NA	2,000/Box	А

Note: 5. Pad layout as shown on Diodes Incorporated's package page, which can be found on http://www.diodes.com/package-outlines.html.

Marking Information


(1) SOT23



Part Number	Package	Identification Code
ZXRE330ASA-7	SOT23	DC
ZXRE330ESA-7	SOT23	DD

(2) TO92


(Top View)






Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.



	SOT23				
Dim	Min	Max	Тур		
Α	0.37	0.51	0.40		
В	1.20	1.40	1.30		
С	2.30	2.50	2.40		
D	0.89	1.03	0.915		
F	0.45	0.60	0.535		
G	1.78	2.05	1.83		
Н	2.80	3.00	2.90		
J	0.013	0.10	0.05		
K	0.890	1.00	0.975		
K1	0.903	1.10	1.025		
L	0.45	0.61	0.55		
L1	0.25	0.55	0.40		
М	0.085	0.150	0.110		
а	0°	8°			
All	All Dimensions in mm				

TO92





	TO92				
Dim	Min	Max	Тур		
Α	3.45	3.66	-		
A2	1.22	1.37	-		
b	-	-	0.38		
С	-	-	0.38		
D	4.27	4.78	-		
D1	-	-	3.87		
E	4.32	4.83	-		
е	-	-	1.27		
e2	2.40	2.90	-		
L	12.98	15.00	-		
L1	12.80	15.00	-		
L2	0.80	-	-		
L3	2.00	3.00	-		
All I	All Dimensions in mm				

SOT23


ø

h



Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	2.9



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com