
HQC0805-Series

High Frequency SMD Inductor for Signal Line

FEATURES

- Especially high Q factor in this series for customers' design.
- Resin-coated surface enables excellent mounting
- Low DC resistance design is ideal for low loss, high output and low power consumption.



APPLICATIONS


- For high-frequency applications including mobile phones, portable phones, such as PA, ANT, VCO, SAW, etc.
- Mobile phones such as GSM, CDMA, PDC, etc.
- Bluetooth, W-LAN

PRODUCT IDENTIFICATION


HQC 0805 - 10N J - T

- | | |
|---------------------------------|------------------------------|
| (1) Product name | (4) Tolerance |
| (2) Shapes and Dimensions (LxW) | G : ±2% ; J : ±5% ; K : ±10% |
| (3) Inductance | (6) Taping style |
| 10N:10nH, 3N3:3.3nH | T : Taping ; None : Bulk |

SHAPES AND DIMENSIONS(Unit:mm)



RECOMMENDED FOOTPRINT(Unit:mm)



HQC0805-Series

High Frequency SMD Inductor for Signal Line

ELECTRICAL CHARACTERISTICS

Our Product Part Number	Inductance (nH)/MHz	Inductance Tolerance	Q/MHz Min.	SRF(Min.) (MHz)	DCR (Ω)Max.	Irms Max. (mA)	Color Coding
HQC0805-2N5□-T	2.5/250	10,5	60/1500	>6000	0.030	1600	Black
HQC0805-5N6□-T	5.6/250	10,5	98/1500	>6000	0.040	1600	Brown
HQC0805-6N2□-T	6.2/250	10,5	70/1000	4750	0.035	1600	Red
HQC0805-10N□-T	10/250	10,5	75/1000	3000	0.050	1600	Gray
HQC0805-12N□-T	12/250	10,5,2	80/1000	3000	0.050	1600	Orange
HQC0805-16N□-T	16/250	10,5,2	72/500	2950	0.060	1500	Yellow
HQC0805-18N□-T	18/250	10,5,2	75/500	2550	0.065	1400	Green
HQC0805-20N□-T	20/250	10,5,2	70/500	2050	0.065	1400	Blue
HQC0805-27N□-T	27/250	10,5,2	75/500	2000	0.075	1300	Violet
HQC0805-30N□-T	30/250	10,5,2	65/500	1950	0.095	1200	Gray
HQC0805-39N□-T	39/250	10,5,2	65/500	1600	0.100	1100	White
HQC0805-48N□-T	48/200	10,5,2	65/500	1400	0.100	1200	Black
HQC0805-51N□-T	51/200	10,5,2	65/500	1400	0.120	1000	Brown

1. When ordering, please specify tolerance and packaging codes. Ex: HQC0805-12NJ-T

Tolerance : G = $\pm 2\%$, J = $\pm 5\%$, K = $\pm 10\%$

Packaging : Clear tape and reel { standard }.

2. L , Q 、 SRF : Agilent/HP E4991A+ Agilent/HP16197A

(The electrical specification test by the smallest gap position) or HP16193A


3. Rdc : DIGITAL MILLIOHM METER Chroma 16502, or equivalent.

4. Irms for a 15°C rise above 25°C ambient.

5. Operating temperature range from -40°C to 125°C.

6. Packaging quantity: 2000 pcs/reel

1st



COLOR CODING

HQC0805-Series

High Frequency SMD Inductor for Signal Line

ELECTRICAL CHARACTERISTICS

Characteristics(L,Q vs. Frequency)

