

# ALUMINUM ELECTROLYTIC CAPACITORS

nichicon

# LGZ

Snap-in Terminal Type, 105°C Long Life Assurance



- Long life product of LGR series.
- Contribute to longer life of equipment.
- Compliant to the RoHS directive (2011/65/EU),(EU)2015/863).


**LGZ** ← Long Life → **LGR**





## ■ Specifications

Item	Performance Characteristics						
Category Temperature Range	-25 to +105°C						
Rated Voltage Range	450V						
Rated Capacitance Range	82 to 330μF						
Capacitance Tolerance	±20% at 120Hz, 20°C						
Leakage Current	After 5 minutes' application of rated voltage at 20°C, leakage current is not more than $3\sqrt{CV}(\mu A)$ or 5 mA, whichever is smaller (at 20°C) [C : Rated Capacitance (μF), V : Voltage (V)]						
Tangent of loss angle (tan δ)	0.20MAX. 120Hz at 20°C						
Stability at Low Temperature	<table border="1"> <tr> <td>Rated voltage (V)</td> <td>450</td> </tr> <tr> <td>Impedance ratio ZT/Z20(MAX.)</td> <td>Z - 25°C / Z+20°C 8</td> </tr> </table>			Rated voltage (V)	450	Impedance ratio ZT/Z20(MAX.)	Z - 25°C / Z+20°C 8
Rated voltage (V)	450						
Impedance ratio ZT/Z20(MAX.)	Z - 25°C / Z+20°C 8						
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after D.C. bias plus rated ripple current is applied for 20000 hours at 105°C, the peak voltage shall not exceed the rated voltage.						
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the characteristic requirements listed at right.						
Marking	Printed with white color letter on black sleeve.						

## ■ Drawing



Type numbering system (Example : 450V 82μF)



(PC board hole dimensions)

(Terminal dimensions)

\* The other terminal is also available upon request.  
Please refer to page 393 for schematic of dimensions.

## ■ Dimensions

450V (2W)				
Cap. (μF)	Size φD x L(mm)	Rated ripple (mArms)	Leakage Current (mA)	Code
82	30 × 25	560	0.57	LGZ2W820MELB25
100	30 × 30	640	0.63	LGZ2W101MELB30
120	30 × 35	720	0.69	LGZ2W121MELB35
	35 × 25	720	0.69	LGZ2W121MELC25
150	30 × 40	790	0.77	LGZ2W151MELB40
	35 × 30	790	0.77	LGZ2W151MELC30
180	30 × 45	870	0.85	LGZ2W181MELB45
	35 × 35	870	0.85	LGZ2W181MELC35
220	30 × 50	1000	0.94	LGZ2W221MELB50
	35 × 40	1000	0.94	LGZ2W221MELC40
270	35 × 45	1190	1.04	LGZ2W271MELC45
330	35 × 50	1380	1.15	LGZ2W331MELC50

Rated ripple current (mAmps) at 105°C 120Hz

## • Frequency coefficient of rated ripple current

Frequency (Hz)	50	60	120	300	1 k	10k	50k or more
Coefficient	0.77	0.82	1.00	1.16	1.30	1.41	1.43

Minimum order quantity : 50pcs.

CAT.8100J