

UUT 6mmL Chip Type, Wide Temperature Range




- Chip type with load life 2000 hours at +105°C.
- Designed for surface mounting on high density PC board.
- Applicable to automatic mounting machine fed with carrier tape.
- Compliant to the RoHS directive (2011/65/EU, (EU)2015/863).
- AEC-Q200 compliant. Please contact us for details.




Specifications

Item	Performance Characteristics								
Category Temperature Range	-55 to +105°C								
Rated Voltage Range	4 to 50V								
Rated Capacitance Range	1 to 100μF								
Capacitance Tolerance	±20% at 120Hz, 20°C								
Leakage Current	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01 CV or 3 (μA) , whichever is greater.								
Tangent of loss angle (tan δ)	Measurement frequency :120Hz at 20°C								
	Rated voltage (V)	4	6.3	10	16	25	35	50	
	tan δ (MAX.)	0.37	0.28	0.24	0.20	0.16	0.13	0.12	
Stability at Low Temperature	Measurement frequency :120Hz								
	Rated voltage (V)		4	6.3	10	16	25	35	50
	Impedance ratio	Z-25°C / Z+20°C	6	3	3	2	2	2	2
	ZT / Z20 (MAX.)	Z-40°C / Z+20°C	12	8	5	4	3	3	3
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 105°C.		Capacitance change	Within ±25% of the initial capacitance value (16V or less)					
			tan δ	Within ±20% of the initial capacitance value (25V or more)					
			Leakage current	200% or less than the initial specified value					
				Less than or equal to the initial specified value					
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.								
Resistance to soldering heat	The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C. The capacitors shall meet the characteristic requirements listed at right when they are removed from the plate and restored to 20°C.		Capacitance change	Within ±10% of the initial capacitance value					
			tan δ	Less than or equal to the initial specified value					
			Leakage current	Less than or equal to the initial specified value					
Marking	Black print on the case top.								

Chip Type



Type numbering system (Example : 16V 10μF)



Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

● Dimension table in next page.

UUT

■ Dimensions

Rated Voltage (V) (code)	Rated Capacitance (μF)	Case Size φD×L (mm)	tan δ	Leakage Current (μA) (at 20°C after 2 minutes)	Rated Ripple (mArms) (105°C/120Hz)	Part Number
4 (0G)	22	4×5.8	0.37	3	22	UUT0G220MCL1GS
	33	5×5.8	0.37	3	30	UUT0G330MCL1GS
	47	5×5.8	0.37	3	36	UUT0G470MCL1GS
	100	6.3×5.8	0.37	4	60	UUT0G101MCL1GS
6.3 (0J)	22	4×5.8	0.28	3	22	UUT0J220MCL1GS
	33	5×5.8	0.28	3	30	UUT0J330MCL1GS
	47	5×5.8	0.28	3	36	UUT0J470MCL1GS
	100	6.3×5.8	0.28	6.3	60	UUT0J101MCL1GS
10 (1A)	22	5×5.8	0.24	3	27	UUT1A220MCL1GS
	33	5×5.8	0.24	3.3	35	UUT1A330MCL1GS
	47	6.3×5.8	0.24	4.7	46	UUT1A470MCL1GS
	100	6.3×5.8	0.24	10	60	UUT1A101MCL1GS
16 (1C)	10	4×5.8	0.20	3	18	UUT1C100MCL1GS
	22	5×5.8	0.20	3.52	30	UUT1C220MCL1GS
	33	6.3×5.8	0.20	5.28	40	UUT1C330MCL1GS
	47	6.3×5.8	0.20	7.52	50	UUT1C470MCL1GS
25 (1E)	4.7	4×5.8	0.16	3	13	UUT1E4R7MCL1GS
	10	5×5.8	0.16	3	23	UUT1E100MCL1GS
	22	6.3×5.8	0.16	5.5	38	UUT1E220MCL1GS
	33	6.3×5.8	0.16	8.25	48	UUT1E330MCL1GS
35 (1V)	4.7	4×5.8	0.13	3	15	UUT1V4R7MCL1GS
	10	5×5.8	0.13	3.5	25	UUT1V100MCL1GS
	22	6.3×5.8	0.13	7.7	42	UUT1V220MCL1GS
50 (1H)	1	4×5.8	0.12	3	6.2	UUT1H010MCL1GS
	2.2	4×5.8	0.12	3	11	UUT1H2R2MCL1GS
	3.3	4×5.8	0.12	3	14	UUT1H3R3MCL1GS
	4.7	5×5.8	0.12	3	19	UUT1H4R7MCL1GS
	10	6.3×5.8	0.12	5	30	UUT1H100MCL1GS

- For taping specifications, recommended land size/soldering by reflow and minimum order quantity, please refer to the Guidelines for Aluminum Electrolytic Capacitors.
- Please select UUX, UUU if high C/V products are required.