


承认书 Specifications			型 名 Type	GCRH127M																									
			GLE 部品型号 GLEPart NO.	GCRH127M 系列																									
接受 Accepted by			客户部品型号 Customer's Part No.																										
			单位 Unit: mm	RoHS Comp.																									
外形尺寸 Physical dimensions																													
备注: 白色印字 使用材料 Materials																													
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="width: 10%;">NO.</th> <th style="width: 30%;">构成部品 Components</th> <th style="width: 40%;">材质 Materials</th> <th colspan="2" style="width: 20%;">原产国 Country of origin</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>磁性材料 Magnetic powder</td> <td>锰锌 Mn-Zn</td> <td colspan="2">中国 China</td> </tr> <tr> <td>2</td> <td>铜线 Wire</td> <td>改良聚胺脂涂布铜线 Polyurethane-system coated copper wire</td> <td colspan="2">德国 Germany</td> </tr> <tr> <td>3</td> <td>胶水 epoxy</td> <td>环氧树脂 Phenolic epoxy resin</td> <td colspan="2">中国 China</td> </tr> <tr> <td>4</td> <td>电极 Electrode</td> <td>铜镀锡 Tinned copper</td> <td colspan="2">中国 China</td> </tr> </tbody> </table>					NO.	构成部品 Components	材质 Materials	原产国 Country of origin		1	磁性材料 Magnetic powder	锰锌 Mn-Zn	中国 China		2	铜线 Wire	改良聚胺脂涂布铜线 Polyurethane-system coated copper wire	德国 Germany		3	胶水 epoxy	环氧树脂 Phenolic epoxy resin	中国 China		4	电极 Electrode	铜镀锡 Tinned copper	中国 China	
NO.	构成部品 Components	材质 Materials	原产国 Country of origin																										
1	磁性材料 Magnetic powder	锰锌 Mn-Zn	中国 China																										
2	铜线 Wire	改良聚胺脂涂布铜线 Polyurethane-system coated copper wire	德国 Germany																										
3	胶水 epoxy	环氧树脂 Phenolic epoxy resin	中国 China																										
4	电极 Electrode	铜镀锡 Tinned copper	中国 China																										
Issued	2019.09.21	首次作成	张立华																										
记号 Symbol	日期 Date	页 Page	变 更 内 容 Contents of revision																										
深圳市格莱尔电子有限公司 Shenzhen Glorious Electronic Co.,Ltd. TEL: 0755-27815501-5503 / 29305001-5003 FAX: 0755-27815500 / 29305500			承认者 Approved by	审查者 Checked by																									
			张立华	张顺钧																									
			刘子善																										

GCRH127M Type 一般规格 General Specifications (1/3)			
	项目 Item	规格 Specification	条件 Condition
1	弯曲测试 Bending test	Change from an initial value L : within $\pm 10\%$	<p>试件焊接在基板上, 按箭头方向以大约 0.5mm/秒的速度加压, 直到基板变形幅度到 3mm 保持 30 秒。 Apply pressure gradually in the direction of the arrow at a rate of about 0.5mm/s until bent depth reaches 3mm and hold for 30±5s.</p>  <p>Pressing device ↓ 加压治具 R340 试料 Specimen 45±2 基板 Board: 40X100mm 厚 Thickness: 1.0mm</p>
2	固着强度 Adhesion strength	Change from an initial value L : within $\pm 10\%$	<p>按箭头方向用 R0.5 的加压棒在试件中施加一定的静力并保持 60±5 秒。 A static load using a R0.5 pressing tool shall be applied the arrow and to the body of the specimen in the direction of the arrow and shall be hold for 60±5s. Measure after removing pressure.</p>  <p>Specimen 试料 1st 5N 2nd 5N</p>
3	耐振性 Vibration	Change from an initial value L : within $\pm 10\%$	<p>振动频率 10~55~10Hz, 振幅 1.5mm, 分 X, Y, Z 方向各振动 2 小时 (共 6 小时)。 The specimen shall be subjected to a vibration of 1.5mm amplitude, sweep frequency 10~55Hz (10Hz to 55Hz to 10Hz in a period of one minute) for 1 h in each of 3(X,Y,Z) axes.</p>
4	耐冲击性 Mechanical shock	Change from an initial value L : within $\pm 10\%$	<p>利用橡胶块式落下冲击试验机, 分别在 3 个互相垂直的方向以 981 m/S² 的冲击加速度落下。 Peak acceleration: 981 m/S² Duration of pulse: 6ms 3 times in each of 3(X,Y,Z)axes. The specimen must be fixed on test board. Three successive shock shall be applied in the perpendicular direction of each surface of the specimen.</p>
5	自然落下试验 Free fall test	Change from an initial value L : within $\pm 10\%$	<p>试件安装在基板上, 并固定在重 500 克的盒中, 由 1 米高自由落体, 3 个互相垂直的方向各 3 次。 The specimen must be fixed on test board. It must be equipped with instruments of which weight is 500g. Then it shall be fallen freely from 1m height to rigid wood 3 times in each of three axes.</p>
6	焊锡付着性 Solder ability	90% 以上的面积要被覆盖。 New solder shall cover 90% minimum of the surface immersed.	<p>试验品的电极深布松香后, 在 5~10 秒内焊锡, 焊锡槽温度 245±5°C, 时间: 3±0.5 秒。 Terminals shall be immersed for 5 to 10 seconds in flux at room temperature. Dip sample into solder bath containing molten solder at 245±5°C for 3±0.5 seconds.</p>
7	焊锡耐热性 Resistance to soldering heat	Change from an initial value L : within $\pm 10\%$	<p>试验方法 Test method 热风炉焊接 Reflow soldering method 预热 Preheat 150~180°C 90±30s 峰值温度 Peak temp 260°C (230°C min, 30±10s) 试验板的厚度 0.8mm 上按上面条件通过两次热风炉。 The specimen shall be subjected to the reflow process under the above condition 2 times. Test board shall be 0.8mm thick. Base material shall be glass epoxy resin.</p> <p>测定 Measurement 常温常湿中放置于 1 小时以上测试。 The specimen shall be stored at standard atmospheric conditions for 1 h in prior to the measurement.</p>

GCRH127M Type 一般规格 General Specifications (2/3)

	项目 Item	规格 Specification	条件 Condition
8	耐电压 Dielectric strength	没有损害。 Without damage.	在电极与磁材之间加入直流电压 100V 通电时间 1 分钟。 100V DC shall be applied for 60s between the terminal and the core.
9	绝缘抵抗 Insulation resistance	100MΩ 以上 100MΩ or more.	在电极与磁材之间加入直流电压 100V。 100V DC shall be applied between the terminal and the core.
10	耐寒性 Low temperature	Change from an initial value L : within ± 10%	在温度 -40 ± 3°C 中放置 500 ± 12 小时后，常温常湿中放置 1 小时以上 2 小时以内测试。 After stored at a temperature of -40 ± 3°C for 500 ± 12h. The specimen should be measured, then it should be measured under normal temperature and humidity in 1h~ 2h hours.
11	耐热性 Dry heat	Change from an initial value L : within ± 10%	在温度 85 ± 2°C 中放置 500 ± 12 小时后，常温常湿中放置 1 小时以上 2 小时以内测试。 The specimen shall be stored at a temperature of 85 ± 2°C for 500 ± 12h. Then it shall be stabilized under standard atmospheric conditions for 1 h before measurement. Measurement shall be made within 1h~ 2h.
12	耐湿性 Damp heat	Change from an initial value L : within ± 10%	在温度 60 ± 2°C，湿度 90 ~ 95% 中放置 500 ± 12 小时后，常温常湿中放置 1 小时以上 2 小时以内测试。 The specimen shall be stored at a temperature of 60 ± 2°C with relative humidity of 90 ~ 95% for 500 ± 12h. Then it shall be stabilized under standard atmospheric conditions for 1 h before measurement. Measurement shall be made within 1h~ 2h.
13	温度循环 Temperature cycle	Change from an initial value L : within ± 10%	以温度 -40°C 中放置 30 分钟，在 85°C 放置 30 分钟，中间转换时间不超过 2 分钟为一个循环。完成 500 个循环后，常温常湿中放置 1 小时以上 2 小时以内测试。 The specimen shall be measured after 500 continuous cycles of temperature change of -40°C for 30 min and 85°C for 30 min with the transit period of 2min or less. Then it shall be stabilized under standard atmospheric conditions for 1 h before measurement. Measurement shall be made within 1h~ 2h.
14	温度特性 Temperature drift	Inductance temperature coefficient 2000 ppm/°C or less	在温度 -25 ~ + 85°C 之间测试。 To be measured in the range of -25°C to 85°C.
15	使用温度范围 Operating temperature range	-40 ~ + 125°C	包括制品的发热温度。 Products heating temperature.
16	保存温度范围 Storage temperature range	-40 ~ + 85°C *(-40 ~ + 60°C)	在包装的状态下。 In packing state.

标准状态 Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions in making measurements and test as follows;



Ambient temperature : 5°C to 35°C, Relative humidity: 45% to 85%, Air pressure: 86kPa to 106kPa

If more strict measurement is required, measurement shall be made within following limits;

Ambient temperature : 20 ± 2°C, Relative humidity: 65 ± 5%, Air pressure: 86kPa to 106kPa

GCRH127M Type 一般规格 General Specifications (3/3)**条件 Reflow soldering condition**

- 1 回数: 2回
- 2 Reflow times: 2times max
- 3 We recommend infrared ray as heat source of reflow bath.
- 4 However halogen lamp shall be used, side heat will be beyond range of resistance heat, so we can't recommend it.

**推荐焊盘寸法 Recommended PCB pattern**

单位 Unit: mm

GCRH127M 个别规格 Part Specifications

客户部品型号 Customer's Part No	GLE 部品型号 GLE Part NO.	中心 InductanceLo (uH)	测定频率 Test Frequency (Hz/v)	直流阻抗 DC Resistance (mΩ) max.	饱和电流 Isat (A) Max. $\Delta L/L \geq -35\%$
	GCRH127M-2R2MC	2.2	100KHz/0.25V	7	25.5
	GCRH127M-4R7MC	4.7	100KHz/0.25V	16	15.9
	GCRH127M-5R6MC	5.6	100KHz/0.25V	20	14.0
	GCRH127M-6R8MC	6.8	100KHz/0.25V	21	13.3
	GCRH127M-8R2MC	8.2	100KHz/0.25V	23	12.2
	GCRH127M-100MC	10	100KHz/0.25V	24	11.2
	GCRH127M-150MC	15	100KHz/0.25V	31	9.00
	GCRH127M-180MC	18	100KHz/0.25V	35	5.10
	GCRH127M-220MC	22	100KHz/0.25V	40	7.57
	GCRH127M-330MC	33	100KHz/0.25V	70	6.22
	GCRH127M-390MC	39	100KHz/0.25V	75	4.50
	GCRH127M-470MC	47	100KHz/0.25V	80	5.28
	GCRH127M-560MC	56	100KHz/0.25V	130	4.50
	GCRH127M-680MC	68	100KHz/0.25V	105	4.26
	GCRH127M-820MC	82	100KHz/0.25V	143	3.80
	GCRH127M-101MC	100	100KHz/0.25V	163	3.52
	GCRH127M-121MC	120	100KHz/0.25V	170	1.90
	GCRH127M-151MC	150	100KHz/0.25V	247	3.01
	GCRH127M-221MC	220	100KHz/0.25V	376	2.36
	GCRH127M-331MC	330	100KHz/0.25V	574	2.00
	GCRH127M-391MC	390	100KHz/0.25V	650	1.50
	GCRH127M-471MC	470	100KHz/0.25V	861	1.64
	GCRH127M-681MC	680	100KHz/0.25V	1080	1.38
	GCRH127M-821MC	820	100KHz/0.25V	1470	1.26
	GCRH127M-102MC	1000	100KHz/0.25V	1660	1.14


Note:

许容公差 Inductance Tolerance : (特性以实物为准)



 J = ±5% K = ±10% L = ±15% M = ± 20% N= ±30%

GCRH127M 捆包规格 Packing Specifications


Unit : mm

1. 尺寸 Tape Dimensions

A	24.0
B	11.5
C	1.75
D	16.0
E	4.00
F	2.00
G	Ø1.50
H	0.40

2. 方法 Taping method 冷封 (The direction shall be seen from the top cover tape side.)**3. 卷盘寸法图 Reel dimensions**

A	330.0
B	Ø13.0
C	21.0
D	30.4
E	100
F	26.4

4. 捆包箱 Packing box

- 1 捆包箱材质 Packing case material
纸 Kraft paper
- 2 收纳数 Real quantity per packing box
2reel / 1box
- 3 数量/ 卷 Quantity : 500PCS / reel
- 4 表示 Marking
客户部品型号, 数量, Lot No.
Customer's part number, Quantity, Lot number.

禁用物质 Prohibited Substances

1. RoHS 规制的六种物质

- | | |
|------------|-------------------------------------|
| 1) 铅及其化合物 | Lead and its compounds |
| 2) 水银及其化合物 | Mercury and its inorganic compounds |
| 3) 镉及其化合物 | Cadmium and its compounds |
| 4) 六价铬化合物 | Hexavalent chromium compounds |
| 5) 多溴联苯 | PBB |
| 6) 多溴二苯醚 | PBDE |

2. 破坏臭氧层的化学物质使用限制

PROHIBITION TO USE OZONE DEPLETING SUBSTANCES (ODS)

- | | |
|----------------|-------------------------------------|
| 限制性物质 | Prohibited substances |
| 1) 氟氯化碳 | CFCS |
| 2) 氟哌丁苯 | Halon |
| 3) 四氯化碳 | Carbon tetrachloride |
| 4) 三氯乙烯 (三氯乙烷) | Trichloroethane (Methyl chloroform) |

我公司保证我司的产品和生产过程符合“RoHS 规则”，所有产品中使用的材料均是化学物质生产规则中登记的材料。

We confirm that our products and our production process accord with "rule of RoHS". All materials used in this product are registered material under Regulation of Manufacture of Chemical Substances.