1A1 THRU **1A7**



1.0 AMP SILICON RECTIFIERS



FEATURES


- * Low forward voltage drop
- * Low leakage current
- * High reliability
- * High current capability

MECHANICAL DATA

- * Case: Molded plastic
- * Epoxy: UL 94V-0 rate flame retardant
- * Lead: Axial leads, solderable per MIL-STD-202, method 208 guranteed
- * Polarity: Color band denotes cathode end
- * Mounting position: Any

VOLTAGE RANGE 50 to 1000 Volts CURRENT

1.0 Ampere



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.


TYPE NUMBER	1A1	1A2	1A3	1A4	1A5	1A6	1A7	UNITS
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current		•			•			
.375"(9.5mm) Lead Length at Ta=25°C	1.0							Α
Peak Forward Surge Current, 8.3 ms single half sine-wave								
superimposed on rated load (JEDEC method)	30						Α	
Maximum Instantaneous Forward Voltage at 1.0A	1.1						V	
Maximum DC Reverse Current Ta=25°C	5.0							μА
at Rated DC Blocking Voltage Ta=100℃	50							μА
Typical Junction Capacitance (Note 1)		15						pF
Typical Thermal Resistance Rθ JA (Note 2)		60						°C/W
Operating and Storage Temperature Range TJ, TsTG		-65—+150						


NOTES:


- 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
- 2. Thermal Resistance from Junction to Ambient .375" (9.5mm) lead length.

RATING AND CHARACTERISTIC CURVES (1A1 THRU 1A7)

FIG.1-TYPICAL FORWARD **CHARACTERISTICS** 50 INSTANTANEOUS FORWARD CURRENT, (A) 10 3.0 1.0 Tj=25℃ Pulse Width 300us 1% Duty Cycle 0.1 .01 .6 1.0 1.2










FIG.4-MAXIMUM NON-REPETITIVE FORWARD

